

PHILIPS

CertaFlux

LED

CertaFlux DLM Slim
1000lm 4"



Datasheet

Plug and Play, easy to use downlight solution

CertaFlux DLM Slim 1000lm 4"

Certaflux DLM Slim downlight module provides plug & play downlight solution with affordable cost but no sacrifice on light quality. The module is integrated with optical and heatsink which help to make the product extremely easy to use. Optimized diffuser gives uniform light. The family is available from 600 lm - 2000lm with different cut out size in 4 CCTs. Certaflux DLM Slim is fully compatible with Philips recommended driver.

Key features and benefits

Integrated with optics and heatsink makes it easy to use

High efficacy, up to 126lm/W @ module level

Full portfolio from 600lm - 2000lm, available in 830/840/850/865 CCT with 4" 6" 8"

Optimized diffuser provides good uniformity

2 years warranty

July 2017

Ordering data

Commercial product name	12NC	Box quantity
CertaFlux DLM Slim 1000lm 830 4"	9290 014 43580	30
CertaFlux DLM Slim 1000lm 840 4"	9290 014 43680	30
CertaFlux DLM Slim 1000lm 850 4"	9290 014 43780	30
CertaFlux DLM Slim 1000lm 865 4"	9290 014 62380	30

Not all products are globally available by default.

Please contact your local Philips Lighting representative for local availability.

Drive currents

Parameter	Nominal*	Life**	Max***	Unit
CertaFlux DLM Slim 1000lm 4"	300	370	420	mA

Module temperatures

Parameter	Nominal*	Life**	Max***	Unit
T _c (case temperature at T _c point)	80	80	100	°C

* Nominal value at which typical performance is specified

** Value at which life time is specified


*** Maximum value for safe operation, do not operate above this value

Optical characteristics - table per color (CCT)

CertaFlux DLM Slim 1000lm 830 4"

Parameter	Min	Typ	Max	Unit
Luminous flux	882	980	1127	lm
Module efficacy		98		lm/W
Correlated color temperature (CCT)		3150		K
Color coordinates (CIEx, CIEy)		(0.426, 0.399)		-
Color consistency			6	SDCM
CRI	80			
Radiation angle		110		deg
Photobiological safety			RG1	


Measurement precision for flux +/- 5%. Measurement precision for efficacy +/- 6%. Measurement precision for x, y +/- 0.005. Measurement precision for CRI +/- 1.5



CertaFlux DLM Slim 1000lm 840 4"

Parameter	Min	Typ	Max	Unit
Luminous flux	936	1040	1196	lm
Module efficacy		104		lm/W
Correlated color temperature (CCT)		4200		K
Color coordinates (CIEx, CIEy)		(0.373, 0.374)		-
Color consistency			6	SDCM
CRI	80			
Radiation angle		110		deg
Photobiological safety			RG1	


Measurement precision for flux +/- 5%. Measurement precision for efficacy +/- 6%. Measurement precision for x, y +/- 0.005. Measurement precision for CRI +/- 1.5



CertaFlux DLM Slim 1000lm 850 4"

Parameter	Min	Typ	Max	Unit
Luminous flux	936	1040	1196	lm
Module efficacy		104		lm/W
Correlated color temperature (CCT)		5400		K
Color coordinates (CIEx, CIEy)		(0.335, 0.350)		-
Color consistency			6	SDCM
CRI	80			
Radiation angle		110		deg
Photobiological safety			RG1	


Measurement precision for flux +/- 5%. Measurement precision for efficacy +/- 6%. Measurement precision for x, y +/- 0.005. Measurement precision for CRI +/- 1.5



CertaFlux DLM Slim 1000lm 865 4"


Parameter	Min	Typ	Max	Unit
Luminous flux	936	1040	1196	lm
Module efficacy		104		lm/W
Correlated color temperature (CCT)		6600		K
Color coordinates (CIEx, CIEy)		(0.313, 0.328)		-
Color consistency			6	SDCM
CRI	80			
Radiation angle		110		deg
Photobiological safety			RG1	

Measurement precision for flux +/- 5%. Measurement precision for efficacy +/- 6%. Measurement precision for x, y +/- 0.005. Measurement precision for CRI +/- 1.5



Beam shape

CertaFlux DLM Slim 1000lm 4"



Electrical characteristics


- CertaFlux DLM Slim 1000lm 830 4"
- CertaFlux DLM Slim 1000lm 840 4"
- CertaFlux DLM Slim 1000lm 850 4"
- CertaFlux DLM Slim 1000lm 865 4"

Parameter	Min	Typ	Max	Unit
Forward voltage		33.4	36.9	V
Power consumption		10.0	11.1	W
Number of modules in series per chain			1	
Number of modules in parallel per chain			1	

Measurement precision for Vf +/- 3%. Measurement precision for power +/- 3.3%.
No series or parallel connection allowed.

Lumen maintenance graphs

Lumen maintenance at I-life and Tc-life conditions




Wiring

Specification item	Value	Unit	Condition
Input wire cross-section	0.75...0.75	mm ²	solid, fused, stranded
	18...18	AWG	solid, fused, stranded
Input wire strip length	8...10	mm	

Mechanical characteristics

CertaFlux DLM Slim 1000lm 830 4"
 CertaFlux DLM Slim 1000lm 840 4"
 CertaFlux DLM Slim 1000lm 850 4"
 CertaFlux DLM Slim 1000lm 865 4"

Parameter	Min	Typ	Max	Unit
Length	118	120	122	mm
Width	99	100	103	mm
Height	34	36	38	mm



Absolute ratings

Parameter	Min	Typ	Max	Unit
Current through the LED module (I-max)			420	mA
Case temperature (Tc-max)			100	°C
Power at rated Vf-max and I-max			15.7	W
ESD (direct contact)			8	kV
Ambient temperature	-20		35	°C
Storage temperature	-40		65	°C

Application information

Certificates and Standards

CE/CB/CQC

IEC/EN 62031:2008 + A1:2013 + A2:2015, IEC TR 62778:2014, EN 55015:2013 + A1:2015, EN 61547:2009, EN 61000-3-2:2014, EN61000-3-3:2013, GB 19510.1-2009, GB 24819-2009


Environmental

RoHS/REACH

Application

IP rating	No IP-rating
Overheating protection	No
Luminaire class	IEC Class II
Dimming	Yes

Operating Window





© 2017 Philips Lighting Holding B.V. All rights reserved.

This document contains information relating to the Philips Lighting portfolio, intended for companies who may be interested in developing their product offering. Note that the information provided is subject to change. Philips Lighting does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

www.philips.com/technology

07/2017