

PHOTOMETRIC RESULTS

LVE22170

Lamp Data	CPO-TT 90W/628				Date:	2012-11-23 12:54:19 PM	
Description	LVE22170						
TestNumber	EF90/002A2						
File	LVE22170						
Comment	Isabel Francois / Philips Turnhout						
Ballast	HID-DV Dali Xt 90/S CPO-TW				Nominal Flux	10535 lm	
Conditions							
Protocol	12 C-planes / 37 Cones				Operator	Philips	
	C-planes ArmUp						
Measured Values					Flux	10471 lm	
Power	97.2989 W	Voltage	230.330 V	Current	0.427 A		

Polar diagram LVE22170 / C-Plane measurement

