



Dim. (mm)	Thickness (0.5 - 1mm)	Thickness (3mm)	Angle
	Tolerance (公差)	Tolerance (公差)	
0 - 3	±0.12	±0.17	±1°
3 - 10	±0.17	±0.24	
10 - 25	±0.23	±0.32	
25 - 63	±0.29	±0.4	
63 - 160	±0.39	±0.55	
160 - 400	±0.5	±0.7	
400 - 1000	±0.7	±0.9	

注：公差标准参考GB/T13914，成形中压件尺寸公差等级F T6

UN-D1041		TOLERANCES UNLESS OTHERWISE STATED		Opt design No.	
				Optics Designer	
				Optics Checker	
GENERAL ROUGHNESS		UNIT mm	MATERIAL : Ø	WEIGHT (g)	Assembly NO:
SCALE 3rd ANGLE PROJECT Ø		TREATMENT :			Milestone revision NO:
					ORDER No
					QUANT
DLM Flex G2 L2		Part No:	Ver No.	Date	Designer
		Ø	Ø	2015/8/18	Luke Tian
Drawing		Ø			
Approver		DATA FMT: UG 7.5 File		FMT Vesion no:1	Supers:
doc. manager		ØPHILIPS GDC LS&C		Total sheet:	sheet: