

中国国家强制性产品认证证书

证书编号: 2015011002760729

委托人名称、地址

飞利浦照明(中国)投资有限公司
上海市闵行区田林路888弄9号楼

生产者(制造商)名称、地址

飞利浦照明(中国)投资有限公司
上海市闵行区田林路888弄9号楼

生产企业名称、地址

横店集团得邦照明股份有限公司
浙江省东阳市横店工业区工业大道183号

产品名称和系列、规格、型号

LED模块用交流电子控制装置(LED控制装置, 内装式, 恒流模式,
定温热保护: 110℃)
见附件。220-240V~ 50/60Hz

产品标准和技术要求

GB19510.14-2009, GB19510.1-2009, GB17743-2007, GB17625.1-
2012

上述产品符合强制性产品认证实施规则
CNCA-C10-01: 2014的要求, 特发此证。

发证日期: 2016年06月15日

有效期至: 2019年02月11日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2015年03月18日

本证书的相关信息可通过国家认监委网站www.cnca.gov.cn查询




主任:

中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. : 2015011002760729

NAME AND ADDRESS OF THE APPLICANT

Philips Lighting (China) Investment Co., Ltd.
Building 9, Lane 888, Tianlin Road, Minhang District, Shanghai City,
P.R. China

NAME AND ADDRESS OF THE MANUFACTURER

Philips Lighting (China) Investment Co., Ltd.
Building 9, Lane 888, Tianlin Road, Minhang District, Shanghai City,
P.R. China

NAME AND ADDRESS OF THE FACTORY

Hengdian Group Tospo Lighting Co., Ltd.
No.183 Industrial Avenue, Hengdian Industrial Zone, Dongyang City,
Zhejiang Province, P.R.China

NAME, MODEL AND SPECIFICATION

A.C. Supplied Electronic Controlgears For LED Modules (LED
Controlgear, Built-in, Constant Current Mode, Temperature Declared
Thermally Protected:110°C)
See Appendix. 220-240V~ 50/60Hz

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB19510.14-2009, GB19510.1-2009, GB17743-2007, GB17625.1-2012

This is to certify that the above mentioned products have met the
requirements of implementation rules for compulsory certification(REF
NO. CNCA-C10-01:2014).

Date of issue: Jun.15,2016 Date of expiry: Feb.11,2019

Validity of this certificate is subject to positive result of the regular
follow up inspection by issuing certification body until the expiry date.

Date of original certification: Mar.18,2015

This certificate can be verified through CNCA's website: www.cnca.gov.cn



President:


Wang Kejiao

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 1 页 共 1 页

证书编号: 2015011002760729

纸号: 1425256

序号	型号	输出电流	最大输出电压	输出电压	输出功率	tc点温度
1	CertaDrive 40W 240mA 160V 230V	0.24A	Max. 340V	116-160V	38W	75°C
2	CertaDrive 40W 360mA 110V 230V	0.36A	Max. 300V	80-116V	42W	75°C
3	CertaDrive 60W 300mA 200V 230V	0.3A	Max. 340V	145-200V	60W	80°C
4	CertaDrive 60W 360mA 170V 230V	0.36A	Max. 340V	120-170V	61.2W	80°C
5	CertaDrive 59W 0.37A 160V 230V	0.37A	Max. 350V	125-160V	59.2W	80°C
6	Certadrive 36W 0.29A 122V 230V	0.295A	Max. 340V	85-122V	36W	75°C

以上均为 220-240V~ 50/60Hz.

注: 此附录与证书同时使用时有效;





主任:

中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 1 页 共 1 页

证书编号: 2015011002760729

纸号: 1239097

型号	输入规格	输出 电流	最大输出 电压	输出电压	输出功率	Tc 点温度
CertaDrive 30W 330mA 82V 230V	220-240V ~ , 50/60Hz, 0.15A , 31W	0.33A	Max.300V	60-85V	28W	75 °C
CertaDrive 40W 360mA 110V 230V	220-240V ~ , 50/60Hz, 0.21A , 46W	0.36A	Max.300V	80-116V	42W	75 °C
CertaDrive 60W 360mA 170V 230V	220-240V ~ , 50/60Hz, 0.3A, 67W	0.36A	Max.340V	120-170V	61.2W	80 °C
CertaDrive 36W 0.31A 117V 230V	220-240V ~ , 50/60Hz, 0.20A , 39.6W	0.31A	Max.300V	85-117V	36W	75 °C
CertaDrive 58W 0.39mA 150V 230V	220-240V ~ , 50/60Hz, 0.31A , 64.5W	0.39A	Max.340V	108-150V	58.5W	75 °C

注: 此附录与证书同时使用时有效。





主任:

中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

变更结论

Modification Approval

证书编号Certificate No.: 2015011002760729

申请编号Application No.: A2015CCC1002-2154068

申请人Applicant: 飞利浦(中国)投资有限公司 Philips (China) Investment Co., Ltd.

证书编号Certificate No. (变更前Original): 2015011002760729

证书编号Certificate No. (变更后Present): 2015011002760729

变更产品名称 LED模块用交流电子控制装置(LED控制装置, 内装式, 恒流模式, 定温热保护: 110℃)

Name of Product Modified: A.C. Supplied Electronic Controlgears For LED Modules (LED Controlgear, Built-in, Constant Current Mode, Temperature Declared Thermally Protected: 110℃)

型号Model/Type: 见附件: 220-240V~, 50/60Hz

变更情况Situation of Modification:

见附件See Annex:


序号	项目Item	变更前Original	变更后Present
1	PCB变更	见检测报告编号: C-00201-15-0257	见检测报告编号: C-00201-15M-2043
2	增加产品型号	见检测报告编号: C-00201-15-0257	见检测报告编号: C-00201-15M-2043
3	关键件变更	见检测报告编号: C-00201-15-0257	见检测报告编号: C-00201-15M-2043

Above Modification is approved. The present will replace the original.

现批准以上变更。

批准日期(Date): 2015-10-15

第 1 页 / 共 1 页



主任:

中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>

