

# CERTIFICATE

Issued to:  
Applicant:  
**Philips Lighting B.V.**  
**High Tech Campus 45**  
**5656 AE Eindhoven**  
**The Netherlands**

Manufacturer/Licensee:  
**Philips Lighting B.V.**  
**High Tech Campus 45**  
**5656 AE Eindhoven**  
**The Netherlands**

Product : Battery supplied LED controlgear for emergency lighting (self-contained)  
Trade name : PHILIPS  
Types : TrustSight Basic L 20-95V 3W  
TrustSight Basic L 20-95V 6W  
TrustSight Pro L 20-95V 3W  
TrustSight Pro L 20-95V 6W

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard EN 61347-1:2008; EN 61347-2-7:2012
- an inspection of the production location according to CENELEC Operational Document CIG 021
- a certification agreement with the number 2037471

DEKRA hereby grants the right to use the ENEC KEMA-KEUR certification mark.

The ENEC KEMA-KEUR certification mark may be applied to the product as specified in this certificate for the duration of the ENEC KEMA-KEUR certification agreement and under the conditions of the ENEC KEMA-KEUR certification agreement.


This certificate is issued on: 25 November 2015 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 2184290.01

DEKRA Certification B.V.



drs. G.J. Zoetbrood  
Managing Director



H.J. Brouwer  
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE  
DUTCH ACCREDITATION  
COUNCIL



**SPECIFICATION OF THE CERTIFIED PRODUCT****Product data**

product	:	Battery supplied LED controlgear for emergency lighting (self-contained)
trade name	:	PHILIPS
types	:	TrustSight Basic L 20-95V 3W, TrustSight Basic L 20-95V 6W, TrustSight Pro L 20-95V 3W, TrustSight Pro L 20-95V 6W
rated current (In)	:	25 mA
rated voltage (Un)	:	220-240 V
rated power (Pn)	:	4 W
nature of supply	:	ac
rated frequency	:	50/60 Hz
output voltage (Uout)	:	110 V
rated output (Pout)	:	see product data per type
output current (Iout)	:	see product data per type
ambient temperature range (ta)	:	-20...+55 °C
max. case temperature (tc)	:	75 °C
powerfactor (PF)	:	0,7C
description	:	Built-in

**Product data - type TrustSight Basic L 20-95V 3W**

rated output (Pout)	:	3 W
output current (Iout)	:	30 - 150 mA

**Product data - type TrustSight Basic L 20-95V 6W**

rated output (Pout)	:	6 W
output current (Iout)	:	60 - 300 mA

**Product data - type TrustSight Pro L 20-95V 3W**

rated output (Pout)	:	3 W
output current (Iout)	:	30 - 150 mA

**Product data - type TrustSight Pro L 20-95V 6W**

rated output (Pout)	:	6 W
output current (Iout)	:	60 - 300 mA

**TESTS****Test requirements**

EN 61347-1:2008 +A1:2011 +A2:2013  
EN 61347-2-7:2012

**Test result**

The test results are laid down in DEKRA test file 2184290.00.

**Conclusion**

The examination proved that all test requirements were met.

Tested by : L.N.H. Huynh



Checked by : T.H.J.M. Michels

