

PHILIPS

Xtanium

LED Xtreme driver



Design-in Guide

Reliable Xtreme technology for demanding LED applications

February 2017

Contents

Introduction to this guide	4	Configure Your Driver	25
Applications	4	Introduction	25
Information and support	4	MultiOne characteristics	26
Document overview	4	Basis blocks	26
		Philips MultiOne Interface tool	26
Warnings and instructions	5	Philips MultiOne Interface tool	27
Safety warnings and installation instructions	5	Philips MultiOne Software	27
		System requirements	27
Xitanium LED Xtreme drivers	6	Getting Started	28
Xitanium LED Xtreme drivers	6	MultiOne System	29
Xitanium LED Xtreme driver versions	6	Settings	29
Configurability Interface (tooling)	6	More information of using Multione	29
Mechanical Design-in	10	Control features	30
Form factors	10	Adjustable output current (AOC)	30
		Adjustable Light Output (ALO)	30
Thermal Design-In	11	LED Module Temperature Protection (MTP)	31
Introduction	11	Constant Light Output (CLO, CLO LITE)	31
Driver case Temperature Point (Tc point)	11	End of Life (EOL)	32
To measure Tc at the Tc point	11	Adjustable Start up Time (AST)	32
Relation between Tc and ambient temperature	11	Light Source Operating Hours (LSO)	32
Module Temperature Protection (MTP)	12	DC emergency dimming operation (DCemDIM)	33
		Control Input 1-10 V	33
Electrical Design-In	14	DALI	34
Xitanium Driver Operating window	14	AmpDim	36
To Select an Appropriate Driver	15	Dynadimmer	37
Programming the output current	15	OEM Write Protection (OWP)	38
Connectors	16		
Mains operating conditions	16	Compliance and approval	39
To Determine the Number of Drivers on a MCB	20		
Surge immunity	21	Disclaimer	40
Touch current	21		
Electromagnetic compatibility (EMC)	22		
Improvement in EMC Performance	23		
Remote mounting and EMC	24		
Electrical insulation	24		

Introduction to this guide



Examples of Xitanium LED Xtreme drivers

Thank you for choosing the Philips Xitanium LED Xtreme drivers. In this guide you will find the information needed to integrate these drivers into a LED luminaire or LED system.

This edition describes the configurable Xitanium FULL Prog (Xi FP) and LITE Prog (Xi LP) LED Xtreme drivers. We advise you to consult our websites for the latest up-to-date information.

Applications

The Xitanium LED Xtreme drivers are designed to operate LED solutions for outdoor and industrial lighting, like roads, streets and highway applications. If you use Philips LED drivers in combination with Philips LED modules, specific design-in guides are available from the below mentioned technology websites.

Information and support

Please consult your local Philips office or visit:
www.philips.com/technology
www.philips.com/multione

Design-in support


On request Design-in support from Philips is available. For this service please contact your Philips sales representative.

Document overview

In order to provide information in the best possible way, Philips' philosophy on product documentation is the following.

- Commercial leaflet contains product family information & system combinations
- Datasheet contains the product specific specifications
- Design-in guide describes how the product is to be designed-in

All these documents can be found on the download page of the OEM website www.philips.com/technology. If you require any further information or support please consult your local Philips office.



Warnings and instructions



Warning:

- Avoid touching live parts!
- Do not use drivers with damaged housing and/or connectors!
- Do not use drivers with damaged wiring!

Safety warnings and installation instructions

- Do not use damaged products
- The luminaire manufacturer is responsible for his own luminaire design and has to comply with all relevant safety standards
- The Xitanium LED Xtreme drivers are suitable for built-in use only and must not be exposed to the elements such as snow, water and ice or to any other chemical agent which can be expected to have an adverse effect on the driver (e.g. corrosive environments). It is the responsibility of both luminaire manufacturer and installer to prevent exposure. The suggested minimum luminaire IP rating in the driver datasheet serves only as guidance and a higher IP rating may be required under certain application conditions. Common sense needs to be used in order to define the proper luminaire IP rating.
- Do not service the driver when the mains voltage is connected, this includes connecting or disconnecting the LED module.
- No components are allowed between the LED driver and the LED modules other than connectors and wiring intended to connect the LED driver to the module.
- Please provide adequate earth and/or equipotential connections whenever possible or applicable.

Philips Design-in support is available; please contact your Philips sales representative.

Xitanium LED Xtreme drivers



Xitanium LED Xtreme Drivers

Xitanium LED Xtreme drivers

Xitanium LED Xtreme drivers are designed to operate LED solutions for general lighting applications such as street, road and highbay lighting.

In the coming years LEDs will continue to increase in efficiency, creating generation and complexity challenges for OEMs. With Xitanium LED Xtreme drivers, flexibility in luminaire design is assured thanks to an adjustable output current. Application-oriented operating windows offer the flexibility required to provide the stable lumen output and light quality levels that lighting specifiers and architects demand. The adjustable output current also enables operation of various LED PCB solutions from different manufacturers.

Xitanium LED Xtreme driver versions

The Xitanium LED Xtreme drivers described in this guide are available in two different versions: FULL Prog and LITE Prog. These drivers come in a wide range of power ratings that enable the most popular light output levels for general outdoor and highbay applications. It is always highly recommended to check our latest Xitanium LED Xtreme driver leaflet for the most up-to-date overview of our range. This leaflet can be downloaded at www.philips.com/technology

Detailed specifications can be found in the Xitanium driver datasheets which can be downloaded at www.philips.com/technology.

Configurability Interface (tooling)

The FULL Prog and LITE Prog Xitanium LED Xtreme drivers are programmable. A large package of features and parameters in these drivers can be set via a specific tool and interface to the tool. This tool is the MultiOne Configurator. There are two types of interface technology used to communicate with this tool:

- DALI
- SimpleSet (New)

SimpleSet

Philips SimpleSet new wireless programming technology allows luminaire manufacturers to quickly and easily program Xitanium LED Xtreme drivers in any stage during of the manufacturing process, without a connection to mains power, offering great flexibility.

As a result, orders can be met faster while reducing cost and inventory.

For more information, please visit www.philips.com/multione or contact your local Philips representative.

	Xitanium sXt Single Current	Xitanium sXt LITE Prog	Xitanium sXt FULL Prog
Lifetime 100kHrs	•	•	•
Surge Protection 8kV/6kV	•	•	•
1-10V	•	•	
LineSwitch		•	•
Adjustable Output Current		•	•
SimpleSet®		•	•
Constant Light Output		LITE	•
DynaDimmer		LITE	•
Diagnostics		Basic	•
Module Temperature Protection (NTC)			•
ThermalGuard			•
DALI			•
AmpDim			•
MainsGuard			•
DC-Emergency			•
Adjustable Startup Time			•
Reset LED module operating hours			•

Adjustable Output Current (AOC)

Flexibility in luminaire design is ensured by the adjustable output current (AOC). The adjustable output current enables operation of various LED configurations from different LED manufacturers whilst also ensuring the solution remains “future proof” for new LED generations. The output current can be configured with the Philips MultiOne Software and the SimpleSet interface. More information about AOC and how to set the output current can be found in the chapter “Electrical design-in”. Information about configuring drivers with SimpleSet can be found in the chapter “Configurability”.

LED Module Temperature Protection (MTP)

Thermal protection of LED modules is possible by integrating a NTC (Negative Thermal Coefficient) resistor in the LED module. More details about the NTC resistor can be found in the Chapter “Thermal design-in”.

Dimming interfaces

Interfacing with the Xitanium LED Xtreme drivers can be done via below interfaces:

- DALI
- 1-10V
- LineSwitch
- Mains input (AmpDim)

Supported interfaces can be found in the naming of the drivers. (see chapter Naming)

Amplitude Modulation (AM) output dimming

Philips Xitanium LED Xtreme drivers dim the output to the LEDs by means of Amplitude Modulation (AM) dimming. This means that at no stage of the dimming, Pulse Width Modulation (PWM) at the output to the LEDs is involved. AM dimming guarantees the most smooth and flicker-free operation over the entire dimming range.

Hot wiring

Xitanium LED Xtreme drivers cannot be serviced, connected or disconnected from the LED module when the mains voltage is connected. Please make sure that power is turned off when working on a Xitanium driver.

DC mains operation

Certain Xitanium LED Xtreme drivers are allowed to be connected to a DC power grid (e.g. central emergency system). The driver behavior once switched to DC input voltage can be programmed via MultiOne software. More details about DC input voltage suitability can be found in the driver datasheet.

Constant Light Output

Traditional light sources suffer from depreciation in light output over time. This applies to LED light sources as well. The CLO feature enables LED solutions to deliver a constant lumen output throughout the life of the light engine. Based on the type of LEDs used, heat sinking and driver output current, a correction of the lumen depreciation can be entered into the driver. The driver then counts the number of operating hours and will correct the output current based on this input.

Since the CLO curve is not generic, the OEM needs to determine the appropriate CLO curve. This can be used to differentiate on e.g. lumen output or power consumption over lifetime.

The CLO feature can be programmed with the Philips MultiOne configurator tool. More information can be found on www.philips.com/multione.

OEM Write Protection (OWP)

OWP allows the OEM to protect their driver setting over the lifetime of the driver by using a password. Drivers equipped with OWP will show this in the feature list if read out by the tool MultiOne.

Specific feature and also the OWP can be enabled and protected with that password to prevent unauthorized changes.

The password management is under the responsibility of the company which is setting it.

Driver diagnostics


On selected Xitanium LED Xtreme drivers the Diagnostics functionality is available. The purpose of Diagnostics is to gather information and help diagnose the history of the driver and connected LED module. The Diagnostics feature consist mainly of counters which keep track of specific variables like the number of startups of the driver, operating hours, temperature of driver and LED modules, current and voltages etc.

More information on the diagnostics see instruction manual of MultiOne Engineering at www.philips.com/multione

When the driver is shutdown the diagnostics data is stored automatically in non-volatile memory.

Naming of the drivers: example

Xitanium LED Xtreme drivers are now part of a new naming system. An example can be seen below.



Mechanical Design-in

Form factors

Xitanium LED Xtreme drivers are available in different housing dimensions. The specific dimensions can be found in the driver datasheet. 3D CAD files are available to verify fitment and can be found at www.philips.com/technology.

Drivers need to be built in such that the driver housing and the driver input and output connectors are not affected by potential water ingress in the luminaire (e.g. due to luminaire sealing malfunction or condensation).

It is highly recommended to mount the driver by using all available mounting feet in order to achieve maximum mechanical robustness against shocks and vibration. The recommended mounting torque is 1.5Nm. This value should not be exceeded in order to prevent deformation of the mounting feet. The use of rivets is not recommended since mounting torque cannot be controlled; damage to the mounting feet or loose mounting may result.

Mounting screw dimensions should be based on the specified fixing hole diameter in the driver datasheet. Oversized and undersized screws should not be used in order to prevent damage to the mounting feet or loose mounting.

Please allow for sufficient free space around the driver SimpleSet antenna if the driver is to be configured after mounting in the luminaire. The minimum recommended space is depending on the type of SimpleSet configuration tool. Using the tool as shown here (LCN9620), the minimum distance is 19 mm (+/-1mm).

Depending on the application and the use in development, factory or field, another configuration tool can be selected. Please check the website www.philips.com/multione to find the correct type.

Every published interface tool is officially approved for use with the MultiOne software. The tool type number can be found by checking the LCN label on the tool itself.

Note: the use of an unapproved tool may result in wrong or bad connection and configuring malfunctioning.

In order to familiarize oneself with SimpleSet a free SimpleSet engineering tool is available from our local Philips representative. This engineering tool is not intended for production or field service purposes but for engineering testing only.



LCN9620 SimpleSet interface tool

Thermal Design-In

Introduction

This chapter describes two aspects of the thermal design of the Xitanium LED Xtreme drivers:

1. The LED driver itself and relationship between Tc point and lifetime of the LED driver.
2. Module Temperature Protection (MTP) function to ensure lifetime of LED module.

To facilitate design-in of LED drivers, the critical thermal management points of the LED driver are set out in this section. In Philips' product design phase all possible precautions have been taken to keep the component temperature as low as possible. However, the design of the luminaire and the ability to guide the heat out of the luminaire are of utmost importance. If these thermal points are taken into account this will ensure the optimum performance and lifetime of the system.

Driver case Temperature Point (Tc point)

To achieve optimal lifetime and reliability, it is critical that the temperature of the components in the driver remains within its rating.

The driver case temperature (Tc) is a reference for the temperatures of the critical internal driver components. The location of the Tc point is identified on the product label. Tc point is marked by the *-sign on the label of the driver.

To measure Tc at the Tc point

The temperature can be measured using a thermocouple that is firmly glued to the driver housing. For a representative measurement the temperature must be stable before any reliable data can be obtained (typically > 3 hours).

Note: Xitanium FULL Prog drivers allow for a driver-internal temperature readout through the MultiOne Diagnostics feature. This readout does not present the driver Tc point temperature and should not be used to define thermal suitability of the driver in the application.

Relation between Tc and ambient temperature

The Tc increases, by approximation, linearly with the driver ambient temperature (Tamb). The temperature offset between driver Tamb and Tc depends on the thermal design of the luminaire and the actual delivered output power relative to the specified nominal output power. A lower output power allows for a higher driver ambient temperature as long as the maximum specified driver Tc is not exceeded. For the approved driver ambient temperature range as well as specified Tc point values please check the specific driver datasheet.

Module Temperature Protection (MTP)

NTC and thermal design

This feature helps to protect the LEDs when operated during abnormal thermal application conditions. The thermal design of an LED module should be designed in such a way that the temperature of the LED module (Tc-life) is not exceeded under normal application conditions. The utilization of an NTC (Negative Temperature Coefficient resistor) serves the purpose to help achieve the lifetime of the LED module if external thermal influences result in the temperature for lifetime (Tlife) being exceeded. When this occurs the light output will be regulated down to remain below the critical temperature of the LEDs.

The following three NTC part numbers are supported in combination with Philips FULL Prog drivers:

1. 10k NTC – Murata, part number NCP18XH103J03R
2. 15 k NTC – Vishay 15 kOhm, part number NTCS0805E3153GMT (previous p/n: 2381 615 54153)
3. 15 k NTC – Murata, part number NCP15XW153E03RC (with a separate 390 ohms fixed-value resistor in series with the NTC)

Setting MTP behavior (programmable drivers only)

It is possible to set the temperature at which the MTP feature is activated, defined by “MTP warn” and the slope, defined by “MTP max”. Using the MultiOne Configurator software these settings can be changed.

Setting the thermal de-rating point via NTC


The driver will start reducing the light output when the NTC reaches a value of 2524 Ohm. The NTC should be selected such that 2524 Ohm represents the critical temperature of the LED module in the application.

For example: An LED module has a defined Tc life at 70 °C. Taking into account the typical tolerances of the NTC of ± 5 °C, this gives a typical value for the NTC of 75 ± 5 °C. By choosing this setting of 75 °C, we ensure that the driver will not dim the output, due to a too high temperature, before the module reaches 70 °C. The following graph shows a typical R vs. T curve of an NTC resistor. To match 2524 Ohm at this temperature, the NTC of 15 kilo-Ohm has been selected.


Note: the driver NTC interface has its own ground reference.

For proper MTP functioning it is not allowed to combine the NTC ground wire with the LED – ground wire.

Note: the length of the two NTC wires between driver and LED module is not allowed to exceed 60cm due to EMC and noise immunity reasons.



Electrical Design-In



1. Required set point for the LED solution
2. Current can be set to needs within range
3. Driver adapts to required voltage, given it fits range
4. Driver minimum power limit
5. Driver maximum power limit

Example Operating window of a Xitanium driver

Note: by means of dimming it is possible to go below the minimum value of the specified output current.

Xitanium Driver Operating window

LED technology is rapidly evolving. Using more efficient LEDs in a next generation means the same light output can be achieved with lower currents. At the same time, LEDs can be driven at different currents levels based on the application requirement. Typically, LED drivers are available in discrete current levels, e. g. 350 mA, 530 mA or 700 mA. It is often necessary to replace a driver when more efficient LEDs or different LED boards become available.

One of the key features of the Xitanium LED Xtreme drivers is the adjustable output current (AOC), offering flexibility and future-proof luminaire design. The Xitanium drivers can operate in a certain “operating window”. This window is defined by the maximum and minimum voltage and current that the driver can handle. An example of an operating window is shown on the left. The area indicates the possible current/voltage combinations. The current selected will depend on the type and manufacturer of the LEDs or the specific LED configuration of the PCB design. The voltage is the sum of the LEDs used (total V_f string). The operating window of every driver can be found in the driver datasheet which can be downloaded at www.philips.com/technology.

The output current of these drivers can be set in two ways.

1. Drivers with SimpleSet functionality can be configured using the Philips MultiOne software and SimpleSet interface.
2. DALI driver versions can be programmed both via SimpleSet and DALI interface. More information can be obtained at www.philips.com/multione.

To Select an Appropriate Driver

Depending on your requirements, several drivers can be a solution for you. The following steps can help you in selecting a driver. For a complete overview of the available drivers, please refer to the website www.philips.com/technology.

1. Determine your required driver current (I_{drive}) and voltage (V_f)
2. Calculate the required power (P_{drive}) where $P_{drive} = V_f \times I_{drive}$ (W)
3. Select the datasheets from the website mentioned above based on the driver having a higher power than required.
4. Does the required current fit the current range of the driver? The current range of the driver can be seen in the name itself. For example, for driver Xi 75W LP 0.2 – 0.7A S1 230 V S240 sXt, the minimum programmable driver current is 0.2 A and maximum is 0.7 A.
 - $I_{driver\ min} \leq I_{drive} \leq I_{driver\ max}$?
5. Does the required voltage fit the voltage range of the driver? The exact value can be found in the datasheet.
 - $V_{driver\ min} \leq V_f \leq V_{driver\ max}$?
6. Does the required power fit the power range of the driver? In the naming of the driver, you can see the maximum possible output power. For example, for driver Xi 150W LP 0.3-1.0A SL 230V S240 sXt, the maximum output power is 150W.
 - $P_{driver\ min} \leq P_{drive} \leq P_{driver\ max}$?
7. Choose your preferred dimming. Please refer to the section about naming of the drivers to know what the naming tells you about the possibilities.

Programming the output current

The Xitanium LED Xtreme drivers offer a full range of controls, enabling customizable luminaire design and performance. It is possible to control light output levels, preset dimming protocols and set system specifications in the factory and even in the complete installations.

This can be done with the Philips MultiOne configurator. The MultiOne configurator is an intuitive tool that unlocks the full potential of all programmable drivers from Philips, ensuring that the driver performance matches the needs of the lighting solution. It offers unprecedented flexibility, before, during and after the product installation.

Programming of new Xitanium LED Xtreme drivers can be done by both the DALI interface (when present) or via the SimpleSet. In the name of the driver you can see which interface is supported.

For more information on MultiOne go to the chapter Configuring Your Driver or visit:

www.philips.com/multione. This site contains detailed information on how to install the software and how to program the driver.

Connectors

Philips Xitanium LED Xtreme drivers are equipped with Wago push-in connectors. The mains, LineSwitch and Equipotential connectors are –depending on driver type – Wago type 804 or 250 while the DALI, 1-10V and LED output connectors are Wago type 805 or 250. All connectors accept stranded, solid core and crimped wires. More info about connectivity (wiring diagram, wire diameters, strip length) can be found in the driver datasheet.

In some scenarios two wires need to be connected to one connector terminal. In this case, the pairing has to be done outside the driver, resulting in only one wire going into the connector terminal. Two wires into one connector terminal are not supported.

The reliability of twin-wire ferrules (or wire end stop), accepting the wires intended to use, should be checked with the supplier of these ferrules.

Mains operating conditions

Xitanium LED Xtreme drivers are designed to withstand high and low mains voltages for a limited period of time.

This includes under- and overvoltage due to malfunction such as a loose neutral wire in the grid.

Low and high mains voltage

Xitanium LED Xtreme drivers are designed to be operated at mains under- and overvoltage per IEC requirements for performance and operation with respect to specified rated input voltage range.

The applicable lower limit for driver performance is lowest rated voltage – 8 % while –10 % applies to driver operation.”

The applicable upper limit for driver performance is highest rated voltage +6 % while +10 % applies to driver operation.

The actual limit values can be found in the driver datasheet.

For optimal luminaire performance it is always recommended to operate drivers within the specified voltage performance range.

Low mains voltage for dimming

Low mains voltage can be used for dimming in combination with the AmpDim feature. This feature in FULL Prog drivers can be programmed to regulate the output power when the input voltage drops below a programmed level.

Excessive low mains voltage (MainsGuard)

Previously, 220–240 VAC rated Xitanium FULL Prog LED Xtreme drivers would turn off the output in case of excessive low mains voltage. Depending on the exact driver type a shutdown would occur between 150 ... 180 VAC.

This shutdown functionality was intended to prevent overcurrent conditions in the mains grid. Without shutdown the driver input current would increase (up to 2.5 times) with decreasing mains voltage since the driver is designed to maintain full light output of the luminaire and thus output power. This would exacerbate the undervoltage condition further. Consequently, mains cables may be overloaded and fuses and/or MCBs may trip.


In order to prevent overcurrent conditions a shutdown mechanism had been implemented in the driver. However, the main disadvantage of this shutdown is loss of lighting.

Xitanium FULL Prog LED Xtreme drivers have now built in a new feature to protect luminaire and mains grid without loss of lighting or the occurrence of overcurrent conditions. This smart feature is called MainsGuard. Its function is to proportionally decrease output power as function of decreasing mains voltage and to keep doing so all the way down to a much lower mains voltage before the driver output eventually is shut down. A small hysteresis (5 ... 10 V) is added before the driver output becomes automatically active again once the mains voltage starts to increase.

A general graphical representation of MainsGuard can be seen in the illustration on the left while exact (fixed) values can be found in the MainsGuard graph in the driver datasheet.

Main benefits of MainsGuard are:

- Light will remain on, even at excessive low mains voltage
- Luminaire and grid are protected against undervoltage and overcurrent
- The maximum input current is limited to max 130%, preventing overcurrent in the mains grid and tripping of MCBs and/or fuses



MainsGuard feature Xitanium FULL Prog LED Xtreme drivers. Shown values are example values. Please refer to the driver datasheet for actual values.

All Xitanium FULL Prog LED Xtreme drivers made after week 36 of the year 2016 (label date code 1636) have the MainsGuard feature on-board.

Note: the voltage levels at which output power is reduced and the output is eventually shut down and re-activated are fixed and cannot be reprogrammed.

Excessive high mains voltage

An excessive high mains voltage will stress the driver and have an adverse effect on the lifetime (maximum of 264-320 V for a period of 48 hours, 321-350 V for a period of two hours). A loose neutral condition has to be avoided as this will reduce the lifetime dramatically.

Use of LineSwitch in three-phase power 230/400 V grids

The Xitanium LED Xtreme drivers allow supplying power from another phase than the one controlling the LineSwitch interface.

The LineSwitch input is designed to be controlled via the same phase as the input voltage but also a different phase can be used.

Power grids

Xitanium Xtreme LED drivers are suitable for direct connection to TN, TT and IT grids. An external luminaire-based fuse in the driver neutral connection is required in case both feeding phases are “hot”.


Note: certain restrictions apply for use in IT grids. Direct connection of Xitanium LED Xtreme drivers is only permitted in delta connection with a phase-to-phase voltage of 230 V. In case the drivers are connected in star connection in a 230V/400 V IT grid, the use of a separate 1:1 insulation transformer with sufficient power rating is required to power the drivers. The secondary output of the transformer needs to be connected to earth.

DC Emergency operation (DCemDim)

Depending on driver type, the driver is released in compliance with lamp control gear standard IEC 61347-2-13 Part J. for operation on a DC input voltage. As a result, the driver is suitable for emergency luminaires in compliance with IEC 60598-2-22, excluding high-risk task areas.

On selected drivers, the DC Emergency Dim feature named DCemDim is available. This feature allows a pre-defined dim level of the driver output to which the driver switches over automatically once connected to a DC input voltage.

The mains input of DC-rated drivers is not polarity-sensitive for DC input voltage and the driver is fully CISPR15 compliant when operated on a DC grid. Specific DC input voltage values can be found in the driver datasheet.



Graphical representation of inrush current

The use of an external, luminaire-based DC rated fuse with sufficient DC voltage rating and breaking capacity is required.

Suggested fuses (per each driver):

- 3.15A 400VDC 1.5kA BC, 5x20mm Slo-Blo® 477 series from Littelfuse
- 3.15A 250VDC 10kA BC, 5x20mm Fast 7008913,3.15 from Siba
- 3.15A 400VDC 30kA BC, 6.3x32mm gPV 7006526,3.15 from Siba

More on setting parameters of DCemDim can be found in the section for Controllability. Specific DC input requirements can be found in the driver datasheet.

Note: The allowed DC input voltage range accepted by the driver is stated in the driver datasheet. Values outside that range will have an adverse effect on the driver performance and reliability.

Inrush current

The term 'Inrush current' refers to the briefly occurring high input current which flows into the driver during the moment of connection to mains; see the illustration on the left. Typically, the amplitude is much greater than the steady-state input current.

The cumulative inrush current of a, given, combined number of drivers may cause Miniature Circuit Breakers (MCB) to trip. In such a case, either one or a combination of the following measures need to be taken to prevent nuisance tripping:

- 1: Replace existing MCB for a less sensitive type (e.g. exchange B type for C type) if in accordance with electrical national standards.
- 2: Distribute the group of drivers over multiple MCB groups or phases.
- 3: Power up drivers sequentially instead of simultaneously
- 4: Install external inrush-current limiting devices.
- 5: Install a zero crossing relay to power up the drivers.

Inrush parameters are driver-specific and can be found in the driver datasheet.

Note: The amplitude and pulse time of the inrush current are not in any way affected by the driver feature Adjustable Startup Time (AST, see chapter Control Features).

MCB type	Rating (A)	Relative number of LED drivers (%)
B	16	100 (stated in datasheet)
B	10	63
B	13	81
B	20	125
B	25	156
C	16	170
C	10	104
C	13	135
C	20	208
C	25	260
L, I	16	108
L, I	10	65
G, U, II	16	212
G, U, II	10	127
K, III	16	254
K, III	10	154

Conversion Table for maximum number of drivers on Different types of Miniature Circuit Breakers.

To Determine the Number of Drivers on a MCB

The maximum amount of drivers on a 16 A type B Miniature Circuit Breaker (MCB) is stated in the driver datasheet.

In the conversion table on the left that stated amount is used as reference (100%).

The maximum quantity of drivers on different types of MCB can be calculated by the reference (see driver's datasheet) x Relative number (last column).

Note: this conversion table does not apply to the following drivers:

Xi FP 35-70-110W 0.3-1.0A NLD 230V C150 sXt
 Xitanium FULL PROG 35-70-110W NLD C150 Xt
 Xitanium FULL PROG 35-70-110W NL1 C150 Xt

These drivers are equipped with the inrush-limiting feature called SoftStart. As a result, the rated steady-state driver input current limits the maximum amount of drivers that can be connected to an MCB. The maximum amount of these drivers per MCB can be found in the driver datasheet.

Example;

If datasheet states: max number on type B, 16 A = 20, then for type C, 13 A the value will be $20 \times 135\% = 27$

Notes:

1. Data is based on a average mains supply with an impedance of $400\text{ m}\Omega + 800\mu\text{H}$. This is in most cases equal to a prospective short circuit current of 500 Amps. Deviating mains impedance is of minor importance regarding the maximum amount of drivers per MCB.
2. Measurements will be verified in real installations; data is therefore subject to change.
3. In some cases the maximum number of drivers is not determined by the MCB but by the maximum electrical load of the installation.
4. Note that the maximum number of drivers is given when these are all switched on at the same time, e.g. by a central relay.
5. For multiple MCBs in one cabinet use the derating tool of the manufacturer of the MCB's for steady- state load. If the actual derating is unknown then it is recommended to use a steady-state current derating of 0.8 by default. No derating is needed in respect to inrush current as this is not part of the thermal properties of the cabinet.
6. The maximum number of drivers that can be connected to one 30 mA Residential Current Device (RCD) is typically 30.

Surge immunity

The Xitanium LED Xtreme drivers have increased differential-mode and common-mode surge immunity levels which by far surpass the limits as defined by IEC. The driver EQUI terminal must be connected to the metal parts of the luminaire and LED module heatsink in all cases (Class I: also to earth) to safeguard the specified immunity levels. Doing so will guarantee the specified driver surge immunity levels and will protect the LEDs against surge damage. Depending on the local conditions, additional protection against excessive high surge voltages may be required by adding an external Surge Protection Device in the luminaire and/or at installation level. The actual driver immunity level can differ per driver and can be found in the driver datasheet.

Note: the specified immunity levels apply with open 1-10V or DALI control interface. Reduced driver/system immunity may result when connecting external control systems. Please contact your local Philips representative for further specific technical support.

Touch current

The Xitanium LED Xtreme drivers are designed to meet touch current requirements for insulation class II applications per lighting control gear standard IEC 61347-1. The specified peak values can be found in the driver datasheet and refer to single-driver only level.

The insulation of the wiring to and from the drivers needs to be in compliance with IEC60598. Taking into account the double insulation of the driver between mains input and LED output, the (supplementary) output wiring insulation rating needs to be based on the maximum open-load voltage of the driver. See the driver datasheet for the specific value.

Note: In a luminaire, the cumulative touch current may be higher, since the LED module may introduce additional touch current. Precautions may be required on the luminaire level if multiple drivers are used in a single luminaire.

Note: do not leave the EQUI terminal open in order to lower the luminaire touch current. Impaired EMC performance and reduced surge immunity will result!

Electromagnetic compatibility (EMC)

Electromagnetic compatibility (EMC) is the ability of a device or system to operate satisfactorily in its electromagnetic environment without causing unacceptable interference in practical situations. Xitanium LED Xtreme drivers meet EMC requirements per CISPR15. This test is conducted with a reference setup that includes a driver and an LED load/heat sink combination mounted on a metal plate.

Note: the driver EQUI terminal must be connected to the luminaire chassis (Class I and II) as well as to Protective Earth (Class I) for optimal EMC performance. Doing so for Class II luminaires/systems is in safety compliance with IEC61347-1, IEC60598-1 and IEC61140 regarding the relation between the driver EQUI terminal and live parts with respect to:


- Maximum allowable touch current
- Minimum required insulation resistance
- Minimum required creepage distances & clearances
- Minimum required electric strength"

Note: The driver EQUI terminal does not have a safety function.


Improvement in EMC Performance

The following practical precautions need to be taken into account in a lighting system for optimal EMC performance:


- Minimize the differential mode loop area of the lamp wires going from the driver to the light source by keeping the wires close together (bundling). This will minimize the magnetic field and reduce the radiated EMI.




- Minimize the common mode parasitic capacitance of the output wiring + light source to earth by keeping the length of the wires between driver and LED module as short as possible. Keep the length of the incoming mains wire inside the luminaire as short as possible.
- Keep mains and control wires (DALI, 0–10 V) separated from the output wires. Do not bundle or cross the wires.



- Do not route any wiring over and/or along the driver enclosure to avoid any coupling/crosstalk with internal components of the driver



- Ground the lighting system chassis and other internal metal parts (mounting plate, heatsink) to protective earth (class I luminaires). Do not keep large metal parts electrically insulated from the driver equipotential connector. **Always** connect the driver equipotential terminal (EQUI) and use equipotential bonding wires for all large unconnected metal luminaire parts like luminaire housing, driver mounting plate, reflector, heatsink etc. Keep the equipotential wires as short as possible to maximize their effectiveness and use, as much as possible, large metal areas (chassis, mounting plates, brackets) for earthing purposes instead. Establish a reliable electrical connection by using a toothed washer and screw(s) fastened with adequate torque.



Adhering to these rules will help in EMC compliance. For further questions and/or design-in support please contact your local Philips representative.

Remote mounting and EMC

Remote mounting of Xitanium LED Xtreme drivers is allowed as long as the additional summarized voltage drop as function of output current along the LED + and LED – wires is accounted for.

Philips has successfully performed CISPR15 compliance EMC tests on systems with a standard output cable length of 60cm as reference. For longer CISPR15-compliant cable lengths please check the driver datasheet for the maximum specified length.


Note: the length of the two NTC wires between driver and LED module is not allowed to exceed 60cm due to EMC and noise immunity reasons.

Electrical insulation

Driver insulation classifications between the several inputs and output can be found in the driver datasheet.

The insulation between the EQUI terminal and the mains input is classified as double for all Xitanium LED Xtreme drivers.

Configure Your Driver



Introduction

The Xitanium LED Xtreme drivers offer a full range of controls, enabling customizable luminaire design and performance. It is possible to control light output levels, preset dimming protocols and set system specifications in the factory and even in the complete installations. This can be done with the Philips MultiOne configurator. The MultiOne configurator is an intuitive tool that unlocks the full potential of all programmable drivers from Philips, ensuring that the driver performance matches the needs of the lighting solution. It offers unprecedented flexibility, before, during and after the product installation. Programming of new Xitanium LED Xtreme drivers can be done by both the DALI interface (when present) or via the SimpleSet. In the name of the driver you can see which interface is supported.

For more information on:

- MultiOne- installation – software and programming: www.philips.com/multione
- Driver – feature set and default settings: datasheets www.philips.com/oem
- Specific features: design in guide of that driver www.philips.com/oem

This chapter describes the way drivers can be configured using the MultiOne Configurator.

Please check the datasheet of the driver on www.philips.com/technology to verify if the selected driver supports specific configurability.

MultiOne characteristics

The characteristics of the MultiOne configurator are:

- One tool for all Philips configurable drivers: Xitanium LED Indoor and Outdoor drivers; HF-R Indoor fluorescent gear; DynaVision Xtreme HID electronic gear...
- Future proof by design: modular approach, very scalable and backwards compatible.
- Provides access to all features built in the driver.
- Tool combines configuration with debugging.
- Settings of the drivers can be changed any point in the product lifecycle.
- Settings of the drivers can be changed at any point in the product lifecycle (if allowed– see OWP feature).

Basis blocks

This configurator consists of:

1. Philips MultiOne Interface tool.
2. USB cable (connection to PC or laptop).
3. Philips MultiOne Software.

Philips MultiOne Interface tool

There are different versions of MultiOne interface tooling depending on the type of communication:

1. LCN8600/00 MultiOne Interface USB2DALI

The interface that can be used with the MultiOne PC software to commission, configure, diagnose drivers via the DALI interface.

2. LCN9610 and LCN9620 SimpleSet interface

The interface that can be used with the MultiOne PC software to configure drivers wirelessly using SimpleSet technology.

3. More interfaces are coming up ...

Note: SimpleSet

The programming of the drivers with SimpleSet must be done while disconnected from mains.

When powering up the driver – during first use after configuration – apply the specified mains voltage for at least 1 second.

If the applied mains voltage is below the specified minimum value of the driver and/or the duration is less than 1 second then the desired configuration changes may not become effective.

Note: DALI

Only for Xi FP 35/70/110W NLD C150 sXt/Xt drivers:
After reconfiguration with DALI, an additional power cycle of the driver (off-on for at least 5 seconds) is required before changes become effective.



MultiOne Interface DALI LCN8600



MultiOne SimpleSet interface LCN9610



MultiOne SimpleSet interface LCN9620

Philips MultiOne Interface tool

When ordering the MultiOne Interface, the correct USB cable will be supplied with the interface tool.

Each interface tool has its own cable.

Check if USB ports of the PC are able to power the interfaces .

When ordering the MultiOne Interface, the correct USB cable will be supplied with the interface tool.

Philips MultiOne Software

There are 2 versions of MultiOne Software depending on functionality and location:

1. MultiOne Engineering

Especially developed to access all functionality of the driver; to configure, diagnose and prepare the configuration file for the production environment. Includes also:

- DALI commands, scheduler.
- SimpleSet .

2. MultiOne Workflow

Developed to configure all devices or subassemblies in the production environment or field in a simple and quick way. Workflow exists of 2 packages:

- Workflow GUI (direct use)
- CommandLine (integration in test bench, robot, automation,...)



Get your software (free downloadable) or check if you have the latest version www.philips.com/multione.

System requirements

The MultiOne configurator must be connected to a system with these minimum system requirements:

- Windows PC or Laptop.
- Microsoft Windows 7, 8.0, 8.1.
- USB 2.0 or 3.0 ports (minimum two free ports).
- Min 45 MB of free disk space.

Note: The software may work well with Windows 10 but possible Windows bugs can affect the good functionality of the MultiOne software. USB ports of the newest PCs and laptops may have the problem of not delivering enough power to the interfaces. Please check this before supplying new systems.



Getting Started

Connect the USB cable of the MultiOne Configurator between the PC and the configuration tool.

To install the software, launch the installation file for the latest version and follow the instructions on your screen. The installation wizard will guide through the process of installing the software and will ask where the software needs to be installed, if a shortcut is needed on the desktop and a new program is also created in the Start Menu.

A User Software key is required to install MultiOne Engineering (available at no charge).

This key can be requested here:

www.lighting.philips.co.uk/oem-emea/products/philips-multione-configurator/multione-configurator-form.html

More information on how to program a driver, can be found in getting started and the instruction manual on the website, www.philips.com/multione.

MultiOne System



Settings

The Xitanium LED Xtreme drivers have a fixed set of features and factory settings when supplied. The set of features is defined in the datasheet of the driver. The default settings of the driver can be found in the driver's datasheet in the download section on www.philips.com/technology.

More information of using Multione

On our up to date website www.philips.com/multione you can find:

- All interface tools with order codes.
- Software free to download.
- All manuals; getting started; SimpleSet explained; instructions manuals.

Request User software key :

- www.lighting.philips.co.uk/oem-emea/products/philips-multione-configurator/multione-configurator-form.html

Control features


How to program the features is explained in the User Manual guide of MultiOne; see the Help function of MultiOne or download it from www.philips.com/multione. In this chapter the features will be explained in more detail.

Adjustable output current (AOC)

AOC limits the driver output current to match the application requirement.

The limited output current is then dimmable over the full user controllable dim range; the AOC level [mA] being the 100% light level.

The default AOC value can be found in the driver datasheet.




Adjustable Light Output (ALO)

Applicable to : Xi FP drivers only.


ALO limits the light output of the driver to match the application requirement. The limited light output is then dimmable over the full user controllable dim range; the ALO level [%] being the 100% light level. Setting an ALO min level prevents the light from dropping below the set level during dimming conditions. This is a useful feature if a minimum light level needs to be maintained under all conditions.

There are 2 versions depending on driver type:

- ALO




- ALO and ALO min




Check the driver datasheet to verify which ALO type is available.


This feature is disabled by default.



MTP



CLO



CLO LITE

LED Module Temperature Protection (MTP)

Applicable to: Xi FP drivers only

MTP is the method in which a thermal sensor (NTC resistor) implemented on the LED module is sensed by the driver, which will cut back output current when a predefined (temperature) limit is exceeded in order to protect the LED module from thermal overstress.

This feature is enabled by default.

The driver accommodates for three NTC resistor choices. See the chapter Thermal Design-In for more details on NTC type.

Constant Light Output (CLO, CLO LITE)

CLO: Applicable to Xi FP drivers only

CLO LITE: applicable to Xi LP drivers only

CLO will gradually increase the light level over time from an initial lower light level up to 100% light level in order to compensate for LED module depreciation over life. It can also serve as a means to reduce energy consumption.

CLO settings includes enabling disabling and redefining the CLO dimming curve. Changes are effective immediately.

The allowed range for CLO is 0-100% with 1% increments (note that 0% results in the LEDs being switched off).

CLO LITE can be configured by setting a start point (at 0 hours only) and an end point. The light level between these point will linearly increase.

The CLO/CLO LITE feature is disabled by default.

End of Life (EOL)

Applicable to: Xi FP drivers only.

EOL is providing a visual notification to a customer that the LED module has reached the end of manufacturer-specified life and that replacement is recommended.

Once active, an indication is given at each power-up of the driver, after which the LEDs will flash for 2.5 seconds before normal operation is continued.

This feature is disabled by default.

☒ Enable

49,000 h

Adjustable Start up Time (AST)

Applicable to: Xi FP drivers only.

AST enables gradual increase of light level at power-up of the driver, ensuring a smooth and comfortable transition from daytime to evening illumination.

AST can be programmed to a value between 0 s and 30s, in increments of 1ms.

Note: this feature does not in any way influence the driver inrush current at mains turn-on.

This feature is disabled by default.

☒ Enable

0 ms

Light Source Operating Hours (LSO)

Light Source Operating: set a specific time or reset the operating hours, e.g. after replacing a LED module or driver with another (new) one.

When CLO resp. CLO LITE is enabled it is recommended to set the correct light source age.

This feature is disabled by default.

☒ Enable


0 ms

DC emergency dimming operation (DCemDIM)

Applicable to: selected Xi FP drivers only.

The Xitanium FULL Prog drivers are equipped with a auto-detect DC voltage feature. As soon as a DC input voltage is detected by these drivers, it will automatically set the output current to a predefined configurable emergency dim level. This feature is enabled by default.

Note: during DC operation the output current cannot be set higher than 60 % of the programmed AOC value applicable during AC operation and the driver will ignore all DALI commands unless the optional checkbox “Allow dimming” in the DC Emergency tab is selected.



☒ Enable
☐ Allow dimming

Emergency level: 241 [=70%]

Control Input 1-10 V

Applicable to: Xi LP S1 drivers only.

This is the traditional way of dimming a driver, based on dimming voltage. The driver dimming interface sources a current of 150µA as a current-controlled voltage source. Note that the 100% light level is determined by the max output current level. The minimum output current that can be supplied by the driver is specified in the datasheet. The 1-10 V interface is enabled by default.

1-10 V dimming provides a way to control the output by means of an analog current-controlled voltage source. The interface is designed to comply with IEC60929 Annex ‘Control by DC Voltage’ (1-10 V). The applied 1-10 V controller should be of the two-quadrant type and be able to sink the cumulative current sourced by the dimming interfaces of all connected drivers.

Depending on driver type, there are multiple linear dimming curves available that can be selected:

0-10 V / 1-10 V curve (set by default) :

- minimum light output at 1 V, maximum light output at 8 V and above
- minimum dim level can be set at 10 % and up in 1% increments

1-9V curve:

- minimum light output at 1 V, maximum light output at 9 V and above
- minimum dim level has a fixed value of 10 % and cannot be modified

Note: the driver output cannot be turned off by pulling down the 1-10 V interface to 0V. Between 0 and 1 V, the minimum light output will be maintained.

DALI

Applicable to: Xi FP drivers only.

- Digital Addressable Lighting Interface, or DALI, is a digital communication protocol popular in the lighting industry. It is an IEC standard and there are many control devices from Philips and other manufacturers that communicate using DALI. The voltage across DALI wires is typically 16 V (refer IEC specification for details) and it is polarity insensitive. Using DALI, it is possible to send dimming commands.
- (1-254 levels), set fade rates and fade times, query driver or LED status, etc. The Xitanium LED drivers also respond to LED-specific DALI commands, for example:
- Query if the LED module is short circuit or open circuit.

For more information on DALI, refer to the IEC specification for DALI protocol.

- IEC 62386: 102 – General requirements – Control gear
- IEC 62386: 207 – Particular requirements for control gear
- LED modules.

Note: Xitanium LED Xtreme FULL Prog drivers are by default configured to have LineSwitch interface as the primary interface. On reception of a DALI frame, the driver will switch over to DALI mode and all other interfaces will be ignored until the next mains cycle. In order to obtain full DALI compatibility in DALI-only applications it is highly recommended to disable LineSwitch through the MultiOne configurator.

LineSwitch

Applicable to: Xi FP and Xi LP SL drivers only.

The LineSwitch feature requires the use of an extra mains pilot line. This is a one-step dimming solution which enables dimming of groups of luminaires to a predefined level with only a simple switch controlled by a timer, presence detector etc.

Dimming to the desired level can be achieved by either applying or disconnecting mains voltage to the LineSwitch driver input.

Connecting mains voltage to the LineSwitch input will lead to a 'High' level of LineSwitch. A 'Low' level of LineSwitch is obtained through disconnecting the LineSwitch input from mains voltage.

Xitanium LED Xtreme drivers are by default programmed with LineSwitch enabled, where the 'High' level is defined as active (due to the light level being lower than the level defined in the disconnected 'Low' state). All parameters of LineSwitch including ramp-up and fade-down times can be programmed via the MultiOne configurator.

Note: LineSwitch is able to 'override' the Dynadimmer/ Dynadimmer LITE profile to temporarily set the light output to 100% (only), e.g. in case of emergencies.

☐ Enable

High V level: 100 %

Low V level: 50 %

Fade on time: 0 %

Switch off delay time: 0 %

Fade off time: 0 %

Note 1: Low V = 0 V on the mains; High V = 208-277 V on the mains.

Note 2: When Dynadimmer is scheduled, LineSwitch can not be used standalone. It can only be used to override Dynadimmer

Note: For proper functionality of the LineSwitch function the length of the LineSwitch pilot line from one luminaire to the next has a restriction. The restriction is given in the below formula:


$$\frac{(\sum L)}{\#D} \leq 56$$

In this formula:


L= length of the cable from cabinet to the LED driver in m

#D= number of connected drivers

Example:




$$\frac{(\sum 6+4(36)+86+46)}{7} 43 \leq 56 \rightarrow \text{OK}$$



AmpDim

Parameter	Min	Max	Increments
Start Voltage	170 V	240 V	1 V
Stop Voltage	150 V	220 V	1 V
Start Percent	30%	100%	1%
Stop Percent	30%	100%	1%
Start Voltage - Stop Voltage	20 V	100 V	



In this example the following assumptions have been made:

1. Luminaires are used in a TN or TT power grid.
2. The parasitic capacitance in the mains cabling between the floating pilot line and the live phase is 100pF/meter.
3. No other loads are connected between the pilot line and other phases.
4. Other loads between the pilot line and neutral can be accepted. In almost all cases this will increase the maximum acceptable cable length.

AmpDim

Applicable to: selected Xi FP drivers only.

Historically mains dimming was used on magnetic ballasts to dim conventional lamps. By lowering the mains voltage, a proportionate reduction in light output was achieved. Until now electronic ballasts were not able to replicate this function. AmpDim enables cabinet based dimming without the need for additional control wires or infrastructure changes.

A cabinet controller signals to the driver to lower the light output via a reduction in the amplitude of the mains voltage. The intelligence embedded in the LED driver allows for a pre-programming of multiple dimming levels based on the amplitude of the mains voltage.


The total range of AmpDim is 170 V – 250 V. The range can be customized via the programming interface. It is possible to set the Start Voltage, Start Percent, Stop Voltage, and Stop Percent. The figure on the left shows an example of the AmpDim programming interface.

Programming note


- AmpDim first needs to be selected first in the Dimming Interface selection for activation. This feature is disabled by default.
- There needs to be a minimum of 20 V difference between Start and Stop Voltage settings when programming the driver. Please refer to the AmpDim parametric table for complete parameters.

Application note

- The AmpDim feature only supports dimming methods based on amplitude dimming. Phase modulation is not supported.
- Leading-edge and trailing-edge dimming is not supported by Xitanium LED Xtreme drivers.



Dynadimmer



Dynadimmer LITE

Dynadimmer

Dynadimmer and Dynadimmer LITE

Dynadimmer: applicable to Xi FP drivers

Dynadimmer LITE: applicable to Xi LP drivers.

The Integrated Dynadimmer is a dimming control developed by Philips that enables a simple, pre-programmed multistep dimming. Main function is energy reduction by reducing light (Xi FP only: turn off also) during the night when it is not required to have full light output. This function is integrated in the features of Xitanium LED Xtreme drivers.

During Dynadimmer operation the other dimming interface functionalities –except DALI– will be ignored.

Dynadimmer can be overruled (“Override”) by DALI to change over to a different light level. Override can also be accomplished by the use of LineSwitch (change over to full light output only).

Override of the Dynadimmer by DALI is implemented by default: as soon as the driver detects a DALI frame it will change over from Dynadimmer mode to DALI mode and remain in DALI mode until the next mains power cycle.

LineSwitch also offers the possibility to overrule the Dynadimmer by applying mains voltage to the LineSwitch input (‘high’ input), albeit to change over to full light output only. As soon as the LineSwitch input is changed back to ‘low’, the Dynadimmer will resume operation.

These kinds of override do not interfere with the Dynadimmer synchronization algorithm.

The Dynadimmer LITE can be overruled in two ways to change over to full light output (only): either by LineSwitch as described above or by the 1-10 V interface.

Override by the 1-10 V interface is possible by shorting the + and – terminals of 1-10 V interface by means of an external relay contact or by pulling it down below 2 V by an external controller. As soon as the short is removed or when the input is raised above 3.2V, the Dynadimmer will resume operation.

These kinds of override do not interfere with the with the Dynadimmer LITE synchronization algorithm.

Group of features - OEM protection

OEM Write Protection	
Summary	Set the OEM Write Protection password
Dynadimmer	<input type="checkbox"/> Enable
LineSwitch	New password: <input type="text"/> <input type="text"/> <input type="text"/> <input type="text"/>
AmpDim	Verify password: <input type="text"/> <input type="text"/> <input type="text"/> <input type="text"/>
ALO	The password must contain 4 numbers (0-255).
AOC	
MTP	
CLO	
Startup Time	
EOL	
DC Emergency	
OWP	

OEM Write Protection (OWP)

OWP can be used by the OEM to protect the change of setting of the Philips programmable driver. Philips Drivers equipped with the feature OWP will show this in their feature list, if read out via the MultiOne Engineering Software.

The feature OWP defines a password that will be set in the driver so the data of OEM Write-protected features can only be written to the driver by providing this configured password.

Depending on the type of driver OEM can protect

- a set of features (fixed)
- a selection of individual features (free selection)

To know which features are locked you see a small lock symbol on each feature while trying to write the driver.

How to program this feature is described in the user manual of MultiOne Engineering at www.philips.com/multione.

The password is needed to change the protected features of this driver. Without the password these features are not changeable.

Encrypted in the feature file, the password can be easy programmed in production via the MultiOne workflow software. New drivers or replacement drivers can be programmed on this way. Already programmed drivers with password are protected and will give an error. They can only be changed using the correct password.

It is important for the OEM to set up a password management system, keeping feature file and password together in the BoM of the luminaire. The password management is under the responsibility of the OEM who sets it.

In case of losing the password, the customer can take contact with the local sales department to discuss a possible solution.

Individual features - OEM protection

OEM Write Protection	
Summary	OEM Write Protected features
DALI PSU	<input type="checkbox"/> (De)select all
ALO	<input type="checkbox"/> DALI PSU
AOC	<input type="checkbox"/> ALO
OWP	<input checked="" type="checkbox"/> ALO Min
ECO FactoryLink	<input checked="" type="checkbox"/> AOC
	Set the OEM Write Protection password
	New password: <input type="text"/> <input type="text"/> <input type="text"/> <input type="text"/>
	Verify password: <input type="text"/> <input type="text"/> <input type="text"/> <input type="text"/>
	The password must contain 4 numbers (0-255).

Compliance and approval

Please contact your local Philips sales representative for all certificates, approvals and compliancy verification with specific national rules and regulations.

Disclaimer

Note that the information provided in this document is subject to change.

This document is not an official testing certificate and cannot be used or construed as a document authorizing or otherwise supporting an official release of a luminaire. The user of this document remains at all times liable and responsible for any and all required testing and approbation prior to the manufacture and sale of any luminaire.

The recommendations and other advice contained in this document, are provided solely for informational purposes for internal evaluation by the user of this document.

Philips Lighting does not make and hereby expressly disclaims any warranties or assurances whatsoever as to the accuracy, completeness, reliability, content and/or quality of any recommendations and other advice contained in this document, whether express or implied including, without limitation, any warranties of satisfactory quality, fitness for a particular purpose or non-infringement. Philips Lighting has not investigated, and is under no obligation or duty to investigate, whether the recommendations and other advice contained in this document are, or may be, in conflict with existing patents or any other intellectual property rights. The recommendations and other advice contained herein are provided by Philips Lighting on an “as is” basis, at the user’s sole risk and expense.

Specifically mentioned products, materials and/or tools from third parties are only indicative and reference to these products, materials and/or tools does not necessarily mean they are endorsed by Philips Lighting. Philips Lighting gives no warranties regarding these and assumes no legal liability or responsibility for any loss or damage resulting from the use of the information thereto given here.

