





# Datasheet

# Xitanium LED drivers - linear HV non-isolated

Xitanium 60W 0.08-0.35A 300V S 230V

#### **Enabling future-proof LED technology**

Xitanium LED drivers are designed to operate LED solutions for general lighting applications such as linear lighting, as well as down lighting and spot/accent lighting.

Reliability is enhanced by specific features that protect the connected LED module, e.g. hot wiring, reduced ripple current and thermal de-rating. Most drivers feature central DC operation.

In the coming years LEDs will continue to increase in efficiency, creating generation and complexity challenges for OEMs. With Xitanium LED drivers, flexibility in luminaire design is assured thanks to an adjustable output current. Application-oriented operating windows offer the flexibility required to provide the stable lumen output and light quality levels that lighting specifiers and architects demand.

#### Benefits

- High reliability underpinned by 5 year warranty
- Future-proof flexibility application-oriented operating windows enable LED generation and complexity management
- Compatibility adjustable output current enables operation of various LED solutions from different manufacturers or OEM own designs
- Flicker and noise free dimming with all Touch and DALI LED drivers due to amplitude dimming (AM)

#### Feature

- Up to 95% efficiency, lowest cost and smallest dimensions
- Operating windows output current can be adjusted via the Philips MultiOne configurator (TD drivers) or with a resistor outside the driver
- Reduced ripple current and thermal de-rating for increased reliability
- Multiple versions DALI dimmable & programmable,
  1-10V dimmable, and fixed-output;
- All T5 form factors but various lengths
- Longer life time (100khrs), improved surge and burst (4kV) and Tambient (-40°C to +60°C) specifications

#### **Application**

- 17W, 36W and 75W LED drivers for office applications
- 110W and 150W LED drivers for industry, warehouses, public areas, distribution centers and shopping malls

### Electrical input data

Specification item	Value	Unit	Condition
Nominal input voltage	220240	V <sub>ac</sub>	performance range
Nominal input frequency	5060	Hz	
Nominal input current	0.3	Α	@230V @ full load
Input voltage	230	V <sub>ac</sub>	
Nominal input power	66	w	@230V @ full load
Power factor	≥ 0.9		@ full load. See graph.
Total harmonic distortion	≤ 20	%	@ full load. See graph.
Efficiency	92.5	%	@230V @ full load
Nominal input voltage DC	186250	V <sub>dc</sub>	
Nominal input current DC	0.3	Α	Input voltage 230 V <sub>dc</sub> , full load
Input voltage AC	202254	V <sub>ac</sub>	Operational range
Input frequency AC	47.563	Hz	Maximum permissible range
Input voltage DC	186250	V <sub>dc</sub>	Maximum permissible range
Isolation Input to Output	No		

### **Electrical output data**

Specification item	Value	Unit	Condition
Regulation method	Constant Current		
Output voltage	100300	V <sub>dc</sub>	
Output voltage max.	330	V	Peak voltage at open load
Output current	0.080.35	A	Full output current setting
Output current tolerance	± 5	%	
Output current ripple LF	≤ 4	%	Ripple = peak / average
Output current ripple HF	≤ 4	%	
Output power	1760	W	Full output

# Electrical data controls input

Specification item	Value	Unit	Condition
Control method	Fixed		

## Logistical data

Specification item	Value
Product name	Xitanium 60W 0.08-0.35A 300V S 230V
Order code	871869655587300
Logistic code 12NC	9290 015 06506
EAN3	8718696555880
Pieces per box	24


### Wiring & Connections

Specification item	Value	Unit	Condition
Input wire cross-section	0.51.5	mm <sup>2</sup>	WAGO744, solid wire
	1620	AWG	WAGO744, solid wire
Input wire strip length	89	mm	
Output wire cross-section	0.51.5	mm <sup>2</sup>	WAGO744, solid wire
	1620	AWG	WAGO744, solid wire
Output wire strip length	89	mm	
Maximum cable length	1500	mm	Total length of wiring including LED module, one way



# Dimensions and weight

Specification item	Value	Unit	Condition
Length (A1)	280	mm	
Width (B1)	30	mm	
Height (C1)	21	mm	
Fixing hole diameter (D1)	4.1	mm	
Fixing hole distance (A2)	270	mm	
Weight	180	gram	



# Operational temperatures and humidity


Specification item	Value	Unit	Condition
Ambient temperature	-25+50	°C	Higher ambient temperature allowed as long as Tcase-max is not
			exceeded.
Tcase-max	75	°C	Maximum temperature measured at T <sub>case</sub> -point
Tcase-life	75	°C	Measured at T <sub>case</sub> -point
Maximum housing temperature	110	°C	In case of a failure
Relative humidity	1090	%	Non-condensing

### Storage temperature and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-25+85	°C	
Relative humidity	595	%	Non-condensing

### Lifetime

Specification item	Value	Unit	Condition
Driver lifetime	50,000	hours	Measured temperature at $T_{case}$ -point is $T_{case}$ -life.
			Maximum failures = 10%



### **Programmable features**

Specification item	Value	Remark	Condition
Set output current (AOC)	SimpleSet	See Design-in guide.	Default output current: ≤ 80 mA
LED module temperature derating (MTP)	No		
Constant Lumen Over Lifetime (CLO)	No		
DC emergency dimming (DCemDIM)	No		
Corridor mode	No		
Energy metering	No		
Diagnostics	No		

#### **Features**


Specification item	Value	Remark	Condition
Open load protection	Yes		Automatic recovering
Short circuit protection	Yes		Automatic recovering
Over power protection	Yes		Automatic recovering
Hot wiring	No		
Suitable for fixtures with protection class	I		per IEC60598

### **Certificates and standards**

Specification item	Value
Approval marks	CCC / CE / ENEC
Ingress Protection classification	20

### Inrush current

Specification item	Value	Unit	Condition
Inrush current I <sub>peak</sub>	17.8	A	Input voltage 230V
Inrush current T <sub>width</sub>	282	μs	Input voltage 230V, measured at 50% I <sub>peak</sub>
Drivers / MCB 16A type B	≤ 24	pcs	



MCB	Rating	Relative number of LED drivers
В	10A	63%
В	13A	81%
В	16A	100% (stated in datasheet)
В	20A	125%
В	25A	156%
С	10A	104%
С	13A	135%
С	16A	170%
С	20A	208%
С	25A	260%

### **Driver touch current**


Specification item	Value	Unit	Condition
Typical touch current	0.5	mA peak	Acc. IEC61347-1. LED module contribution not included

### Surge immunity


Specification item	Value	Unit	Condition
Mains surge immunity (diff. mode)	1	kV	Acc. IEC61000-4-5. 2 Ohm, 1.2/50us, 8/20us
Mains surge immunity (comm. mode)	2	kV	Acc. IEC61000-4-5. 12 Ohm, 1.2/50us, 8/20us

### Graphs


# Operating window




### Power factor versus output power



#### Efficiency versus output power



### **THD** versus output power





©2016 Philips Lighting B.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights. Data subject to change.

Date of release: March 31, 2016