

PHILIPS

Fortimo

LED

Fortimo LED Strip 2ft LF
9xx LV6



Datasheet

The Fortimo LED Strip is a uniquely wide portfolio which can be used in all kind of linear indoor luminaire types. Its form factor makes it easy to design-in and handle in production as it complies to Zhaga standards. Due to the availability from 0.25ft up to 5ft lengths only one product family is needed to cover a wide range of needs.

Key features and benefits

- Typical module efficiency of 186 lm/W (at 4000K CRI80)
- CRI90 High Efficiency typical performance of 174 lm/W (at 4000K CRI90)
- Long life-time: >72,000 hours
- Excellent color consistency of 3 SDCM
- Two lumen packages per length available: LF (650 lm/ft) and MF (1100 lm/ft)
- Wide range of CCTs available: 2700K, 3000K, 3500K, 4000K, 5000K and 6500K
- Available in High Voltage (HV) and Low Voltage (LV)
- Options in front connector (FC) or back connector (BC)
- Small LED module width of only 20mm
- Available lengths: 0.25ft / 0.5ft / 1ft / 2ft / 4ft (1120mm) / 4ft extended (1150mm) / 5ft (1400mm) / 5ft extended 1450mm)
- Wide temperature (Tc) range -40°C to +80°C
- Five year system warranty

March 2023



Ordering data

Commercial product name	EOC	12NC	EPREL registration #	Box quantity
Fortimo LED Strip 2ft LF 930 FC LV6	8719514 488885 00	9290 029 44406	1413430	110
Fortimo LED Strip 2ft LF 940 FC LV6	8719514 488908 00	9290 029 44506	1413431	110

Drive currents

Parameter	Nominal*	Life**	Max***	Unit
Fortimo LED Strip 2ft LF 9xx LV6	192	300	480	mA

Module temperatures

Parameter	Nominal*	Life**	Max***	Unit
T _c (case temperature at T _c point)	45	75	85	°C

* Nominal value at which typical performance is specified

** Value at which life time is specified

*** Maximum value for safe operation, do not operate above this value

Optical characteristics - table per color (CCT)


Fortimo LED Strip 2ft LF 930 FC LV6

Parameter	Min	Typ	Max	Unit
Luminous flux	1190	1214	1330	lm
Efficacy	156	162	188	lm/W
Correlated color temperature (CCT)		3000		K
Color coordinates (CIEx, CIEy)		(0.436, 0.402)		-
Color consistency			3	SDCM
CRI	90			
R9	50			
Photometric code		930/339		
Photobiological safety			RG1 unlimited	



Measurement precision $\pm 5\%$ for the flux data and $\pm 6\%$ for the efficacy data. Measurement precision for color coordinates ± 0.005 . Measurement precision for CRI ± 1.5 .

Operation point	930	lm	lm/W
80% I-nom 154mA	Tc 25 °C	1006	172
	Tc-nom 45 °C	983	166
	Tc-max 85 °C	924	154
I-nom 192mA	Tc 25 °C	1243	167
	Tc-nom 45 °C	1214	162
	Tc-max 85 °C	1141	150
I-max 480mA	Tc 25 °C	2903	143
	Tc-nom 45 °C	2833	138
	Tc-max 85 °C	2657	128




Fortimo LED Strip 2ft LF 940 FC LV6

Parameter	Min	Typ	Max	Unit
Luminous flux	1260	1300	1420	lm
Efficacy	165	174	201	lm/W
Correlated color temperature (CCT)		4000		K
Color coordinates (CIEx, CIEy)		(0.382, 0.378)		-
Color consistency			3	SDCM
CRI	90			
R9	50			
Photometric code		940/339		
Photobiological safety			RG1 unlimited	



Measurement precision $\pm 5\%$ for the flux data and $\pm 6\%$ for the efficacy data. Measurement precision for color coordinates ± 0.005 . Measurement precision for CRI ± 1.5 .

Operation point	940	lm	lm/W
80% I-nom 154mA	Tc 25 °C	1080	184
	Tc-nom 45 °C	1052	178
	Tc-max 85 °C	985	164
I-nom 192mA	Tc 25 °C	1334	180
	Tc-nom 45 °C	1300	174
	Tc-max 85 °C	1217	160
I-max 480mA	Tc 25 °C	3117	153
	Tc-nom 45 °C	3035	148
	Tc-max 85 °C	2836	137



Electrical characteristics


Parameter	Min	Typ	Max	Unit
Forward voltage	36.9	39.0	39.7	V
Power consumption	7.1	7.5	7.6	W = kWh/1000h
Number of modules per chain			2	

Measurement precision for Vf +/- 3%. Measurement precision for power +/- 3.3%

Tuning information


Flux and efficacy versus current (at Tc nominal)

I [mA]	Flux [%]	Efficacy [%]
300	152	94
246	126	97
192	100	100
154	81	103
96	52	107



Flux and efficacy versus temperature at Tc (at I nominal)

Tc [°C]	Flux [%]	Efficacy [%]
85	94	93
45	100	100
25	102	103
0	105	107




Lumen maintenance

Operation point	Lumen maintenance x 1000 hours	L70			L80			L90		
		B50	B20	B10	B50	B20	B10	B50	B20	B10
80% Inom=154mA	Tc=25°C	>100	>100	>100	>100	>100	>100	>50	>50	>50
	Tc_nom=45°C	>100	>100	>100	>100	>100	97	>50	49	48
	Tc_life=75°C	>100	>100	>100	79	76	75	37	36	35
Inom=192mA	Tc=25°C	>100	>100	>100	>100	>100	>100	>50	>50	>50
	Tc_nom=45°C	>100	>100	>100	>100	100	98	50	47	46
	Tc_life=75°C	>100	>100	>100	75	73	72	35	34	34
Ilife=300mA	Tc=25°C	>69	>69	>69	>69	>69	>69	>32	>32	>32
	Tc_nom=45°C	>69	>69	>69	>69	>69	>69	>32	>32	>32
	Tc_life=75°C	>69	>69	>69	69	67	66	32	31	31

Lifetime

Parameter	Value	Unit
M70F50 nominal	>100000	hours
M70F50 life	>69000	hours

Performance Window




Wiring

Specification item	Value	Unit	Condition
Input wire cross-section	0.25...0.75	mm ²	solid wire
	18...24	AWG	solid wire
Input wire strip length	7.5...8.5	mm	
Input wire cross-section	0.33...0.5	mm ²	stranded wire
	20...22	AWG	stranded wire
Input wire strip length	7.5...8.5	mm	

Mechanical characteristics

Parameter	Min	Typ	Max	Unit
Length	558.9	559.2	559.5	mm
Width	19.8	20	20.6	mm
Height PCB	1.45	1.6	1.75	mm
Height Total		4.3		mm
Product mass		34.5		gram



Absolute ratings

Parameter	Min	Max	Unit
Current through the LED module (I-max)		480	mA
Case temperature (Tc-max)		85	°C
ESD (direct contact)	8		kV
Working voltage		350	V _{dc}

Application information

Certificates and Standards

CE
ENEC
ENEC+
cULus

Environmental

RoHS/REACH

Application

Dimming	Yes
---------	-----



© 2023 Signify Holding, IBRS 10461, 5600VB, NL. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

www.philips.com/oem

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.
UK importer address: Signify Commercial UK Limited, 3 Guildford Business Park, GU2 8XG

02/03/2023