

PHILIPS

Fortimo

LED

Fortimo LED Strip 2ft
6000lm HV6



Datasheet

Fortimo LED Strip 2ft 6000lm HV6

The Fortimo LED Strip High Flux HV6 is the ideal solution for applications where the lighting fixtures are mounted at higher heights. Key applications include industry and retail where often trunking luminaires, highbay luminaires, battens or waterproof luminaires are being used. The LED modules are designed to have a high light output combined with an extremely long lifetime.

Key features and benefits

- Two lumen output versions: 2000 lm/ft and 3000 lm/ft
- LED module efficiency of 178 Lm/W (4000K, CRI80)
- Long life time of >100,000 hours
- High color rendering: CRI >80
- Excellent color consistency of 3 SDCM
- Variation of color temperatures: 3000 K, 4000 K, 5000 K, and 6500 K
- Two lengths: 1ft and 2ft
- Wide case temperature (Tc) range from -40 °C to +95 °C
- Five years system warranty

November 2021



Ordering data

Commercial product name	EOC	12NC	Box quantity
Fortimo LED Strip 2ft 6000lm FC 830 HV6	8718699 788148 00	9290 028 02506	84
Fortimo LED Strip 2ft 6000lm FC 840 HV6	8718699 789428 00	9290 028 02606	84
Fortimo LED Strip 2ft 6000lm FC 850 HV6	8718699 789442 00	9290 028 02706	84
Fortimo LED Strip 2ft 6000lm FC 865 HV6	8718699 789466 00	9290 028 02806	84

Drive currents

Parameter	Nominal*	Life**	Max***	Unit
Fortimo LED Strip 2ft 6000lm HV6	428	600	720	mA

Module temperatures

Parameter	Nominal*	Life**	Max***	Unit
T _c (case temperature at T _c point)	55	90	95	°C

* Nominal value at which typical performance is specified

** Value at which life time is specified

*** Maximum value for safe operation, do not operate above this value


Optical characteristics - table per color (CCT)

Fortimo LED Strip 2ft 6000lm FC 830 HV6

Parameter	Min	Typ	Max	Unit
Luminous flux	4995	5400	5805	lm
Module efficacy	157	160	177	lm/W
Correlated color temperature (CCT)		3000		K
Color coordinates (CIEx, CIEy)		(0.430, 0.400)		-
Color consistency			3	SDCM
CRI	80			
Photometric code		830/359		
Photobiological safety			RG1 unlimited	

Measurement precision for flux +/- 5%. Measurement precision for x, y +/- 0.005. Measurement precision for CRI 1.5

Operation point	830	lm	lm/W
80% I-nom 342mA	Tc 25 °C	4497	167
	Tc-nom 55 °C	4375	164
	Tc-max 95 °C	4137	158
I-nom 428mA	Tc 25 °C	5551	162
	Tc-nom 55 °C	5400	160
	Tc-max 95 °C	5105	153
I-max 720mA	Tc 25 °C	9000	149
	Tc-nom 55 °C	8750	146
	Tc-max 95 °C	8264	140




Fortimo LED Strip 2ft 6000lm FC 840 HV6

Parameter	Min	Typ	Max	Unit
Luminous flux	5272	5700	6128	lm
Module efficacy	167	169	189	lm/W
Correlated color temperature (CCT)		4000		K
Color coordinates (CIEx, CIEy)		(0.379, 0.375)		-
Color consistency			3	SDCM
CRI	80			
Photometric code		840/359		
Photobiological safety			RG1 unlimited	

Measurement precision for flux +/- 5%. Measurement precision for x, y +/- 0.005. Measurement precision for CRI 1.5

Operation point	840	lm	lm/W
80% I-nom 342mA	Tc 25 °C	4760	178
	Tc-nom 55 °C	4617	174
	Tc-max 95 °C	4344	166
I-nom 428mA	Tc 25 °C	5877	172
	Tc-nom 55 °C	5700	169
	Tc-max 95 °C	5361	161
I-max 720mA	Tc 25 °C	9532	157
	Tc-nom 55 °C	9239	153
	Tc-max 95 °C	8680	146




Fortimo LED Strip 2ft 6000lm FC 850 HV6

Parameter	Min	Typ	Max	Unit
Luminous flux	5272	5700	6128	lm
Module efficacy	167	169	189	lm/W
Correlated color temperature (CCT)		5000		K
Color coordinates (CIEx, CIEy)		(0.341, 0.349)		-
Color consistency			3	SDCM
CRI	80			
Photometric code		850/359		
Photobiological safety			RG1 unlimited	

Measurement precision for flux +/- 5%. Measurement precision for x, y +/- 0.005. Measurement precision for CRI 1.5

Operation point	850	lm	lm/W
80% I-nom 342mA	Tc 25 °C	4760	178
	Tc-nom 55 °C	4617	174
	Tc-max 95 °C	4344	166
I-nom 428mA	Tc 25 °C	5877	172
	Tc-nom 55 °C	5700	169
	Tc-max 95 °C	5361	161
I-max 720mA	Tc 25 °C	9532	157
	Tc-nom 55 °C	9239	153
	Tc-max 95 °C	8680	146




Fortimo LED Strip 2ft 6000lm FC 865 HV6

Parameter	Min	Typ	Max	Unit
Luminous flux	5208	5630	6052	lm
Module efficacy	166	167	187	lm/W
Correlated color temperature (CCT)		6500		K
Color coordinates (CIEx, CIEy)		(0.309, 0.322)		-
Color consistency			3	SDCM
CRI	80			
Photometric code		865/359		
Photobiological safety			RG1 unlimited	

Measurement precision for flux +/- 5%. Measurement precision for x, y +/- 0.005. Measurement precision for CRI 1.5

Operation point	865	lm	lm/W
80% I-nom 342mA	Tc 25 °C	4715	175
	Tc-nom 55 °C	4560	172
	Tc-max 95 °C	4268	163
I-nom 428mA	Tc 25 °C	5821	170
	Tc-nom 55 °C	5630	167
	Tc-max 95 °C	5267	158
I-max 720mA	Tc 25 °C	9441	156
	Tc-nom 55 °C	9126	152
	Tc-max 95 °C	8528	144



Electrical characteristics


Parameter	Min	Typ	Max	Unit
Forward voltage	77.2	79.0	80.4	V
Power consumption	33.1	33.8	34.4	W = kWh/1000h
Number of modules in series per chain			4	

Measurement precision for Vf +/- 3%. Measurement precision for power +/- 3.3%.

Tuning information


Flux and efficacy versus current (at Tc nominal)

I [mA]	Flux [%]	Efficacy [%]
600	137	95
514	119	97
428	100	100
342	81	103
214	52	108



Flux and efficacy versus temperature at Tc (at I nominal)

Tc [°C]	Flux [%]	Efficacy [%]
90	95	96
55	100	100
25	103	102
0	106	104




Lumen maintenance

Operation point	Lumen maintenance x 1000 hours	L70			L80			L90		
		B50	B20	B10	B50	B20	B10	B50	B20	B10
80% I _{nom} 342mA	T _c 25°C	>100	>100	>100	>100	>100	>100	>100	>100	>100
	T _{c_nom} 55°C	>100	>100	>100	>100	>100	>100	82	80	80
	T _{c_life} 90°C	>100	73	57	>100	73	57	57	56	55
I _{nom} 428mA	T _c 25°C	>100	>100	>100	>100	>100	>100	>100	>100	>100
	T _{c_nom} 55°C	>100	>100	>100	>100	>100	>100	78	77	76
	T _{c_life} 90°C	>100	732	57	>100	73	57	55	54	53
I _{life} 600mA	T _c 25°C	>100	>100	>100	>100	>100	>100	>100	>100	>100
	T _{c_nom} 55°C	>100	>100	>100	>100	>100	>100	73	72	71
	T _{c_life} 90°C	>100	73	57	>100	73	57	51	50	49

Lifetime

Parameter	Value	Unit
M70F50 nominal	>100000	hours
M70F50 life	>100000	hours

Performance Window




Wiring

Specification item	Value	Unit	Condition
Input wire cross-section	0.25...0.75	mm ²	solid wire
	18...24	AWG	solid wire
Input wire strip length	7.5...8.5	mm	
Input wire cross-section	0.33...0.5	mm ²	stranded wire
	20...22	AWG	stranded wire
Input wire strip length	7.5...8.5	mm	

Mechanical characteristics

Parameter	Min	Typ	Max	Unit
Length	558.9	559.2	559.5	mm
Width	19.8	20	20.6	mm
Height PCB	1.4	1.6	1.8	mm
Height total		6.1		mm
Product mass		37		gram



Absolute ratings

Parameter	Min	Max	Unit
Current through the LED module (I-max)		720	mA
Case temperature (Tc-max)		95	°C
ESD (direct contact)	8		kV
Working voltage		350	V _{dc}

Application information

Certificates and Standards

CE
ENEC
ENEC+

Environmental

RoHS/REACH

Application

Dimming	Yes
---------	-----



© 2021 Signify Holding, IBRS 10461, 5600VB, NL. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

www.philips.com/oem

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.
UK importer address: 3 Guildford Business Park, GU2 8XG

24/11/2021