

PHILIPS

sense and simplicity

Introducing the new
HID PrimaVision Compact Connector
Smart gear, made simple

Ruud van der Zanden
Category OEM
June 2012



eHID portfolio overview

AspiraVision

AspiraVision Compact 35W, 50W & 70W

AspiraVision, a mark of excellence in HID electronic gears technology. Intelligent, easy to use and easy to install



Features:



AspiraVision DALI 70W

Excellence complimented with innovation; our AspiraVision DALI gears are equipped with DALI interface and offer dimmability and boosting of CDM lamps



Features:



PrimaVision

PrimaVision Mini 20W, 35W, 50W



Features:



Miniature size gears that allow pushing boundaries of creativity and innovation in luminaire designs

PrimaVision Compact 35W, 50W, 70W



Features:



High quality compact size gears for optimal and reliable performance of CDM lamps

PrimaVision Twin 35W, 70W



Features:



Dual lamp operation with a single gear for cost effectiveness and increased luminaire design flexibility

PrimaVision Power 100W, 150W



Features:



Higher power gears packed in a small size. Optimal and reliable performance with CDM lamps, ideal where high intensity of light is of key importance

PrimaVision Economy

PrimaVision Economy 35W & 70W



Features:



PrimaVision Economy is a plug-and-play cost-down solution for luminaires that are not temperature-critical

Electronic driver types


Standard



/S

Built in the luminaire

PCB



/P

Built in the luminaire

Independent



/I

Placed on ceiling

Connector



/C

Placed on ceiling


Cabled



/G /GM

Placed on ceiling

PrimaVision Connector



Plug and Play


- Allows for late stage configuration
- Idiot proof; wiring mistakes not possible
- ST18 Universal connector on the lamp side
- Industry standard GST18 connector on the mains side

Simplify logistical complexity

- Just keep one driver in stock + multiple cables
- Fix configuration at a late stage (even at project side)
- No more labor intensive, in house cabling

Save on operational costs

- No labor costs and no processing time to mount cables
- Lowest material costs per lighting installation (driven by late stage configuration)



Logistics information



Product Codes

12NC	Description
913700647966	HID-PV C 35 /C CDM 220-240V 50/60Hz
913700680266	HID-PV C 50 /C CDM 220-240V 50/60Hz
913700646966	HID-PV C 70 /C CDM 220-240V 50/60Hz

Compatibility PrimaVision and MASTERColour CDM

Philips lamp type	Compatible
CDM-T/TC/TD/Tm-GU6.5	Yes
CDM-T/TC/Tm-GU6.5 Elite	Yes
CDM-R/R111/Rm	Yes
CDM-R/R111/Rm Elite	Yes
CDM-Tm-PGJ5	No

