



# Datasheet

# CertaDrive LED drivers - Linear HV non-isolated

CertaDrive 30W 0.29A 102V 230V

9290 015 98606

#### Fixed current/voltage LED drivers for high volume LED propositions

The CertaDrive LED drivers are designed to fulfill the market need for essential lighting. The CertaDrive LED drivers offer basic specifications such as specific current and voltage settings, optimal to operate CertaFlux LED modules. Life time of the driver is set at 50,000 hours. Philips will extend the portfolio of CertaDrive LED drivers to match high volume CertaFlux LED line propositions as well as high volume opportunities of other LED board manufactures.

#### **Benefits**

- Design freedom
- Optimized to operate CertaFlux LED lines
- 3-years warranty

### **Features**

- Small dimensions
- Specific current and voltage
- 50.000 hours life time
- Fast Time to Market

#### **Application**

- Waterproof luminaires
- Recessed, surface and suspended luminaires in offices

#### **Electrical input data**

Specification item	Value	Unit	Condition
Rated input voltage range	220240	V <sub>ac</sub>	Performance range
Rated input voltage	230	V <sub>ac</sub>	
Rated input frequency range	5060	Hz	Performance range
Rated input current	0.17	А	@ full output power @ rated input voltage
Rated input power	32.5	W	@ full output power @ rated input voltage
Power factor	0.9		@ rated output power @ rated input voltage
Total harmonic distortion	20	%	@ rated output power @ rated input voltage
Efficiency	87	%	@ rated output power @ rated input voltage
Rated input voltage DC range	186250	V <sub>dc</sub>	Performance range
Input voltage AC range	202254	V <sub>ac</sub>	Operational range
Input frequency AC range	47.563	Hz	Operational range
Input voltage DC range	186250	V <sub>dc</sub>	Operational range
Isolation input to output	No		

### **Electrical output data**


Specification item	Value	Unit	Condition
Regulation method	Constant Current		
Output voltage	68102	V <sub>dc</sub>	
Output voltage max.	310	V	Maximum output voltage (rms)
Output current	0.29	Α	Fixed output current
Output current tolerance ±	8	%	
Output current ripple LF	≤ 30	%	Ripple = peak / average, < 3kHz
Output power	2029.6	W	

# Electrical data controls input

Specification item	Value	Unit	Condition
Control method	Fixed		

# **Wiring and Connections**

Specification item	Value	Unit	Туре
Input wire cross-section	0.51.5 / 2016	mm <sup>2</sup> / AWG	WAGO744, solid wire
Input wire strip length	89	mm	
Output wire cross-section	0.51.5 / 2016	mm <sup>2</sup> / AWG	WAGO744, solid wire
Output wire strip length	89	mm	
Maximum cable length	0.6	m	Total length of wiring including LED module, one way. For longer
			wiring please double check EMI behavior of luminaire.




#### Insulation

Insulation per IEC61347-1	Input	Output	Housing
Input		Non	Basic
Output	Non		Basic
Housing	Basic	Basic	

# Dimensions and weight

Specification item	Value	Unit	Tolerance (mm)
Length (A1)	209	mm	
Mounting hole distance (A2)	195	mm	
Width (B1)	30	mm	
Height (C1)	21.5	mm	
Mounting hole diameter (D1)	4.1	mm	
Weight	132	gram	



# Logistical data


Specification item	Value
Product name	CertaDrive 30W 0.29A 102V 230V
EOC	871869674401700
Logistic code 12NC	9290 015 98606
EAN1 (GTIN)	8718696744017
EAN3 (box)	8718696744024
Pieces per box	20

# Operational temperatures and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-20+50	°C	Higher ambient temperature allowed as long as Tcase-max is not exceeded
Tcase-max	75	°C	Maximum temperature measured at T <sub>case</sub> -point
Tcase-life	65	°C	Measured at T <sub>case</sub> -point
Maximum housing temperature	110	°C	In case of a failure, inherent by design
Relative humidity	1090	%	Non-condensing

#### Lifetime

Specification item	Value	Unit	Condition
Driver lifetime	50,000	hours	Measured temperature at Tcase-point is Tcase-life. Maximum
			failures = 10%



# Storage temperature and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-25+85	°C	
Relative humidity	595	%	Non-condensing

# Programmable features


Specification item	Available	Default setting	Condition
Set Adjustable Output Current (AOC)	No	290 mA	Fixed output current
LED Module Temperature Protection (MTP)	No		
Constant Light Output (CLO)	No		
DC emergency (DCemDim)	No		

#### **Features**

Specification item	Value	Condition
Open load protection	Yes	Automatic recovering
Short circuit protection	Yes	Automatic recovering
Over power protection	Yes	
Hot wiring	No	
Suitable for fixtures with protection class	I	per IEC60598

#### Inrush current

Specification item	Value	Unit	Condition
Inrush current I <sub>peak</sub>	8	Α	Input voltage 230V
Inrush current T <sub>width</sub>	60	μs	Input voltage 230V, measured at 50% I <sub>peak</sub>
Drivers / MCB 16A type B	≤ 24	pcs	Indicative value



МСВ	Rating	Relative number of LED drivers
В	4A	25%
В	6A	40%
В	10A	63%
В	13A	81%
В	16A	100% (stated in datasheet)
В	20A	125%
В	25A	156%
В	32A	200%
В	40A	250%
С	4A	42%
С	6A	63%
С	10A	104%
С	13A	135%
С	16A	170%
С	20A	208%
С	25A	260%
С	32A	340%
С	40A	415%

# Driver touch current / protective conductor current

Specification item	Value	Unit	Condition
Typical Protective Conductor Current (ins. Class I)	0.5	mA rms	Acc. IEC60598-1. LED module contribution not included

# Surge immunity


Specification item	Value	Unit	Condition
Mains surge immunity (diff. mode)	1	kV	Acc. IEC61000-4-5. 2 Ohm, 1.2/50us, 8/20us
Mains surge immunity (comm. mode)	2	kV	Acc. IEC61000-4-5. 12 Ohm 1.2/50us,8/20us

# **Application Info**


Specification item	Value
Approval marks	CCC / CE / ENEC / RCM / TISI
Ingress Protection classification (IP)	20
Application	Indoor Linear
Mounting Type	Built-in

### Graphs


# Operating window




### Power factor versus output power



# Efficiency versus output power







© 2021 Signify Holding, IBRS 10461, 5600 VB, NL. All rights reserved. UK importer address: Signify Commercial UK Limited, 3, Guildford Business Park, GU2 8XG.

The information provided herein is subject to change without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Date of release: March 3, 2021 v2