





# Datasheet

# **LED Transformers**

### CertaDrive LED Transformer 30W 24VDC

#### **Product description**

Philips full-electronic constant voltage LED Transformers are designed to operate 24VDC LED solutions used in general applications such as refrigerated display lighting, retail display lighting and linear accent lighting. They are specifically designed to ensure the highest performance with maximum robustness combined with a long lifetime.

### Benefits

SELV operating voltages, ensuring safety even if wiring or LED boards become damaged

Energy savings through high efficiency Ultimate robustness, offering peace of mind and lower maintenance costs Easy to design-in and install Long lifetime

#### **Features**

- Built-in use for Insulation Class I and II applications
- · Global approbations and certifications
- Stable output voltage
- · Wide ambient temperature range
- · Protection against overpower
- Output short-circuit shutdown feature with automatic restart

### Application

Retail display lighting, linear accent lighting and refrigerated display lighting

- · Shelf lighting
- Cove lighting
- · Facade accent lighting
- · Coolers and freezers

### Electrical input data

Specification item	Value	Unit	Condition
Rated input voltage range	220240	Vac	Performance
Rated input voltage range	198264	Vac	Operational safety
Rated input frequency	5060	Hz	Performance
Rated input frequency	4566	Hz	Operational safety
Rated input current	0.17	Α	
Rated input power	35	W	
Power factor	0.95		
Total harmonic distortion	< 20	%	
Efficiency	85	%	(a) rated output power (a) rated input voltage (a) max. Uout

### Electrical output data

Specification item	Value	Unit	Condition
Regulation method	Constant Voltage		Rated output voltage = 24VDC
Output voltage range	22.825.2	Vdc	@ output current range 0.75 1.25A
utput current range	0.251.25	Adc	
ıtput voltage ripple	< 2400	mV <sub>pp</sub>	
ited output power	30	W	Min output power 6W
e regulation	<3	%	
ad regulation	< 5	%	
n-on delay	≤ 1	S	
itput voltage rise time	≤ 100	ms	
ld-up time	≥ 10	ms	
ntrol method	Fixed		

### Logistical data

Specification item	Value
Product name	CertaDrive LED Transformer 30W 24VDC
Order code	749453 00
Logistic code 12NC	9290 021 46280
Pieces per box	50

### Wiring & Connections

Specification item	Value	Unit	Condition
Input wire cross-section	0.51.5	mm²	Solid and stranded wire
Input wire strip length	67	mm	
Output wire cross-section	0.51.5	mm²	Solid and stranded wire
Output wire strip length	67	mm	
Maximum output cable length	1.0	m	CISPR15: between driver and LED module




#### Insulation

Insulation	Mains	LED
Mains		SELV (double)
LED	SELV (double)	

#### Dimensions and weight

		Condition
150.0	mm	
40.0	mm	
28.0	mm	
140.0	mm	Fixing hole diameter: 4.2 mm
90	gram	
	40.0 28.0 140.0	40.0 mm 28.0 mm 140.0 mm





### Operational temperatures and humidity

Specification item	Value	Unit	Condition
Driver ambient temperature	-20+50	°C	At rated output power. Higher ambient temperature allowed as long as Tcase-max is not exceeded.
Tcase-min	-20	°C	
Tcase-max	90	°C	Max. steady-state Tcase
Tcase-life	80	°C	For rated driver lifetime
Maximum housing temperature	110	°C	In case of failure
Relative humidity	1090	%	Non-condensing
Ingress Protection*	IP20		
Noise and hum	≤ 20	dB	

<sup>\*:</sup> The LED Transformer is primarily intended for built-in use. It must not be exposed including but not limited to snow, water and ice or any other chemical agent which may have an adverse affect on driver operation and performance. Exposure may lead to driver failure. It is the luminaire manufacturer's/installer's responsibity to prevent exposure.

### Storage temperature and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-20+80	°C	
Relative humidity	595	%	Non-condensing

### Lifetime

Specification item	Value	Unit	Condition
Rated driver lifetime	30,000	hours	Tcase ≤ Tcase-life. Maximum failures = 10%.
			See graph.

#### **Features**


Specification item	Value	Remark	Condition
Open load protection	Yes		Uout (open circuit) = 35V max
Short circuit protection	Yes		Hiccup mode, automatic recovering
Over power protection	Yes		Automatic recovering
Overheating protection	Yes		
Hot wiring	Yes		
Suitable insulation class applications	I and II		Per IEC60598

#### **Certificates and standards**

Specification item	Value
Approval marks	CE / CB / CCC / SELV / 110 / Double-insulated / ENEC

#### Inrush current

Specification item	Value	Unit	Condition
Inrush current Ipeak (typ)	4.6	A	Input voltage 240Vac
Inrush current Twidth (typ)	60	μs	Input voltage 240Vac, measured at 50% Ipeak
Max. recommended number of drivers	28	pcs	MCB 16A B type, mains impedance 200mΩ + 400μH



МСВ	Rating	Relative number of drivers*		
В	6A	37%		
В	10A	63%		
В	13A	81%		
В	16A	100%		
В	20A	125%		
В	25A	156%		
С	6A	63%		
С	10A	104%		
С	13A	135%		
С	16A	170%		
С	20A	208%		
С	25A	260%		
D	6A	125%		
D	10A	104%		
D	13A	135%		
D	16A	170%		
D	20A	208%		


 $<sup>\</sup>ensuremath{^*}$  : please check that cable cross sectional area corresponds with MCB rating and type

### Surge immunity


Specification item	Value	Remark	Condition		
Mains surge immunity (diff. mode)	1	kV	L-N, acc. IEC61000-4-5. 2 Ohm, 1.2/50us, 8/20us		

### Graphs


### Power factor versus output power




### Efficiency versus output power



## THD versus output power



#### Driver lifetime versus Tc temperature





 $\hbox{@2021}$  Signify Holding, IBRS 10461, 5600 VB, NL. All rights reserved.

The information provided herein is subject to change without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Date of release: August 31, 2021