

PHILIPS

CertaFlux

LED

CertaFlux LED Strip 2ft
2200lm HV4



Datasheet

CertaFlux LED Strip

Generation 4 of the Certaflux LED Strip is designed to provide a better efficiency without sacrificing its other success factors as lifetime and light quality. The Certaflux LED Strip is an ideal product for several different applications: office, industry and waterproof.

Key features and benefits

- LED module efficiency up to 165 lm/W
- Long life-time: >50,000 hours
- Good color rendering, CRI: >80
- Color consistency of 3 SDCM
- Color temperatures of 3000 K, 4000 K and 6500 K
- One-foot (280mm) and two-foot (560mm) lengths available
- Two lumen packages: 775lm per foot and 1100lm per foot
- PCB width is only 20mm
- Wide temperature range (Tc) from -40°C to +85°C
- Push-in connectors enable automatic wiring
- Designed to work together with CertaDrive drivers
- Three year system warranty

October 2021



Ordering data

Commercial product name	EOC	12NC	Box quantity
CertaFlux LED Strip 2ft 2200lm 830 HV4	8718699 666729 00	9290 016 85306	168
CertaFlux LED Strip 2ft 2200lm 840 HV4	8718699 666743 00	9290 016 85406	168
CertaFlux LED Strip 2ft 2200lm 865 HV4	8718699 666767 00	9290 016 85506	168

Drive currents

Parameter	Nominal*	Life**	Max***	Unit
CertaFlux LED Strip 2ft 2200lm HV4	328	580	580	mA

Module temperatures

Parameter	Nominal*	Life**	Max***	Unit
T _c (case temperature at T _c point)	55	85	85	°C

* Nominal value at which typical performance is specified

** Value at which life time is specified

*** Maximum value for safe operation, do not operate above this value


Optical characteristics - table per color (CCT)

CertaFlux LED Strip 2ft 2200lm 830 HV4

Parameter	Min	Typ	Max	Unit
Luminous flux	1836	1985	2134	lm
Module efficacy		149		lm/W
Correlated color temperature (CCT)		3000		K
Color coordinates (CIEx, CIEy)		(0.432, 0.399)		-
Color consistency			3	SDCM
CRI	80			
Photometric code		830/369		
Photobiological safety			RG1 unlimited	

Measurement precision $\pm 5\%$ for the flux data and $\pm 6\%$ for the efficacy data. Measurement precision for color coordinates ± 0.005 . Measurement precision for CRI ± 1.5

Operation point	830	lm	lm/W
80% I-nom 262mA	Tc 25 °C	1757	166
	Tc-nom 55 °C	1675	161
	Tc-max 85 °C	1578	155
I-nom 328mA	Tc 25 °C	2161	161
	Tc-nom 55 °C	1985	149
	Tc-max 85 °C	1937	149
I-max 580mA	Tc 25 °C	3610	143
	Tc-nom 55 °C	3430	138
	Tc-max 85 °C	3219	132




CertaFlux LED Strip 2ft 2200lm 840 HV4

Parameter	Min	Typ	Max	Unit
Luminous flux	1961	2120	2279	lm
Module efficacy		159		lm/W
Correlated color temperature (CCT)		4000		K
Color coordinates (CIEx, CIEy)		(0.377, 0.372)		-
Color consistency			3	SDCM
CRI	80			
Photometric code		840/369		
Photobiological safety			RG1 unlimited	

Measurement precision $\pm 5\%$ for the flux data and $\pm 6\%$ for the efficacy data. Measurement precision for color coordinates ± 0.005 . Measurement precision for CRI ± 1.5

Operation point	840	lm	lm/W
80% I-nom 262mA	Tc 25 °C	1876	178
	Tc-nom 55 °C	1789	172
	Tc-max 85 °C	1686	165
I-nom 328mA	Tc 25 °C	2309	172
	Tc-nom 55 °C	2120	159
	Tc-max 85 °C	2069	159
I-max 580mA	Tc 25 °C	3856	153
	Tc-nom 55 °C	3665	148
	Tc-max 85 °C	3439	141




CertaFlux LED Strip 2ft 2200lm 865 HV4

Parameter	Min	Typ	Max	Unit
Luminous flux	1894	2060	2202	lm
Module efficacy		155		lm/W
Correlated color temperature (CCT)		6500		K
Color coordinates (CIEx, CIEy)		(0.310, 0.325)		-
Color consistency			3	SDCM
CRI	80			
Photometric code		865/369		
Photobiological safety			RG1 unlimited	


Measurement precision $\pm 5\%$ for the flux data and $\pm 6\%$ for the efficacy data. Measurement precision for color coordinates ± 0.005 . Measurement precision for CRI ± 1.5

Operation point	865	lm	lm/W
80% I-nom 262mA	Tc 25 °C	1842	174
	Tc-nom 55 °C	1756	169
	Tc-max 85 °C	1655	162
I-nom 328mA	Tc 25 °C	2267	169
	Tc-nom 55 °C	2060	155
	Tc-max 85 °C	2032	156
I-max 580mA	Tc 25 °C	3787	150
	Tc-nom 55 °C	3599	145
	Tc-max 85 °C	3378	138



Beam shape

The Philips LED module generates a Lambertian beam shape, which is a pragmatic starting point for OEMs wishing to design secondary optics.



Electrical characteristics

Parameter	Min	Typ	Max	Unit
Forward voltage	39.1	40.6	41.5	V
Power consumption	12.8	13.3	13.6	W = kWh/1000h
Number of modules in series per chain			6	

Measurement precision for Vf +/- 3%. Measurement precision for power +/- 3.3%


Specifications stated at Tc-nom and I-nom

Parallel connection allowed. Check www.easydesignintool.com.

Tuning information


Flux and efficacy versus current (at Tc nominal)

I [mA]	Flux [%]	Efficacy [%]
580	167	89
454	134	94
328	100	100
262	81	104
164	52	109



Flux and efficacy versus temperature at Tc (at I nominal)

Tc [°C]	Flux [%]	Efficacy [%]
85	94	96
55	100	100
25	105	103
0	109	105




Lumen maintenance

Operation point	Lumen maintenance x 1000 hours	L70			L80			L90		
		B50	B20	B10	B50	B20	B10	B50	B20	B10
80% I-nom 262 mA	Tc 25°C	>100	>100	>100	>100	>100	>100	65	63	62
	Tc-nom 45°C	>100	>100	>100	>100	>100	>100	52	50	49
	Tc-life 85°C	>100	>100	>100	73	71	69	34	33	32
I-nom 328 mA	Tc 25°C	>100	>100	>100	>100	>100	>100	62	60	59
	Tc-nom 45°C	>100	>100	>100	94	91	89	44	43	42
	Tc-life 85°C	>100	>100	>100	70	68	66	33	32	31
I-life 580 mA	Tc 25°C	>100	>100	>100	>100	>100	>100	55	53	52
	Tc-nom 45°C	>100	>100	>100	94	90	88	44	42	41
	Tc-life 85°C	100	96	95	62	60	59	29	28	28

Lifetime

Parameter	Value	Unit
M70F50 nominal	87000	hours
M70F50 life	60000	hours

Performance Window




Wiring

Specification item	Value	Unit	Condition
Input wire cross-section	0.33...0.5	mm ²	solid wire
	20...22	AWG	solid wire
Input wire strip length	6.1...7.1	mm	
Input wire cross-section	0.33...0.75	mm ²	stranded (tin-dipped) wire
	18...22	AWG	stranded (tin-dipped) wire
Input wire strip length	6.1...7.1	mm	



Mechanical characteristics

Parameter	Min	Typ	Max	Unit
Length	558.9	559.2	559.5	mm
Width	19.8	20	20.6	mm
Height PCB		1		mm
Height with connector		5.25	5.7	mm
Product mass		24		gram



Absolute ratings

Parameter	Min	Max	Unit
Current through the LED module (I-max)		580	mA
Case temperature (Tc-max)		85	°C
Power at rated Vf-max and I-max		27.3	W
ESD (direct contact)	1		kV
Working voltage		350	V _{dc}
Ambient temperature	-40		°C

Application information

Certificates and Standards

IEC 62031:2008/A1:2012/A2:2014

EN 62031:2008/A1:2013/A2:2015

Relevant clauses of IEC 62471:2006 (Incl. IEC/TR 62471-2: 2009 and IEC/TR 62778: 2014)

Relevant clauses of EN 62471:2008 (With IEC/TR 62471-2: 2009 and IEC/TR 62778: 2014)

ENEC

ENEC+

CE

Application

IP rating	No IP-rating
Overheating protection	No protection
Dimming	Yes



© 2021 Signify Holding, IBRS 10461, 5600VB, NL. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

www.philips.com/oem

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.
UK importer address: 3 Guildford Business Park, GU2 8XG

18/10/2021