

# ET driver and lamp compatibility list

Driver 12nc		913710032179		929002101880		913710032479	
Description		ET-E 10 220-240V		ET-H 10 220-240V		ET-S 15 LED 220-240V	
# of drivers : lamps		1:1	1:2	1:1	1:2	1:1	1:2
Lamp 10nc	Description						
9290011474	MASTER LED 4-35W 2700K MR16 24D	X	X	X	X	X	✓
9290011477	MASTER LED 4-35W 3000K MR16 24D	X	X	X	X	X	✓
9290011475	MASTER LED 4-35W 2700K MR16 36D	X	X	X	X	X	✓
9290011476	MASTER LED 4-35W 3000K MR16 36D	X	X	X	X	X	✓
9290011459	MASTER LED 5.5-50W 2700K MR16 24D	X	✓	X	✓	✓	✓
9290011461	MASTER LED 5.5-50W 2700K MR16 36D	X	✓	X	✓	✓	✓
9290011466	MASTER LED 5.5-50W 3000K MR16 36D	X	✓	X	✓	✓	✓
9290011467	MASTER LED 5.5-50W 3000K MR16 24D	X	✓	X	✓	✓	✓
9290011468	MASTER LED 5.5-50W 4000K MR16 24D	X	✓	X	✓	✓	✓
9290011469	MASTER LED 5.5-50W 4000K MR16 36D	X	✓	X	✓	✓	✓
9290024926	MAS LED spot VLE D 5.8-35W MR16 930 36D	✓	✓	✓	✓	✓	✓
9290024927	MAS LED spot VLE D 5.8-35W MR16 940 36D	✓	✓	✓	✓	✓	✓
9290024928	MAS LED spot VLE D 5.8-35W MR16 927 60D	✓	✓	✓	✓	✓	✓
9290024929	MAS LED spot VLE D 5.8-35W MR16 930 60D	✓	✓	✓	✓	✓	✓
9290024930	MAS LED spot VLE D 5.8-35W MR16 940 60D	✓	✓	✓	✓	✓	✓
9290024932	MAS LED SPOT VLE D 7.5-50W MR16 927 36D	✓	✓	✓	✓	✓	✓
9290024933	MAS LED SPOT VLE D 7.5-50W MR16 930 36D	✓	✓	✓	✓	✓	✓
9290024934	MAS LED SPOT VLE D 7.5-50W MR16 940 36D	✓	✓	✓	✓	✓	✓
9290024935	MAS LED SPOT VLE D 7.5-50W MR16 927 60D	✓	✓	✓	✓	✓	✓
9290024936	MAS LED SPOT VLE D 7.5-50W MR16 930 60D	✓	✓	✓	✓	✓	✓
9290024937	MAS LED SPOT VLE D 7.5-50W MR16 940 60D	✓	✓	✓	✓	✓	✓
9290030870	MAS LEDspotLV 3.5-20W 827 MR11 24D	X	X	X	X	✓	✓
9290030716	MASTER LED 6.5-50W 927 MR16 10D Dim	✓	✓	✓	✓	✓	✓
9290030717	MASTER LED 6.5-50W 930 MR16 10D Dim	✓	✓	✓	✓	✓	✓
9290030718	MASTER LED 6.5-50W 940 MR16 10D Dim	✓	✓	✓	✓	✓	✓
9290030719	MASTER LED 6.5-50W 927 MR16 24D Dim	✓	✓	✓	✓	✓	✓
9290030720	MASTER LED 6.5-50W 930 MR16 24D Dim	✓	✓	✓	✓	✓	✓
9290030721	MASTER LED 6.5-50W 940 MR16 24D Dim	✓	✓	✓	✓	✓	✓
9290030722	MASTER LED 6.5-50W 927 MR16 36D Dim	✓	✓	✓	✓	✓	✓
9290030723	MASTER LED 6.5-50W 930 MR16 36D Dim	✓	✓	✓	✓	✓	✓
9290030724	MASTER LED 6.5-50W 940 MR16 36D Dim	✓	✓	✓	✓	✓	✓
9290030759	MASTER LED 6.5-50W 927 MR16 60D Dim	✓	✓	✓	✓	✓	✓
9290030760	MASTER LED 6.5-50W 930 MR16 60D Dim	✓	✓	✓	✓	✓	✓
9290030761	MASTER LED 6.5-50W 940 MR16 60D Dim	✓	✓	✓	✓	✓	✓
9290018819	MASTER LED 6.5-50W 927 MR16 24D ND	X	✓	X	✓	✓	✓
9290018820	MASTER LED 6.5-50W 930 MR16 24D ND	X	✓	X	✓	✓	✓
9290018821	MASTER LED 6.5-50W 940 MR16 24D ND	X	✓	X	✓	✓	✓
9290018822	MASTER LED 6.5-50W 927 MR16 36D ND	X	✓	X	✓	✓	✓
9290018823	MASTER LED 6.5-50W 930 MR16 36D ND	X	✓	X	✓	✓	✓
9290018824	MASTER LED 6.5-50W 940 MR16 36D ND	X	✓	X	✓	✓	✓
9290030725	MASTER LED 7.5-50W+ 827 MR16 24D Dim	✓	✓	✓	✓	✓	✓
9290030726	MASTER LED 7.5-50W+ 830 MR16 24D Dim	✓	✓	✓	✓	✓	✓
9290030727	MASTER LED 7.5-50W+ 827 MR16 36D Dim	✓	✓	✓	✓	✓	✓
9290030728	MASTER LED 7.5-50W+ 830 MR16 36D Dim	✓	✓	✓	✓	✓	✓
9290030729	MASTER LED 7.5-50W+ 840 MR16 36D Dim	✓	✓	✓	✓	✓	✓
9290030785	MAS LED MR16 ExpertColor 6.7-50W 927 60D	✓	✓	✓	✓	✓	✓
9290030786	MAS LED MR16 ExpertColor 6.7-50W 930 60D	✓	✓	✓	✓	✓	✓
9290030787	MAS LED MR16 ExpertColor 6.7-50W 940 60D	✓	✓	✓	✓	✓	✓
9290030767	MAS LED MR16 ExpertColor 6.7-50W 927 10D	✓	✓	✓	✓	✓	✓
9290030768	MAS LED MR16 ExpertColor 6.7-50W 930 10D	✓	✓	✓	✓	✓	✓
9290030769	MAS LED MR16 ExpertColor 6.7-50W 940 10D	✓	✓	✓	✓	✓	✓
9290030770	MAS LED MR16 ExpertColor 6.7-50W 927 24D	✓	✓	✓	✓	✓	✓
9290030771	MAS LED MR16 ExpertColor 6.7-50W 930 24D	✓	✓	✓	✓	✓	✓
9290030772	MAS LED MR16 ExpertColor 6.7-50W 940 24D	✓	✓	✓	✓	✓	✓
9290030773	MAS LED MR16 ExpertColor 6.7-50W 927 36D	✓	✓	✓	✓	✓	✓
9290030774	MAS LED MR16 ExpertColor 6.7-50W 930 36D	✓	✓	✓	✓	✓	✓
9290030775	MAS LED MR16 ExpertColor 6.7-50W 940 36D	✓	✓	✓	✓	✓	✓
9290012397	Essential LED 3-35W 2700K MR16 24D	✓	✓	✓	✓	✓	✓
9290012398	Essential LED 3-35W 6500K MR16 24D	✓	✓	✓	✓	✓	✓
9290012401	Essential LED 5-50W 2700K MR16 24D	✓	✓	✓	✓	✓	✓
9290012402	Essential LED 5-50W 6500K MR16 24D	✓	✓	✓	✓	✓	✓
9290024946	CorePro LED spot ND 4.4-35W MR16 827 36D	✓	✓	✓	✓	✓	✓
9290024947	CorePro LED spot ND 4.4-35W MR16 840 36D	✓	✓	✓	✓	✓	✓
9290012804	LEDClassic 5-50W MR16 830 60D	✓	✓	✓	✓	✓	✓
9290012805	LEDClassic 5-50W MR16 840 60D	✓	✓	✓	✓	✓	✓
9290035723	LEDSpot 35W DS ND MR16 12V 60D	✓	✓	✓	✓	✓	✓
9290035724	LEDSpot 50W DS ND MR16 12V 60D	✓	✓	✓	✓	✓	✓
9290024217	MASTER LED 3.8-50W 2700K MR16 15D	N/A	N/A	N/A	N/A	✓	N/A
9290024218	MASTER LED 3.8-50W 2700K MR16 24D	N/A	N/A	N/A	N/A	✓	N/A
9290024219	MASTER LED 3.8-50W 2700K MR16 36D	N/A	N/A	N/A	N/A	✓	N/A
9290024220	MASTER LED 3.8-50W 3000K MR16 15D	N/A	N/A	N/A	N/A	✓	N/A
9290024221	MASTER LED 3.8-50W 3000K MR16 24D	N/A	N/A	N/A	N/A	✓	N/A
9290024222	MASTER LED 3.8-50W 3000K MR16 36D	N/A	N/A	N/A	N/A	✓	N/A

# ET driver and lamp compatibility list

Driver 12nc		913710032179				929002101880				913710032479	
Description		ET-E 10 220-240V				ET-H 10 220-240V				ET-S 15 LED 220-240V	
# of drivers : lamps		1:1	1:2	1:3	1:4	1:1	1:2	1:3	1:4	1:1	1:2
Lamp 10nc	Description										
9290012397	Essential LED 3-35W 2700K MR16 24D	✓	✓	N/A	N/A	✓	✓	N/A	N/A	✓	✓
9290012398	Essential LED 3-35W 6500K MR16 24D	✓	✓	N/A	N/A	✓	✓	N/A	N/A	✓	✓
9290012401	Essential LED 5-50W 2700K MR16 24D	✓	✓	N/A	N/A	✓	✓	N/A	N/A	✓	✓
9290012402	Essential LED 5-50W 6500K MR16 24D	✓	✓	N/A	N/A	✓	✓	N/A	N/A	✓	✓
9290024946	CorePro LED spot ND 4.4-35W MR16 827 36D	✓	✓	N/A	N/A	✓	✓	N/A	N/A	✓	✓
9290024947	CorePro LED spot ND 4.4-35W MR16 840 36D	✓	✓	N/A	N/A	✓	✓	N/A	N/A	✓	✓
9290012804	LEDClassic 5-50W MR16 830 60D	✓	✓	N/A	N/A	✓	✓	N/A	N/A	✓	✓
9290012805	LEDClassic 5-50W MR16 840 60D	✓	✓	N/A	N/A	✓	✓	N/A	N/A	✓	✓
9290035723	LEDSpot 35W DS ND MR16 12V 60D	✓	✓	N/A	N/A	✓	✓	N/A	N/A	✓	✓
9290035724	LEDSpot 50W DS ND MR16 12V 60D	✓	✓	N/A	N/A	✓	✓	N/A	N/A	✓	✓
9290036102	MASTER LED 3.9-35W 2700K MR16 24D	X	✓	N/A	N/A	X	✓	N/A	N/A	✓	✓
9290036103	MASTER LED 3.9-35W 3000K MR16 24D	X	✓	N/A	N/A	X	✓	N/A	N/A	✓	✓
9290036104	MASTER LED 3.9-35W 2700K MR16 36D	X	✓	N/A	N/A	X	✓	N/A	N/A	✓	✓
9290036105	MASTER LED 3.9-35W 3000K MR16 36D	X	✓	N/A	N/A	X	✓	N/A	N/A	✓	✓
9290036106	MASTER LED 4.9-50W 2700K MR16 24D	X	✓	N/A	N/A	X	✓	N/A	N/A	✓	✓
9290036107	MASTER LED 4.9-50W 3000K MR16 24D	X	✓	N/A	N/A	X	✓	N/A	N/A	✓	✓
9290036108	MASTER LED 4.9-50W 4000K MR16 24D	X	✓	N/A	N/A	X	✓	N/A	N/A	✓	✓
9290036109	MASTER LED 4.9-50W 2700K MR16 36D	X	✓	N/A	N/A	X	✓	N/A	N/A	✓	✓
9290036110	MASTER LED 4.9-50W 3000K MR16 36D	X	✓	N/A	N/A	X	✓	N/A	N/A	✓	✓
9290036111	MASTER LED 4.9-50W 4000K MR16 36D	X	✓	N/A	N/A	X	✓	N/A	N/A	✓	✓
9290023888	LED 10W G4 WW 12V ND	N/A	N/A	✓	✓	N/A	N/A	✓	✓	N/A	N/A
9290023889	LED 10W G4 WH 12V ND	N/A	N/A	✓	✓	N/A	N/A	✓	✓	N/A	N/A
9290023890	LED 20W G4 WW 12V ND	N/A	N/A	X	X	N/A	N/A	X	X	N/A	N/A
9290023891	LED 20W G4 WH 12V RF ND	N/A	N/A	X	X	N/A	N/A	X	X	N/A	N/A
9290023892	CorePro LEDcapsuleLV 2.7-28W G4 827	N/A	N/A	X	X	N/A	N/A	X	X	N/A	N/A
9290023893	CorePro LEDcapsuleLV 2.7-28W G4 830	N/A	N/A	X	X	N/A	N/A	X	X	N/A	N/A
9290023894	CorePro LEDcapsuleLV 2.1-20W G4 827 D	N/A	N/A	X	✓	N/A	N/A	X	✓	N/A	N/A

Note:

1. System EMI performance need to test based system design;
2. This list is based on measurements performed in a lab environment with limited sample size, performance may be different with different batch lamps or transformers