

Lamp - ballast combination mHID runners

Lamp		Advised gear system for best performance			Alternative gear system		
Commercial name	Technical name	Ballast	Ignitor	Capacitor	Ballast	Ignitor	Capacitor
HPL-N	HPL-N 50W	BHL 50/80 K407	-	7µF/250V	BHL 80/125 K407	-	8µF/250V
HPL	HPL-N 80W	BHL 50/80 K407	-	8µF/250V			
HPL 4	HPL-N 125W	BHL 80/125 K407	-	10µF/250V			
HPL Comfort	HPL-N 250W	BHL 250 K307	-	18µF/250V			
HPL-R	HPL-N 400W	BHL 400 K307	-	25µF/250V			
SON-H	SON-H 68W	BHL 50/80 K407	-	8µF/250V			
	SON-H 110W	BHL 80/125 K407	-	10µF/250V			
	SON-H 220W	BHL 250 K307	-	18µF/250V			
	SON-H 350W	BHL 400 K307	-	25µF/250V			
MASTER SON-T PIA PLUS	SON 50W	BSN 50 K407-ITS	SKD-578	10µF/250V			
MASTER SON PIA PLUS	SON 70W	BSN 70 K407-ITS	SKD-578	12µF/250V			
MASTER SON-T PIA	SON 100W	BSN 100 K407-ITS	SKD-578	12µF/250V			
SON	SON 150W	BSN 150 K407-ITS	SKD-578	18µF/250V			
	SON 250W	BSN 250 K407-ITS	SKD-578	32µF/250V			
	SON 400W	BSN 400 K407-ITS	SKD-578	45µF/250V			
	SON 600W	BSN 600 K302-ITS	SKD-578	60µF/250V			
MASTER Colour City CDO-T/TT/ET	CDO 50W	BSN 50 K407-ITS	SKD-578	10µF/250V			
	CDO 70W	BSN 70 K407-ITS	SKD-578	12µF/250V			
	CDO 100W	BSN 100 K407-ITS	SKD-578	12µF/250V			
	CDO 150W	BSN 150 K407-ITS	SKD-578	18µF/250V			
	CDO 250W	BSN 250 K407-ITS	SKD-578	32µF/250V			
MASTER HPI PLUS	HPI PLUS 250W BU	BSN 250 K407-ITS	SKD-578	32µF/250V	BHL 250 K307	SI-51	18µF/250V
MH-T	HPI PLUS 400W BU	BSN 400 K407-ITS	SKD-578	45µF/250V	BHL 400 K307	SI-51	25µF/250V
	HPI PLUS 400W BUS	BSN 400 K407-ITS	-	45µF/250V	BHL 400 K307	-	25µF/250V
MHN-TD	MHN-TD 150W	BSN 150 K407-ITS	SKD-578	18µF/250V			
	MHN-TD 250W	BSN 250 K407-ITS	SKD-578	32µF/250V			
	MHW-TD 150W	BSN 150 K407-ITS	SKD-578	18µF/250V			
MHN-TD	MHN-TD 70W	BMH 70 K407-ITS	SKD-578	12µF/250V			
MHN-TD B	MHN-TD 150W	BSN 150 K407-ITS	SKD-578	18µF/250V			
MHN-TDES	MHN-TD 250W	BSN 250 K407-ITS	SKD-578	32µF/250V			
MASTER SDW-T	SDW-T 35W	BSL 35 K327-TS	CSLS 35	6µF/250V			
	SDW-T 50W	BSL 50 K307-TS	CSLS 50	9µF/250V			
	SDW-T 100W	BSL 100 K307-TS	CSLS 100	14µF/250V			
MASTER Colour CDM-TP	CDM 150W	BSN 150 K407-ITS	SKD-578	18µF/250V			
	CDM 250W	BSN 250 K407-ITS	SKD-578	32µF/250V			
MASTER Colour CDM-T/TD	CDM-T/TD 35W	BMH 35 K407-ITS	SKD-578	6µF/250V			
	CDM-T/TD 70W	BMH 70 K407-ITS	SKD-578	12µF/250V			
	CDM-T/TD 150W	BSN 150 K407-ITS	SKD-578	18µF/250V			
MASTER Colour CDM-TT/ET	CDM-TT/ET 70W	BMH 70 K407-ITS	SKD-578	12µF/250V			
	CDM -TT/ET 150W	BSN 150 K407-ITS	SKD-578	18µF/250V			
HPI-T	HPI-T 1000W	BHL 1000 L78	SI-52	65µF/250V	BHL 1000 L307-A	SI-52	65µF/250V
	HPI-T 2000W HO /400V	BHL 2000 L76	SI-54	35µF/450V	BHL 2000 L4018-A	SI-54	35µF/450V
	HPI-T 2000W HO /400V	BHL 2000 L50	SI-54	35µF/450V	BHL 2000 L4018-A	SI-54	35µF/450V
	HPI-T 2000W/220V	BHL 2000 L78	SI-52	125µF/250V	BHL 2000 L4018-A	SI-54	35µF/450V
	HPI-T 2000W/380V	BHL 2000 L76	SI-54	35µF/450V			
	HPI-T 2000W/380V	BHL 2000 L50	SI-54	35µF/450V			
HPL-N	HPL-N 1000W	BHL 1000 L78		65µF/250V	BHL 1000 L307-A		65µF/250V
MHN-FC	MHN-FC 2000W/400V	BMH 2000 L5019-A LA/FC	380MZN2000	65µF/400V	BMH 2000 L5018-A	380MZN2000	65µF/450V
MHN-LA	MHN-LA 1000W/230V	BSN 1000 L78	SN56/SN59	100µF/250V	BSN 1000 L307-A	MZN 1000-S	100µF/250V
	MHN-LA 1000W/230V	BSN 1000 L407-I-A	SN59	100µF/250V	BMH 2000 L5018-A	380MZN2000	65µF/450V
	MHN-LA 2000W/400V	BMH 2000 L76	380MZN2000	65µF/400V			
	MHN-LA 2000W/400V	BHD 2000 L76	380MZN2000	65µF/400V			
	MHN-LA 2000W/400V	BHD 2000 L77	380MZN2000	65µF/400V			
	MHN-LA 2000W/400V	BMH 2000 L5019-A LA/FC	380MZN2000	65µF/400V			
MHN-LA 2000W/400V	BMH 2000 L5018-A	380MZN2000	65µF/450V				
MHN-SA	MHN-SA 1800W/230V	BMH 1800 L78	SN56/SN59	200µF/250V	BMH 2000 L5018-A	380MZN2000	70µF/450V
	MHN-SA 1800W/400V	BMH 2000 L76	380MZN2000	70µF/400V			
	MHN-SA 1800W/400V	BHD 2000 L76	380MZN2000	75µF/400V			
	MHN-SA 1800W/400V	BHD 2000 L77	380MZN2000	75µF/400V			
	MHN-SA 2000W/400V	BHD 2000 L76	380MZN2000	70µF/400V			
	MHN-SA 2000W/400V	BHD 2000 L77	380MZN2000	70µF/400V			
	MHN-SA 2000W/400V	BMH 2000 L5018-A	380MZN2000	70µF/450V			
MHN-SB	MHN-SB 2000W/400V	BMH 2000 L5018-A	380MZN2000	70µF/450V	BMH 2000 L5018-A	380MZN2000	70µF/450V
MHN-SE	MHN-SE 2000W/400V	BMH 2000 L5018-A	380MZN2000	70µF/450V			
SON-T	SON-T 1000W	BSN 1000 L78	SN56/SN59	100µF/250V	BSN 1000 L307-A	MZN 1000-S	100µF/250V
	SON-T 1000W	BSN 1000 L407-I-A	SN59	100µF/250V			