

Electronic Gear	Lamp Power	SOFT START	# gear per 16A type B circuit breaker
HID-PV Compact /S, /I, /P	35	NO	24
HID-AV Compact /I, /C	35	YES	58
HID-PV Compact TWIN /S	2 x 35	NO	14
HID-PV Compact TWIN /I	2 x 35	YES	20 *
HID-PV Compact /S, /I, /P	70	NO	20
HID-AV Compact /I, /C	70	YES	32
HID-PV Compact TWIN /S	2 x 70	NO	10
HID-PV Compact TWIN /I	2 x 70	YES	14
HID-PV Compact /S	100	NO	7
HID-PV Compact /I	100	YES	17
HID-PV Compact /S	150	NO	6
HID-PV Compact /I	150	NO	6

* To be verified