

CERTIFICATE

Issued to:
Applicant:
Philips Lighting B.V.
High Tech Campus 45
5656 AE Eindhoven, The Netherlands

Licensee:
Philips Lighting B.V.
High Tech Campus 45
5656 AE Eindhoven, The Netherlands

Product : LED driver
Trade name(s) : PHILIPS
Type(s)/model(s) : CertaDrive 25W/m 0.6A 42V 230V, CertaDrive 30W/m 0.7A 42V 230V,
CertaDrive 34W/m 0.8A 42V 230V, CertaDrive 40W/m 0.9A 44V 230V and
CertaDrive 41W/m 1.05A 39V 230V

The product and any acceptable variation thereto is specified in the Annex to this certificate and the documents therein referred to.

DEKRA hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard EN 61347-1:2015, EN 61347-2-13:2014, EN 61347-2-13:2014/A1:2017, EN 62384:2006, EN 62384:2006/A1:2009 and EN 60598-1:2015
- an inspection of the production location according to CENELEC Operational Document CIG 021
- a certification agreement with the number 947556

DEKRA hereby grants the right to use the ENEC certification mark.

The ENEC certification mark may be applied to the product as specified in this certificate for the duration of the ENEC certification agreement and under the conditions of the ENEC certification agreement.


This certificate is issued on 22 March 2018 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 31-103118

DEKRA Certification B.V.



drs. G.J. Zoetbrood
Managing Director



Kate Xu
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	: LED driver
Trade name(s)	: PHILIPS
Type(s)/model(s)	: CertaDrive 25W/m 0.6A 42V 230V, CertaDrive 30W/m 0.7A 42V 230V, CertaDrive 34W/m 0.8A 42V 230V, CertaDrive 40W/m 0.9A 44V 230V and CertaDrive 41W/m 1.05A 39V 230V
Rated input voltage	: 220-240 V
Nature of supply	: ac
Rated frequency	: 50/60 Hz
Power factor	: 0,9C
Max.case temperature (tc)	: 80 °C
Description	: Built-in/ independent with SR cover

Product data – type CertaDrive 25W/m 0.6A 42V 230V

Rated input current	: 0,135 A
Rated input power	: 29 W
Output current	: 0,6 A
Output power	: 25 W
U-out	: 30-42 Vdc; 60 Vdc max.

Product data – type CertaDrive 30W/m 0.7A 42V 230V

Rated input current	: 0,15 A
Rated input power	: 33 W
Output current	: 0,7 A
Output power	: 30 W
U-out	: 30-42 Vdc; 60 Vdc max.

Product data – type CertaDrive 34W/m 0.8A 42V 230V

Rated input current	: 0,175 A
Rated input power	: 38 W
Output current	: 0,8 A
Output power	: 34 W
U-out	: 30-42 Vdc; 60 Vdc max.

Product data – type CertaDrive 40W/m 0.9A 44V 230V

Rated input current	: 0,2 A
Rated input power	: 44 W
Output current	: 0,9 A
Output power	: 40 W
U-out	: 30-44 Vdc; 60 Vdc max.

Product data – type CertaDrive 41W/m 1.05A 39V 230V

Rated input current	: 0,21 A
Rated input power	: 46 W
Output current	: 1,05 A
Output power	: 41 W
U-out	: 27-39 Vdc; 60 Vdc max.

TESTS**Test requirements**

EN 61347-1:2015
EN 61347-2-13:2014
EN 61347-2-13:2014/A1:2017
EN 62384:2006
EN 62384:2006/A1:2009
EN 60598-1:2015

Test result

The test results are laid down in DEKRA test file 602586100.

Additional information

Constant current type and with screwless terminal
Thermal protected

The tests were performed by the manufacturer under the conditions of the agreement concerning the manufacturer's right to conduct type tests for the KEMA-KEUR / ENEC certification system under supervision of DEKRA (CTF Stage 3).

The list of components is laid down at test report 6025861.50.

Conclusion

The examination proved that all requirements were met.

Factory locations

Hengdian Group Tospo Lighting Co., Ltd.
Hengdian Electronics Industrial Zone
Dongyang City, Jinhua
322118 Zhejiang, China

Taiwan Surface Mounting Technology (SuZhou) Co., Ltd.
No. 888 GanQuan Dong Road
Economic Technology Development Zone
WuJiang
215200 Jiangsu Province, China