

LED Transformers LED Transformer 60W 24V 220-240V PP

Product description

Philips full-electronic constant voltage LED Transformers are designed to operate 24VDC LED solutions used in general applications such as refrigerated display lighting, retail display lighting and linear accent lighting. They are specifically designed to ensure the highest performance with maximum robustness combined with a long lifetime.

Benefits

- SELV operating voltages, ensuring safety even if wiring or LED boards become damaged
- Energy savings through high efficiency
- Ultimate robustness, offering peace of mind and lower maintenance costs
- Easy to design-in and install
- Long lifetime

Features

- Independent use for Insulation Class II application
- Global approbations and certifications
- Stable output voltage
- Wide ambient temperature range
- Protection against overpower and overvoltage
- Output short-circuit shutdown feature with automatic restart

Applications

Retail display lighting, linear accent lighting and refrigerated display lighting

- Shelf lighting
- Cove lighting
- Facade accent lighting
- Coolers and freezers

Electrical input data

Specification item	Value	Unit	Condition
Rated input voltage range	220 240	Vac	Performance
Rated input voltage range	198 264	Vac	Operational safety
Rated input frequency	50 60	Hz	Performance
Rated input frequency	45 66	Hz	Operational safety
Rated input current	0.30	A	230Vac, @ rated output power
Rated input power	69	W	230Vac, @ rated output power
Power factor	0.98		230Vac, @ rated output power.
Total harmonic distortion	10	%	230Vac, @ rated output power.
Efficiency (typ)	87	%	230Vac, @ rated output power.

Electrical output data


Specification item	Value	Unit	Condition
Regulation method	Constant Voltage		Rated output voltage = 24VDC
Output voltage range	22.8 25.2	Vdc	@ output current range 1.5 2.5A
Output current range	0.1 2.5	Adc	
Output voltage ripple	< 2	V _{pp}	
Rated output power	60	W	
Line regulation	< 1	%	
Load regulation	< 3	%	
Turn-on delay	< 0.5	S	With Integrade engine 24VDC module at rated output power
Output voltage rise time	≤ 50	ms	
Hold-up time	≥10	ms	

Logistical data

Specification item	Value
Product name	LED Transformer 60W 24V 220-240V PP
Order code	695132 00
Logistic code 12NC	9290 021 06280
Pieces per box	20

Wiring & Connections

Specification item	Value	Unit	Condition
Input cable cross-section	2 x 0.75	mm ²	Lenght: 1.5m, VDE certified with C plug
IVoltage rating	300	V	
Input wire strip length	6 7	mm	
Output cable cross-section	2 x 0.8	mm ²	Length: 20cm
Junction box	8	Fold	
Strain relief screw max. torque	0.5	Nm	
Connector screw max. torque	0.5	Nm	
Maximum output cable length	2.5	m	CISPR15: between driver and LED module




Insulation

Insulation	Mains	LED
Mains		SELV (double)
LED	SELV (double)	

Dimensions and weight

Specification item	Value	Unit	Condition
Length (A1)	250.0	mm	
Width (B1)	40.0	mm	
Height (C1)	30.0	mm	
Fixing hole distance (A2)	240.0	mm	Fixing hole diameter (D): 4.2 mm
Fixing hole distance (B2)	29.0	mm	
Weight	390	gram	
Juction box Length (G)	60.0	mm	
Juction box Width (E)	30.0	mm	
Juction box Height (K)	13.0	mm	
Cable hole diameter (J)	4.0	mm	
Cable hole distance (H)	10.0	mm	
Output cable Length (F)	18	cm	
Input cable Length (L)	1.5	m	



Operational temperatures and humidity

Specification item	Value	Unit	Condition
Driver ambient temperature	-20 +45	°C	At rated output power. Higher ambient temperature allowed as long as Tcase-max is not exceeded.
Tcase-min	-20	°C	
Tcase-max	+85	°C	Max. steady-state Tcase
Tcase-life	+85	°C	For rated driver lifetime
Maximum housing temperature	110	°C	In case of failure
Relative humidity	10 90	%	Non-condensing
Ingress Protection *	IP20		
Noise and hum	≤ 20	dB(A)	

*: The LED Transformer is primarily intended for independent use. It must not be exposed including but not limited to snow, water and ice or any other chemical agent which may have an adverse affect on driver operation and performance. Exposure may lead to driver failure. It is the luminaire manufacturer's / installer's responsibity to prevent exposure.

Storage temperature and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-20 +80	°C	
Relative humidity	5 95	%	Non-condensing

Lifetime

Specification item	Value	Unit	Condition
Rated driver lifetime	50,000	hours	Tcase ≤ Tcase-life. Maximum failures = 10%. See graph.

Features


Specification item	Value	Remark	Condition
Open load protection	Yes		U _{out} (open circuit) = 31V max.
Short-circuit protection	Yes		Hiccup mode, automatic recovering
Overpower protection	Yes		Automatic recovering
Overheating protection	Yes		Automatic recovering
Hot wiring	Yes		
Suitable insulation class applications	II		Per IEC60598

Certificates and standards

Specification item	Value
Approval marks	CE / ENEC / F / MM / 110 / Double-insulated / Independent / SELV

Inrush current

Specification item	Value	Unit	Condition
Inrush current I _{peak} (typ)	21	A	Input voltage 230Vac
Inrush current T _{width} (typ)	150	μs	Input voltage 230Vac
Max. recommended number of drivers	37	pcs	MCB/melting fuse 16A



MCB/fuse	Rating	Recommended number of drivers*
B,C	6A	14
B,C	10A	23
B,C	13A	30
B,C	16A	37
B,C	20A	47
B,C	25A	59


- Specified inrush current values apply for mains impedance of 200m Ω + 400 μH - Twidth specified at 50% of Ipeak

* : please check that cable cross sectional area corresponds with MCB/fuse rating and type


Surge immunity

Specification item	Value	Unit	Condition
Mains surge immunity (diff. mode)	1 / 0.5	kV / kA	L-N, acc. IEC61000-4-5. 2 Ohm, 1.2/50us, 8/20us







Driver efficiency versus output power



Input current THD versus output power







©2021 Signify Holding, IBRS 10461, 5600 VB, NL. All rights reserved. UK importer address: Signify Commercial UK Limited, 3, Guildford Business Park, GU2 8XG

The information provided herein is subject to change without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners. Date of release: March 11, 2020 v5

www.philips.com/oem