



EC Declaration of Conformity

We, Philips Lighting B.V.
BG LS&E
 Mathildelaan 1
 5611 BD Eindhoven
 The Netherlands

Internal Ref. Nr.: BMS-BLHI-QUA-804-OT
Year in which CE Mark was first affixed: 2006

Declare under our responsibility for the product(s):

Product Range:	Ceramic Discharge metal Halide Lamps
Product Code:	please refer to attached appendix

The designated product(s) is (are) in conformity with the essential requirements of the following European Directives and harmonized standards:

Low Voltage Directive (LVD), 2006/95/EC, date of issue 12 December 2006
<ul style="list-style-type: none"> • EN 62035:2000 with amendments to A2:2012 • EN 60061-1:1993+amendments to A48:2012 • EN 60061-4:2003+amendments to A14:2011 • EN 61167 :1994+amendments A3:1998 • EN 62471 : 2008

Restriction of hazardous substances directive 2011-65-EU
EN 50581:2012

and are produced under a quality scheme at least in conformity with ISO 9001, ISO 14001 and OHSAS 18001.

Signature:

Name:	Jan Stoffels	Hans Bellemans
Function:	Global Technology Manager BG LS&E	Quality Manager BG LS&E
Contact address:	Mathildelaan 1 5611 BD Eindhoven The Netherlands	Mathildelaan 1 5611 BD Eindhoven The Netherlands
Date:	2013-06-25	2013-06-25

Appendix: Specific products that includes the CE-declaration

Issue date appendix: 2013-06-25

Product Code	Product name
928061405117	MASTERColor CDM-T Warm T6 70W/925 G12
928061405131	MASTERColour CDM-T Warm 70W/925 G12
928061505131	MASTERColour CDM-TC Warm 70W/925 G8.5
928063705130	MASTERC CDM-TD Essential 70W/830 RX7s
928063805130	MASTERC CDM-TD Essential 150W/830 RX7s
928063905130	MASTERC CDM-TD Essential 70W/842 RX7s
928064105130	MASTERC CDM-TD Essential 150W/842 RX7s
928064205110	MASTERC CDM-T Elite 100W/942 G12
928064205115	MASTERColor CDM-T Elite 100W/942 G12 1CT
928064205131	MASTERC CDM-T Elite 100W/942 G12 1CT
928064205177	MASTERC CDM-T Elite 100W/942 G12
928064305115	MASTERC CDM-T Evolution 35W/930 G12
928064305131	MC CDM-T Evolution 35W/930 G12
928064305177	MC CDM-T Evolution 35W/930 G12 OEM
928064405115	MASTERC CDM-TC Evolution 35W/930 G8.5
928064405131	MC CDM-TC Evolution 35W/930 G8.5
928064405177	MC CDM-TC Evolution 35W/930 G8.5 OEM
928064705115	MASTERC CDM-T Evolution 20W/930 G12
928064705131	MC CDM-T Evolution 20W/930 G12
928064705177	MC CDM-T Evolution 20W/930 G12 OEM
928064805115	MASTERC CDM-TC Evolution 20W/930 G8.5
928064805131	MC CDM-TC Evolution 20W/930 G8.5
928064805177	MC CDM-TC Evolution 20W/930 G8.5 OEM
928070900630	MASTERC CDM-R 35W/830 E27 PAR30L 10D 1CT
928070900691	MASTERC CDM-R 35W/830 E27 PAR30L 10D 1CT
928071000630	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT
928071000650	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT
928071000691	MASTERC CDM-R 35W/830 E27 PAR30L 30D 1CT
928071100630	MASTERC CDM-R 70W/830 E27 PAR30L 10D 1CT
928071100650	MASTERC CDM-R 70W/830 E27 PAR30L 10D 1CT
928071100691	MASTERC CDM-R 70W/830 E27 PAR30L 10D 1CT
928071200630	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT
928071200650	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT
928071200691	MASTERC CDM-R 70W/830 E27 PAR30L 40D 1CT
928080015110	MC CDM-T Elite 50W/942 G12 1CT
928080015118	MC CDM-T Elite 50W/942 G12 1CT
928080015131	MASTERC CDM-T Elite 50W/942 G12 1CT
928080015177	MASTERC CDM-T Elite 50W/942 G12 OEM
928080115110	MC CDM-TC Elite 50W/942 G8.5 1CT
928080115117	MC CDM-TC Elite 50W/942 G8.5 1CT

928080115131	MASTERC CDM-TC Elite 50W/942 G8.5 1CT
928080115177	MASTERC CDM-TC Elite 50W/942 G8.5 OEM
928082205110	MASTERC CDM-TD 70W/830 RX7s 1CT/12
928082205115	CDM-TD 70W/830 RX7s T6 CL
928082205117	CDM-TD 70W/830 RX7s T6 CL
928082205125	MASTERC CDM-TD 70W/830 RX7s 1CT/12
928082205178	MASTERC CDM-TD 70W/830 RX7s OEM 1CT/12
928082305105	MASTERC CDM-T 70W/830 G12
928082305110	CDM-T 70W /830 G12.1CT/12
928082305115	CDM-T 70W/830 G12 T6 CL
928082305117	CDM-T 70W/830 G12 T6 CL
928082305125	MASTERC CDM-T 70W/830 G12 1CT/12
928082305166	MASTERC CDM-T 70W/830 G12 1CT/12
928082305176	MASTERC CDM-T 70W/830 G12 1CT/12
928082305192	MASTERC CDM-T 70W/830 G12 1CT/12
928083105105	MASTERC CDM-T 35W/830 G12
928083105110	CDM-T 35W /830 G12.1CT/12
928083105115	CDM-T 35W/830 G12 T6 CL
928083105117	CDM-T 35W/830 G12 T6 CL
928083105122	CDM35/T6/830 12PK (GR-223289)
928083105125	MASTERC CDM-T 35W/830 G12 1CT/12
928083105166	MASTERC CDM-T 35W/830 G12 1CT/12
928083105176	MASTERC CDM-T 35W/830 G12 1CT/12
928083105192	MASTERC CDM-T 35W/830 G12 1CT/12
928083605110	CDM-TD 150W /830 RX7S.1CT/12
928083605116	CDM 150/TD/830 12PK
928083605133	MASTERC CDM-TD 150W/830 RX7s 1CT
928083605177	MASTERC CDM-TD 150W/830 RX7s 1CT
928083705105	MASTERC CDM-T 150W/830 G12
928083705110	CDM-T 150W /830 G12.1CT/12
928083705115	CDM150/T6/830 12PK
928083705116	CDM150/T6/830 12PK
928083705125	MASTERC CDM-T 150W/830 G12 1CT
928083705166	MASTERC CDM-T 150W/830 G12 1CT
928083705176	MASTERC CDM-T 150W/830 G12 1CT
928084000630	CDM-R 35W/830 E27 PAR20 30D 1CT/12
928084000650	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT
928084000691	MASTERC CDM-R 35W/830 E27 PAR20 30D 1CT
928084100603	MASTERC CDM-R 35W/830 E27 PAR20 10D 1CT
928084100630	CDM-R 35W/830 PAR20 10D 1CT/12
928084100650	MASTERC CDM-R 35W/830 E27 PAR20 10D 1CT
928084100691	MASTERC CDM-R 35W/830 E27 PAR20 10D 1CT
928084505105	MASTERC CDM-T 70W/942 G12
928084505110	CDM-T 70W /942 G12.1CT/12
928084505115	CDM-T 70W/942 G12 T6 CL
928084505117	CDM-T 70W/942 G12 T6 CL
928084505131	MASTERC CDM-T 70W/942 G12 1CT/12

928084505166	MASTERC CDM-T 70W/942 G12 1CT/12
928084505175	MASTERC CDM-T 70W/942 G12 1CT/12
928084505192	MASTERC CDM-T 70W/942 G12 1CT/12
928084605105	MASTERC CDM-T 150W/942 G12
928084605110	CDM-T 150W /942 G12.1CT/12
928084605115	CDM150/T6/942 12PK
928084605116	CDM150/T6/942 12PK
928084605122	CDM150/T6/942 12PK (GR-373696)
928084605131	MASTERC CDM-T 150W/942 G12 1CT
928084605166	MASTERC CDM-T 150W/942 G12 1CT
928084605175	MASTERC CDM-T 150W/942 G12 1CT
928084705110	MASTERC CDM-TD 70W/942 RX7s 1CT
928084705115	CDM-TD 70W/942 RX7s T6 CL
928084705133	MASTERC CDM-TD 70W/942 RX7s 1CT/12
928084705177	MASTERC CDM-TD 70W/942 RX7s OEM 1CT/12
928084805110	MASTERC CDM-TD 150W/942 RX7s 1CT
928084805122	CDM 150/TD/942 12PK (GR-373712)
928084805133	MASTERC CDM-TD 150W/942 RX7s 1CT
928084805177	MASTERC CDM-TD 150W/942 RX7s 1CT
928085205105	MASTERC CDM-TC 35W/830 G8.5
928085205110	CDM-TC 35W /830 G8.5.1CT/12
928085205115	CDM-TC 35W/830 G8.5 T4 CL
928085205117	CDM-TC 35W/830 G8.5 T4 CL
928085205125	MASTERC CDM-TC 35W/830 G8.5 1CT/12
928085205166	MASTERC CDM-TC 35W/830 G8.5 1CT/12
928085205175	MASTERC CDM-TC 35W/830 G8.5 UVbi-Q OEM
928085909230	MASTERC CDM-TP 70W/842 PG12-2 1CT/12
928086209230	MASTERC CDM-TP 150W/942 PGX12-2 1CT/12
928086505105	MASTERC CDM-TC 70W/830 G8.5
928086505110	CDM-TC 70W/830.1CT/12
928086505115	CDM-TC 70W/830 G8.5 T4 CL
928086505117	CDM-TC 70W/830 G8.5 T4 CL
928086505131	MASTERC CDM-TC 70W/830 G8.5 1CT/12
928086505166	MASTERC CDM-TC 70W/830 G8.5 1CT/12
928086505175	MASTERC CDM-TC 70W/830 G8.5 UVbi-Q OEM
928086909230	MASTERC CDM-TP 70W/830 PG12-2 1CT/12
928087009230	MASTERC CDM-TP 150W/830 PGX12-2 1CT/12
928087905110	MASTERC CDM-Tm 20W/830 PGJ5 1CT/12
928087905115	CDM20/TM/830 12PK
928087905119	CDM20/TM/830 12PK
928087905130	MASTERC CDM-Tm Mini 20W/830 PGJ5 1CT/12
928088205305	CDM-R111 35W/830 GX8.5 SP 10D 1CT
928088205306	CDM-R111 35W/830 GX8.5 SP 10D 1CT
928088205330	MASTERC CDM-R111 35W/830 GX8.5 10D 1CT/6
928088305305	CDM-R111 35W/830 GX8.5 NFL 24D 1CT
928088305306	CDM-R111 35W/830 GX8.5 NFL 24D 1CT
928088305330	MASTERC CDM-R111 35W/830 GX8.5 24D 1CT/6

928088405305	CDM-R111 35W/830 GX8.5 FL 40D 1CT
928088405306	CDM-R111 35W/830 GX8.5 FL 40D 1CT
928088405330	MASTERC CDM-R111 35W/830 GX8.5 40D 1CT/6
928089300630	MASTERC CDM-R 70W/942 E27 PAR30L 10D 1CT
928089300691	MASTERC CDM-R 70W/942 E27 PAR30L 10D 1CT
928089400603	MASTERC CDM-R 70W/942 E27 PAR30L 40D 1CT
928089400630	MASTERC CDM-R 70W/942 E27 PAR30L 40D 1CT
928089400691	MASTERC CDM-R 70W/942 E27 PAR30L 40D 1CT
928089700630	MASTERC CDM-R 70W/942 E27 PAR30L 30D 1CT
928089700691	MASTERC CDM-R 70W/942 E27 PAR30L 30D 1CT
928089805130	MASTERC CDM-T 250W/830 G12 1CT/12
928089805131	MASTERC CDM-T 250W/830 G12 1CT/12
928089900630	MASTERC CDM-R 70W/830 E27 PAR30L 30D 1CT
928089900691	MASTERC CDM-R 70W/830 E27 PAR30L 30D 1CT
928091305305	CDM-R111 70W/830 GX8.5 SP 10D 1CT
928091305306	CDM-R111 70W/830 GX8.5 SP 10D 1CT
928091305330	MASTERC CDM-R111 70W/830 GX8.5 10D 1CT/6
928091405305	CDM-R111 70W/830 GX8.5 NFL 24D 1CT
928091405306	CDM-R111 70W/830 24DG 6PK
928091405330	MASTERC CDM-R111 70W/830 GX8.5 24D 1CT/6
928091505305	CDM-R111 70W/830 GX8.5 FL 40D 1CT
928091505306	CDM-R111 70W/830 GX8.5 FL 40D 1CT
928091505330	MASTERC CDM-R111 70W/830 GX8.5 40D 1CT/6
928091700630	MASTERC CDM-R 35W/942 E27 PAR20 30D 1CT
928091700691	MASTERC CDM-R 35W/942 E27 PAR20 30D 1CT
928091900630	MASTERC CDM-R 35W/942 E27 PAR20 10D 1CT
928091900691	MASTERC CDM-R 35W/942 E27 PAR20 10D 1CT
928093105330	MASTERC CDM-R111 20W/830 GX8.5 10D 1CT/6
928093205330	MASTERC CDM-R111 20W/830 GX8.5 24D 1CT/6
928093805105	MASTERC CDM-TC 35W/842 G8.5
928093805110	MASTERC CDM-TC 35W/842 G8.5.1CT/12
928093805125	MASTERC CDM-TC 35W/842 G8.5 1CT/12
928093805166	MASTERC CDM-TC 35W/842 G8.5 1CT/12
928093805177	MASTERC CDM-TC 35W/842 G8.5 OEM
928093905110	MASTERC CDM-Tm 35W/930 PGJ5 1CT/12
928093905115	CDM 35/TM/930
928093905119	CDM-TM 35W/930 1CT
928093905130	MASTERC CDM-Tm Mini 35W/930 PGJ5 1CT/12
928094205131	MASTERC CDM-T 250W/942 G12 1CT/12
928094305105	MASTERC CDM-T 35W/842 G12
928094305110	CDM-T 35W/842 G12.1CT/12
928094305125	MASTERC CDM-T 35W/842 G12 1CT/12
928094305166	MASTERC CDM-T 35W/842 G12 1CT/12
928094305177	MASTERC CDM-T 35W/842 G12 OEM
928094305192	MASTERC CDM-T 35W/842 G12 1CT/12
928094605105	MASTERC CDM-TC 70W/842 G8.5
928094605110	CDM-TC 70W/842 G8.5.1CT/12

928094605115	CDM-TC 70W/842 T4
928094605117	CDM70/TC/842 12PK
928094605131	MASTERC CDM-TC - 70W/842 G8.5 1CT/12
928094605166	MASTERC CDM-TC - 70W/842 G8.5 1CT/12
928094605175	MASTERC CDM-TC 70W/842 G8.5 UVbl-Q OEM
928094705125	MASTERC CDM-T Elite 150W/930 G12 1CT/12
928094705177	MASTERC CDM-T Elite 150W/930 G12 OEM
928096405330	MASTERC CDM-R111 35W/942 GX8.5 10D 1CT/6
928096505330	MASTERC CDM-R111 35W/942 GX8.5 24D 1CT
928096605330	MASTERC CDM-R111 35W/942 GX8.5 40D 1CT/6
928183205110	MASTERC CDM-T Elite 100W/930 G12.1CT/12
928183205115	MASTERCColor CDM-T Elite 100W/930.1CT/12
928183205117	MASTERCColor CDM-T Elite 100W/930.1CT/12
928183205125	MASTERC CDM-T Elite 100W/930 G12 1CT/12
928183205177	MASTERC CDM-T Elite 100W/930 G12 OEM
928183305115	CDM-T 20W830 G12 T6 CL 1CT/12
928183305117	CDM20/T/830 Elite
928183305125	MASTERC CDM-T 20W/830 G12 1CT/12
928183305177	MASTERC CDM-T 20W/830 G12 OEM
928183405105	MASTERC CDM-TC 20W/830 G8.5
928183405115	CDM20/TC/830 Elite
928183405117	CDM20/TC/830 Elite
928183405125	MASTERC CDM-TC 20W/830 G8.5 1CT/12
928183405177	MASTERC CDM-TC 20W/830 G8.5 OEM
928183505115	MASTERC CDM-Tm mini 20W/830 GU6.5 1CT
928183505119	MASTERC CDM-Tm mini 20W/830 GU6.5.1CT
928183505130	MASTERC CDM-Tm Mini GU6.5 20W/830 1CT/12
928183505147	LIGHT SOURCE HALIDE 20W 3000K 1CT/12
928183505177	MASTERC CDM-Tm Mini 20W/830 GU6.5 OEM
928184200630	MC CDM-R Elite 70W/930 E27 PAR30L 10D
928184300630	MC CDM-R Elite 70W/930 E27 PAR30L 30D
928184400630	MC CDM-R Elite 70W/930 E27 PAR30L 40D
928184500609	MC CDM-R Elite 70W/930 E26 PAR30L 10D
928184800630	MC CDM-R Elite 35W/930 E27 PAR30L 10D
928184900630	MC CDM-R Elite 35W/930 E27 PAR30L 30D
928185205110	MC CDM-T ELITE 35W/930 G12 1CT/12
928185205115	MASTERCColor CDM-T Elite 35W/930 G12 1CT
928185205117	MASTERCColor CDM-T Elite 35W/930 G12 1CT
928185205131	MASTERC CDM-T Elite 35W/930 G12 1CT/12
928185205166	MASTERC CDM-T Elite 35W/930 G12 1CT/12
928185205177	MASTERC CDM-T Elite 35W/930 G12 OEM
928185205191	MASTERC CDM-T Elite 35W/930 G12 1CT/12
928185305110	MC CDM-T Elite 70W/930 G12 1CT/12
928185305115	MASTERCColor CDM-T Elite 70W/930 G12 1CT
928185305117	MASTERCColor CDM-T Elite 70W/930 G12 1CT
928185305131	MASTERC CDM-T Elite 70W/930 G12 1CT/12
928185305166	MASTERC CDM-T Elite 70W/930 G12 1CT/12

928185305177	MASTERC CDM-T Elite 70W/930 G12 OEM
928185305191	MASTERC CDM-T Elite 70W/930 G12 1CT/12
928187405115	MASTERC CDM-Tm Elite Mini 35W/930 GU6.5
928187405119	MASTERC CDM-Tm Elite Mini 35W/930 GU6.5
928187405130	MC CDM-Tm Elite Mini 35W/930 GU6.5 1CT
928187405177	MC CDM-Tm Elite Mini 35W/930 GU6.5 OEM
928189105110	MC CDM-TC Elite 35W/930 G8.5 1CT/12
928189105115	MASTERColor CDM-TC Elite 35W/930 G8.5
928189105117	MASTERColor CDM-TC Elite 35W/930 G8.5
928189105131	MASTERC CDM-TC Elite 35W/930 G8.5 1CT/12
928189105166	MASTERC CDM-TC Elite 35W/930 G8.5 1CT/12
928189105177	MASTERC CDM-TC Elite 35W/930 G8.5 OEM
928189505110	MC CDM-TC Elite 70W/930 G8.5 1CT/12
928189505115	MASTERColor CDM-TC ELITE 70W/930 G8.5
928189505117	MASTERColor CDM-TC ELITE 70W/930 G8.5
928189505131	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12
928189505166	MASTERC CDM-TC Elite 70W/930 G8.5 1CT/12
928189505177	MASTERC CDM-TC Elite 70W/930 G8.5 OEM
928191005315	CDM-Rm Elite Mini 20W/830 GX10 MR16 10D
928191005318	CDM-Rm Elite Mini 20W/830 GX10 MR16 10D
928191005330	CDM-Rm Mini 20W/830 GX10 MR16 10D
928191005331	CDM-Rm Mini 20W/830 GX10 MR16 10D
928191105315	CDM-Rm Elite Mini 20W/830 GX10 MR16 25D
928191105318	CDM-Rm Elite Mini 20W/830 GX10 MR16 25D
928191105330	CDM-Rm Mini 20W/830 GX10 MR16 25D
928191105331	CDM-Rm Mini 20W/830 GX10 MR16 25D
928191205315	CDM-Rm Elite Mini 20W/830 GX10 MR16 40D
928191205318	CDM-Rm Elite Mini 20W/830 GX10 MR16 40D
928191205330	CDM-Rm Mini 20W/830 GX10 MR16 40D
928191205331	CDM-Rm Mini 20W/830 GX10 MR16 40D
928191705110	MASTERColour CDM-T Elite 50W/930 G12
928191705115	CDM50/T6/930 ELITE 12PK
928191705118	CDM50/T6/930 ELITE 12PK
928191705131	MASTERC CDM-T Elite 50W/930 G12 1CT/12
928191705177	MASTERC CDM-T Elite 50W/930 G12 OEM
928191805110	MASTERColour CDM-TC 50W/930 G8.5 1CT/12
928191805115	MasterColor CDM-TC 50W/930 G8.5
928191805117	MasterColor CDM-TC 50W/930 G8.5
928191805131	MASTERC CDM-TC Elite 50W/930 G8.5 1CT/12
928191805177	MASTERC CDM-TC Elite 50W/930 G8.5 OEM
928191905131	MC CDM-T Elite Light Boost 70W/930 G12
928192005131	MC CDM-T Elite Light Boost 70W/942 G12
928192105131	MC CDM-TC Elite Light Boost 70W/930 G8.5
928192205131	MC CDM-TC Elite Light Boost 70W/942 G8.5
928192305309	MC CDM-Rm Mini 20W/830 GX10 MR16 10D
928192405309	MC CDM-Rm Mini 20W/830 GX10 MR16 25D
928192505309	MC CDM-Rm Mini 20W/830 GX10 MR16 40D

928192605310	MC CDM-Rm Mini 35W/942 GX10 MR16 15D
928192605330	CDM-Rm Mini 35W/942 GX10 MR16 15D
928192705310	MC CDM-Rm Mini 35W/942 GX10 MR16 25D
928192705330	CDM-Rm Mini 35W/942 GX10 MR16 25D
928192805310	MC CDM-Rm Mini 35W/942 GX10 MR16 40D
928192805330	CDM-Rm Mini 35W/942 GX10 MR16 40D
928193105310	CDM-Rm Elite Mini 50W/930 GX10 MR16 60D
928193105319	CDM-Rm Elite Mini 50W/930 GX10 MR16 60D
928193105330	CDM-Rm Elite Mini 50W/930 GX10 MR16 60D
928193205310	CDM-Rm Elite Mini 50W/930 GX10 MR16 25D
928193205315	CDM-Rm Elite Mini 50W/930 GX10 MR16 25D
928193205319	CDM-Rm Elite Mini 50W/930 GX10 MR16 25D
928193205330	CDM-Rm Elite Mini 50W/930 GX10 MR16 25D
928193305310	CDM-Rm Elite Mini 50W/930 GX10 MR16 40D
928193305315	CDM-Rm Elite Mini 50W/930 GX10 MR16 40D
928193305319	CDM-Rm Elite Mini 50W/930 GX10 MR16 40D
928193305330	CDM-Rm Elite Mini 50W/930 GX10 MR16 40D
928193605110	MASTERC colour CDM-T Elite 35W/942 G12
928193605131	MASTERC CDM-T Elite 35W/942 G12 1CT
928193605177	MASTERC CDM-T Elite 35W/942 G12 OEM
928193705110	MASTERC colour CDM-T Elite 70W/942 G12
928193705115	MASTERC CDM-T Elite 70W/942 G12
928193705117	MASTERC CDM-T Elite 70W/942 G12
928193705131	MASTERC CDM-T Elite 70W/942 G12 1CT
928193705177	MASTERC CDM-T Elite 70W/942 G12 OEM
928193805110	MASTERC colour CDM-TC Elite 35W/942 G8.5
928193805117	CDM-TC Elite 35W/942 G8.5 1CT
928193805131	MASTERC CDM-TC Elite 35W/942 G8.5 1CT
928193805177	MASTERC CDM-TC Elite 35W/942 G8.5 OEM
928193905110	MASTERC colour CDM-TC Elite 70W/942 G8.5
928193905115	CDM-TC Elite 70W/942 G8.5 1CT
928193905117	CDM-TC Elite 70W/942 G8.5 1CT
928193905131	MASTERC CDM-TC Elite 70W/942 G8.5 1CT
928193905177	MASTERC CDM-TC Elite 70W/942 G8.5 OEM
928194605310	CDM-Rm Elite Mini 35W/930 GX10 MR16 10D
928194605315	CDM-Rm Elite Mini 35W/930 GX10 MR16 10D
928194605319	CDM-Rm Elite Mini 35W/930 GX10 MR16 10D
928194605330	CDM-Rm Elite Mini 35W/930 GX10 MR16 10D
928194705310	CDM-Rm Elite Mini 35W/930 GX10 MR16 25D
928194705315	CDM-Rm Elite Mini 35W/930 GX10 MR16 25D
928194705319	CDM-Rm Elite Mini 35W/930 GX10 MR16 25D
928194705330	CDM-Rm Elite Mini 35W/930 GX10 MR16 25D
928194805310	CDM-Rm Elite Mini 35W/930 GX10 MR16 40D
928194805315	CDM-Rm Elite Mini 35W/930 GX10 MR16 40D
928194805319	CDM-Rm Elite Mini 35W/930 GX10 MR16 40D
928194805330	CDM-Rm Elite Mini 35W/930 GX10 MR16 40D
928196405115	MASTERC color CDM-T Fresh 70W/740 G12

928196405117	MASTERCOLOR CDM-T Fresh 70W/740 G12
928196405131	MASTERCOLOR CDM-T Fresh 70W/740 G12 1CT
928196505115	MASTERC CDM-Tm Elite Mini 50W/930 GU6.5
928196505119	MASTERC CDM-Tm Elite Mini 50W/930 GU6.5
928196505130	MC CDM-Tm Elite Mini 50W/930 GU6.5
928196505177	MC CDM-Tm Elite Mini 50W/930 GU6.5 OEM