

PHILIPS LIGHTING B.V.

PHOTOMETRIC RESULTS

LVE18877

Lamp Data	CDM-T Elite+ 50W				Date:	2010-07-28 9:41:23 AM	
Description	LVE18877						
TestNumber	JACT2-BU-2						
File	LVE18877						
Comment	Set=230V Cone measurement: 5491 lm Kirsten Verheijen / GTD HID / Turnhout						
Ballast	HID PV C50/S CDM				Nominal Flux	5000 lm	
Conditions							
Protocol	37 Cones / 12 Cplanes				Operator	Philips	
	Cones 0-180 5/2 ; Cplanes 0-180 1						
Measured Values					Flux	5457.97 lm	
Power	55.0948 W	Voltage	230.114 V	Current	0.247 A		

Polar diagram LVE18877 / C-Plane measurement

