



Superior light quality gives merchandize its ultimate appeal

Better presentation makes products look more appealing, creates the ultimate shopping experience and maximizes the impact at the point-of-purchase. The new InteGrade premium white family LED lighting takes product attractiveness to the ultimate level and stimulates the desire to shop. It is designed to maximize product attractiveness through a combination of a superior light quality, excellent light distribution and state-of-the-art efficacy.

Illumination beyond your imagination

InteGrade premium white enhances whites and delivers astonishingly lively rich colors in chillers, freezers, serve overs and islands in food retail, and shelf lighting in fashion retail. This not only improves product attractiveness and enhances the shopping experience; it also brings economic and environmental benefits relating to energy consumption and cost-efficient maintenance.



With premium white,

you don't need to choose between light quality or energy efficiency. It offers both.

Every store strives to reinforce its brand

Food and fashion retailers pay careful attention to how customer perceive their stores. Brand image is important regardless of whether a retailer aims high or attracts budget shoppers. Premium white for applications where the quality of light and product perception is an important part of the shopping experience.

Step up to InteGrade for retail lighting

InteGrade premium white LED lighting in retail display cabinets make food and packaging look more attractive and appetizing. And in fashion retailing, it gives merchandize the extra appeal of amazing whites and astonishing colors. This new generation enables you to build tailor-made lighting solutions with superior light quality for cabinets, doors, canopies and shelves.

Take color rendering to the next level

The latest InteGrade gen 3
LED engines and fixtures are specially formulated for superior light quality. They take color rendering to the next level with superb whites and colors. We have unique optimized optic for each application, which direct light where it's needed. These include standard, uniform beam and narrow beam versions optimized for shelf, canopy and doors respectively. We optimized the color spectrum to enhance white performance and render astonishing lively rich colors while providing an outstanding efficacy up to 125 lumens per watt to keep energy consumption – and the cost of ownership – low. The LED technology delivers efficacy up to 125 lumens per watt to keep energy costs low.

One shop experience

ultimate shopping experience with consistent look and feel throughout stores. In addition to InteGrade premium white, we also offer Philips Fortimo SLM down- and spotlight modules with premium white for retail applications. This makes it possible for retailers to create a unified shopping experience with accent lighting and shelf lighting with the same unique color spectrum. It's a unique opportunity to guarantee one look and feel.

Build in innovative lighting with the flexibility, style and functionality today's stores are looking for

Maximum design flexibility and hassle-free installation

The ultra-thin InteGrade LED engines and fixtures provide more aesthetic design flexibility to enable you to build a variety of innovative refrigeration systems with the modern style and functionality that stores are looking for. Thanks to extensive range of engine lengths, color temperatures and accessories, InteGrade LED engines maximize design flexibility with a modular approach.

Fewer components needed

The miniaturized, ultra-thin engines and fixtures are easily integrated into display cabinets with plug and play simplicity. The standard engine lengths of 140, 575, 855, 1150 and 1430 mm correspond with the common sizes for most applications. This reduces the number of components you need per installation. And you can assemble custom length light-lines by combining modules. Fixtures (engine plus profile) are 1500 mm long. Design simplicity is assured with a range of mounting profiles, mounting clips, power cables and Philips Constant Voltage LED drivers. The accessories fit together for hassle-free installation.

The new Premium White portfolio

premium white version featuring uniform light distribution in chillers thanks to its breakthrough optical design. We have further expanded the portfolio with a brand new narrow beam engine and fixture for doors. They have more than double the lumen and lux levels for better product visibility.

Light where you want it

When mounted, the light sources are virtually out of sight, so they don't draw attention away from merchandize. For each specific application (shelf-, canopy- and door lighting), we have optimized the optic system. This ensures exceptional light distribution where it's needed. It also produces a continuous line of light without undesirable hot spots, glare or reflections on the merchandize. The result is brighter, more uniform product illumination, both horizontally and vertically. Merchandize looks more appealing.

Exceptionally long lifetime

Philips LEDs have minimal output degradation and color shift over time, so the light stays consistent throughout the long service life. Lifetime is an exceptional 50,000 hours







Standard modules for tailor-made solutions

InteGrade gen 3 premium white engines are available as high output 'vision' and standard 'value' types.

InteGrade gen 3 premium white for shelf lighting

Horizontally integrated modules fo shelf lighting in open- and closed cabinets

InteGrade narrow beam gen 3 premium white for lighting in chillers with doors

The narrow beam versions have extremely small dimensions for integration into doors and mullions where there is limited space to place a lighting solution. The unique optical system directs the light precisely where you want it, thus making optimum use of the light and energy. The modules are suitable for vertically integrated lighting in half-height and full-height cabinets.

InteGrade uniform beam gen 3 premium white for canopy lighting

provide uniform illumination over the full height of cabinet from the canopy.

InteGrade high flux premium white for canopy and chillers with doors

The high lumen and lux level in combination with superb optics ensure InteGrade high flux premium white delivers exceptionally uniform light distribution in combination with ultimate product visibility.

Key benefits of InteGrade premium white

Breakthrough performance

- Superior light quality thanks to an optimized color spectrum for enhanced white performance and astonishingly rich colors.
- One look and feel in stores for the ultimate shopping experience when combined with Premium White spot- and down lighting solutions.
- State-of-art efficacy up to 125 lumens per watt.
- Attention stays focused on the displayed products:
 - Revolutionary optics to direct the light where you want it.
 - Brand new canopy version featuring a uniform light distribution in the chillers due to its breakthrough optical design.
 - Brand new narrow beam engines and fixture for doors with more than double lumen and lux levels.
 - Continuous line of light without undesirable hot spots, glare or reflections.
- · High flux versions deliver high lumen in combination with high lux levels.

Maximum design flexibility

- Miniaturized design for aesthetic integration and focusing attention on displayed products.
- Extensive range of engine lengths, color temperatures and accessories.



Philips InteGrade LED products

InteGrade LED system gen 3 (premium white range)

InteGrade LED engines have been designed to match the most common application lengths, reducing the number of components needed per installation; yet maintaining the outstanding flexibility that its modular approach offers, enabling the creation of odd size lighting solutions to match every project specification.

Thanks to a range of engine lengths, fixtures, accessories like mounting profiles, mounting clips, power cables, and Philips Constant Voltage LED drivers the InteGrade LED system gen 3 offers maximum design flexibility and plug-and-play simplicity to enable a vast variety of innovative systems with style, modernity and functionality according the needs of the stores.

InteGrade engine value premium white gen 3

Product name	Power consumption	Lumen	Color Rendering Index	Correlated Color Temperature*	Product code
	W, typical ± 20%	lm, typical ± 20%	CRI, typical	К	(12NC)
InteGrade engine Va 140mm 930 PW G3	0,8	85	93	3000	929001567506
InteGrade engine Va 575mm 930 PW G3	3,4	380	93	3000	929001567606
InteGrade engine Va 855mm 930 PW G3	4,9	550	93	3000	929001567706
InteGrade engine Va 1150mm 930 PW G3	6,7	760	93	3000	929001567806
InteGrade engine Va 140mm 940 PW G3	0,8	90	93	4000	929001567906
InteGrade engine Va 575mm 940 PW G3	3,4	420	93	4000	929001568006
InteGrade engine Va 855mm 940 PW G3	4,9	600	93	4000	929001568106
InteGrade engine Va 1150mm 940 PW G3	6,7	840	93	4000	929001568206

^{*} Correlated color temperature within 5 SDCM range

For shelf lighting

InteGrade engine vision premium white gen 3

Product name	Power consumption	Lumen	Color Rendering Index	Correlated Color Temperature*	Product code
	W, typical ± 20%	lm, typical ± 20%	CRI, typical		(12NC)
InteGrade engine Vi 140mm 930 PW G3	1,6	170	93	3000	929001568306
InteGrade engine Vi 575mm 930 PW G3	6,9	750	93	3000	929001568406
InteGrade engine Vi 855mm 930 PW G3	10,1	1090	93	3000	929001568506
InteGrade engine Vi 1150mm 930 PW G3	13,8	1500	93	3000	929001568606
InteGrade engine Vi 140mm 940 PW G3	1,6	180	93	4000	929001568706
InteGrade engine Vi 575mm 940 PW G3	6,9	800	93	4000	929001568806
InteGrade engine Vi 855mm 940 PW G3	10,1	1160	93	4000	929001568906
InteGrade engine Vi 1150mm 940 PW G3	13,8	1600	93	4000	929001569006

For canopy lighting InteGrade engine uniform beam value premium white gen 3

Product name	Power consumption	Lumen	Color Rendering Index	Correlated Color Temperature*	Product code
	W, typical ± 20%	lm, typical ± 20%	CRI, typical	К	(12NC)
InteGrade engine UB Va 855mm 930 PW G3	9,6	940	93	3000	929001626606
InteGrade engine UB Va 1150mm 930 PW G3	12,8	1250	93	3000	929001626806
InteGrade engine UB Va 855mm 940 PW G3	9,6	1025	93	4000	929001626706
InteGrade engine UB Va 1150mm 940 PW G3	12,8	1350	93	4000	929001626906

^{*} Correlated color temperature within 5 SDCM range

InteGrade engine uniform beam vision premium white gen 3

Product name	Power consumption	Lumen	Color Rendering Index	Correlated Color Temperature*	Product code
	W, typical ± 20%	lm, typical ± 20%	CRI, typical		(12NC)
InteGrade engine UB Vi 140mm 930 PW G3	2,5	250	93	3000	929001572506
InteGrade engine UB Vi 575mm 930 PW G3	10	1000	93	3000	929001569706
InteGrade engine UB Vi 855mm 930 PW G3	15	1500	93	3000	929001569806
InteGrade engine UB Vi 1150mm 930 PW G3	20	2000	93	3000	929001569906
InteGrade engine UB Vi 140mm 940 PW G3	2,5	280	93	4000	929001572606
InteGrade engine UB Vi 575mm 940 PW G3	10	1100	93	4000	929001570006
InteGrade engine UB Vi 855mm 940 PW G3	15	1650	93	4000	929001570106
InteGrade engine UB Vi 1150mm 940 PW G3	20	2200	93	4000	929001570206

^{*} Correlated color temperature within 5 SDCM range

InteGrade engine narrow beam value premium white gen 3

Product name	Power consumption	Lumen	Color Rendering Index	Correlated Color Temperature*	Product code
	W, typical ± 20%	lm, typical ± 20%	CRI, typical		(12NC)
InteGrade engine NB Va 140mm 930 PW G3		115	93	3000	929001569106
InteGrade engine NB Va 575mm 930 PW G3	4,5	500	93	3000	929001569206
InteGrade engine NB Va 1430mm 930 PW G3		1230	93	3000	929001569306
InteGrade engine NB Va 140mm 940 PW G3		120	93	4000	929001569406
InteGrade engine NB Va 575mm 940 PW G3	4,5	530	93	4000	929001569506
InteGrade engine NB Va 1430mm 940 PW G3		1300	93	4000	929001569606

 $^{^{*}}$ Correlated color temperature within 5 SDCM range

InteGrade engine narrow beam vision premium white gen 3 Product specification

Product name	Power consumption	Lumen	Color Rendering Index	Correlated Color Temperature*	Product code
	W, typical ± 20%	lm, typical ± 20%	CRI, typical	К	(12NC)
InteGrade engine NB Vi 140mm 930 PW G3	2,7	280	93	3000	929001605406
InteGrade engine NB Vi 575mm 930 PW G3	10,9	1146	93	3000	929001681106
InteGrade engine NB Vi 1430mm 930 PW G3	27,2	2850	93	3000	929001571706
InteGrade engine NB Vi 140mm 940 PW G3	2,7	300	93	4000	929001605506
InteGrade engine NB Vi 575mm 940 PW G3	10,9	1200	93	4000	929001681206
InteGrade engine NB Vi 1430mm 940 PW G3	27,2	3100	93	4000	929001571806

^{*} Correlated color temperature within 5 SDCM range PW: premium white

InteGrade fixture narrow beam value premium white gen 3

Product name	Power consumption	Lumen	Color Rendering Index	Correlated Color Temperature*	Product code
	W, typical ± 20%	lm, typical ± 20%	CRI, typical	К	(12NC)
InteGrade F NB Va 1500mm 930 PW SD G3	11	1230	93	3000	929001572006
InteGrade F NB Va 1500mm 930 PW CTR G3	22	2460	93	3000	929001572106
InteGrade F NB Va 1500mm 940 PW SD G3	11	1300	93	4000	929001572206
InteGrade F NB Va 1500mm 940 PW CTR G3	22	2600	93	4000	929001572306

^{*} Correlated color temperature within 5 SDCM range

InteGrade fixture narrow beam vision premium white gen 3

Product name	Power consumption	Lumen	Color Rendering Index	Correlated Color Temperature*	Product code
	W, typical ± 20%	lm, typical ± 20%	CRI, typical		(12NC)
InteGrade F NB Vi 1500mm 930 PW SD G3	26,2	2850	93	3000	929001570306
InteGrade F NB Vi 1500mm 930 PW CTR G3	52,4	5700	93	3000	929001570406
InteGrade F NB Vi 1500mm 940 PW SD G3	26,3	3100	93	4000	929001570506
InteGrade F NB Vi 1500mm 940 PW CTR G3	52,6	6200	93	4000	929001570606

^{*} Correlated color temperature within 5 SDCM range

For canopy and chillers with doors InteGrade engine high flux premium white gen 3 Product specification

Product name	Power consumption	Lumen	Color Rendering Index	Correlated Color Temperature*	Product code
	W, typical ± 20%	lm, typical ± 20%	CRI, typical		(12NC)
InteGrade engine HF 140mm 930 PW G3	4,4	400	93	3000	929001605606
InteGrade engine HF 575mm 930 PW G3	17,5	1575	93	3000	929001605706
InteGrade engine HF 1150mm 930 PW G3	34,9	3150	93	3000	929001605806
InteGrade engine HF 140mm 940 PW G3	4,0	400	93	4000	929001605906
InteGrade engine HF 575mm 940 PW G3	16,1	1575	93	4000	929001606006
InteGrade engine HF 1150mm 940 PW G3	32,2	3150	93	4000	929001606106

^{*} Correlated color temperature within 5 SDCM range



Philips InteGrade LED products

InteGrade LED system premium white gen 3

Plug and play Philips constant voltage driver list	Product code
	(12NC)
LED transformer 60W 24VDC 120V PP	929002106080
LED transformer 60W 24VDC 220-240V PP	929002106280
LED transformer 100W 24VDC 120V PP	929002106180
LED transformer 100W 24VDC 220-240V PP	929002106380
LED transformer 150W 24VDC 220-240V PP	929002106480
Non-plug and play Philips constant voltage drivers	Product code
	(12NC)
LED power driver 20W 24VDC 100-240V	929000654006
LED power driver 80W 24VDC 120-240V	929001669406
LED power driver 100W 24VDC 120-240V	929001669506
LED power driver 150W 24VDC 120-240V	929002101980
LED power driver 240W 24VDC 120-240V	929002102080
LED transformer 20W 24VDC 120-277V	929002105580
LED transformer 40W 24VDC 120-277V	929002105680
LED transformer 60W 24VDC 120-277V	929002105780
LED transformer 60W 24VDC 220-240V	913710032267
LED transformer 100W 24VDC 120-277V	929002105880
LED transformer 120W 24VDC 220-240V	913710032567
LED transformer 150W 24VDC 220-240V	929002105980
Xitanium 77W 100-277V 3.2A XI077C320V024FNS1M *	929001708113
Xitanium 100W 100-277V 4.1A XI100C410V024FNS1M*	929000771913
LED driver outdoor 100W 100-240V 24V**	929000485303
* Only for NAM region	

^{*} Only for NAM reg ** Only for Japan

Accessories	Product code
	(12NC)
Clips	
InteGrade mounting clip shelf arm V2	929000957806
InteGrade engine clip shelf arm G2	929001516006
InteGrade engine mounting clip G2	929001516106
InteGrade mounting clip under shelf	929000643903
InteGrade engine clip magnetic	929001624606
InteGrade mounting clip canopy	929001571106
InteGrade engine clip mullion side	929001624506
InteGrade engine clip mullion center	929001624406
InteGrade mounting clip for T style prof	929000853213
Profiles	
InteGrade profile 875mm(34")	929000643413
InteGrade profile 1175mm(46")	929000643313
InteGrade profile 2000mm(79")	929000654413
InteGrade profile 2000mm(79") F style	929000654313
InteGrade profile 2000mm(79") L style	929000654513

InteGrade prof 2000mm(79") T style CTR	929000853013
InteGrade profile 2000mm(79") T style SD	929000853113
InteGrade profile 2356mm(93") M style	929000871313
Power cables - to connect engine to driver	
InteGrade power cable 0.7m white	929001625306
InteGrade power cable 1m(39") black	929000641014
InteGrade power cable 2.5m(98") black	929000641114
InteGrade cable 1m(39") black angle	929000644614
InteGrade cable 2.5m(98") black angle	929000644814
InteGrade power cable 1m(39") white	929000645614
InteGrade power cable 1.85m white	929001625206
InteGrade power cable 2.5m(98") white	929000644514
InteGrade cable 1m(39") white angle	929000644714
InteGrade cable 2.5m(98") white angle	929000644914
InteGrade power cable 6m white	929001624806
InteGrade spacer cable 113mm white	929001625106
InteGrade spacer cable 0.3m black	929001625006
InteGrade spacer cable 0.5m black	929000645014
InteGrade spacer cable 0.5m white	929000645114
InteGrade spacer cable M 0.7m 5.5c black	929001624706
InteGrade extension cab 1.5m(59") black	929000874413
InteGrade Y cable black	929000874313
Other accessories	
InteGrade engine lock inline	929000643713
InteGrade connector	929000959106
InteGrade magnet for M style profile	929000871413
InteGrade rotational bracket	929000874613
RDL track system	
RDL track	
RDL track 1800mm gr	929002113606
RDL track 1200mm gr	929002113706
RDL track 600mm gr	929002113806
Power cables – to connect the RDL track to the driver	
InteGrade track powercable 1.5m gr	929002113906
InteGrade track powercable 1.5m gr angle	929002114006
Track cables – to connect the engines to the RDL track	
InteGrade track cable M 0.7m gr angle	929002114106
InteGrade track cable 0.7m gr angle	929002114206
InteGrade track cable 0.3m transp angle	929002114306
InteGrade track cable 0.4m transp angle	929002114406
InteGrade track cable 0.5m transp angle	929002114506
* gr = Gray, M = Magnetic, transp = Transparent	





©2019 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

All other trademarks are owned by Signify Holding or their respective owners.