

**PHILIPS**

**InteGrade**

**LED**

InteGrade accessories



Datasheet

# InteGrade LED system

## **Compact linear LED lighting for ultimate shopping experience**

Thanks to a range of accessories, engine lengths, fixtures, color temperatures and Constant Voltage LED power drivers, the InteGrade LED system offers modular approach for maximum design flexibility. This enables a vast variety of innovative systems with style and functionality according the needs of the stores. The accessory table shows which accessories are suitable for your InteGrade LED system.

June 2017


## Ordering data

Commercial product name	EOC	12NC	Box quantity
InteGrade power cable 1m(39") black	8718291 218128 00	9290 006 41014	24
InteGrade power cable 1m(39") white	8718291 221401 00	9290 006 45614	24
InteGrade power cable 2.5m(98") black	8718291 221449 00	9290 006 41114	24
InteGrade power cable 2.5m(98") white	8718291 221487 00	9290 006 44514	24
InteGrade cable 1m(39") black angle	8718291 221364 00	9290 006 44614	24
InteGrade cable 1m(39") white angle	8718291 221425 00	9290 006 44714	24
InteGrade cable 2.5m(98") black angle	8718291 221463 00	9290 006 44814	24
InteGrade cable 2.5m(98") white angle	8718291 221500 00	9290 006 44914	24
InteGrade spacer cable 0.5m black	8718291 221524 00	9290 006 45014	24
InteGrade spacer cable 0.5m white	8718291 221548 00	9290 006 45114	24
InteGrade extension cable 1.5m(59") black	8718291 707257 00	9290 008 74413	24
InteGrade Y cable black	8718291 707233 00	9290 008 74313	24
InteGrade mounting clip canopy	8718696 716304 00	9290 015 71106	100
InteGrade engine mounting clip G2	9718696 657126 00	9290 015 16106	100
InteGrade engine clip shelf arm G2	8718696 657102 00	9290 015 16006	100
InteGrade mounting clip under shelf	8718291 218814 00	9290 006 43903	100
InteGrade mounting clip shelf arm V2	8718696 446454 00	9290 009 57806	100
InteGrade mounting clip for T style profile	8718291 676508 00	9290 008 53213	100
InteGrade rotational bracket	8718291 707691 00	9290 008 74613	100
InteGrade connector	8718696 462157 00	9290 009 59106	500
InteGrade engine lock inline	8718291 219514 00	9290 006 43713	100
InteGrade profile 875mm(34")	8718291 219538 00	9290 006 43413	48
InteGrade profile 1175mm(46")	8718291 219552 00	9290 006 43313	48
InteGrade profile 2000mm(79")	8718291 257899 00	9290 006 54413	48
InteGrade profile 2000mm(79") L style	8718291 257912 00	9290 006 54513	48
InteGrade profile 2000mm(79") F style	8718291 227892 00	9290 006 54313	24
InteGrade profile 2000mm(79") T style CTR	8718291 676461 00	9290 008 53013	16
InteGrade profile 2000mm(79") T style SD	8718291 676485 00	9290 008 53113	16
InteGrade profile 2356mm (93") M style	8718291 703198 00	9290 008 71313	36
InteGrade magnet for M style profile	9718291 707271 00	9290 008 71413	100

Compatibility with InteGrade engines and fixtures

InteGrade engine value and vision	InteGrade engine Uniform Beam (UB) value and vision	InteGrade engine Narrow Beam (NB) value and vision	InteGrade Fixture Narrow Beam (NB) value and vision	InteGrade engine High Flux (HF)	InteGrade Fixture (DIY)	Product name	12NC
•	•	•	•	•	•	InteGrade power cable 1m(39") black	929000641014
•	•	•	•	•	•	InteGrade power cable 1m(39") white	929000645614
•	•	•	•	•	•	InteGrade power cable 2.5m(98") black	929000641114
•	•	•	•	•	•	InteGrade power cable 2.5m(98") white	929000644514
•	•	•			•	InteGrade cable 1m(39") black angle	929000644614
•	•	•			•	InteGrade cable 1m(39") white angle	929000644714
•	•	•			•	InteGrade cable 2.5m(98") black angle	929000644814
•	•	•			•	InteGrade cable 2.5m(98") white angle	929000644914
•	•	•			•	InteGrade spacer cable 0.5m black	929000645014
•	•	•			•	InteGrade spacer cable 0.5m white	929000645114
•	•				•	InteGrade extension cable 1.5m(59")black	929000874413
•	•				•	InteGrade Y cable black	929000874313
•	•					InteGrade mounting clip canopy	929001571106
•						InteGrade engine mounting clip G2	929001516106
•						InteGrade engine clip shelf arm G2	929001516006
					•	InteGrade mounting clip under shelf	929000643903
					•	InteGrade mounting clip shelf arm v2	929000957806
		•	•		•	InteGrade mounting clip for T style profile	929000853213
•	•				•	InteGrade rotational bracket	929000874613
		•		•	•	InteGrade connector	929000959106
		•		•	•	InteGrade engine lock inline	929000643713
					•	InteGrade profile 875mm(34")	929000643413
					•	InteGrade profile 1175mm(46")	929000643313
					•	InteGrade profile 2000mm(79")	929000654413
•	•				•	InteGrade profile 2000mm(79") L style	929000654513
					•	InteGrade profile 2000mm(79") F style	929000654313
		•			•	InteGrade profile 2000mm(79") T style SD	929000853113
		•			•	InteGrade profile 2000mm(79") T style CTR	929000853013
					•	InteGrade profile 2356mm (93") M style	929000871313
					•	InteGrade magnet for M style profile	929000871413

## Mechanical characteristics



## Absolute ratings

Parameter	Min	Typ	Max	Unit
Ambient temperature	-30		30	°C
Storage temperature	-30		60	°C



© 2017 Philips Lighting Holding B.V. All rights reserved.

This document contains information relating to the Philips Lighting portfolio, intended for companies who may be interested in developing their product offering. Note that the information provided is subject to change. Philips Lighting does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

[www.philips.com/technology](http://www.philips.com/technology)

06/2017