



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2021011002386035

Valid from: May.17,2021

Valid until: May.17,2026

**NAME AND REGISTERED
ADDRESS OF THE APPLICANT**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND REGISTERED
ADDRESS OF THE
MANUFACTURER**

Signify (China) Investment Co., Ltd.
Building no.9, Lane 888, Tianlin Road, Minhang District, Shanghai 200233, China

**NAME AND LOCATION
OF THE FACTORY**

Zhejiang Klite Lighting Holdings Co., Ltd.
No.12 TingChao Road, JianShan New District, HaiNing City, ZheJiang Province, P.R.China

PRODUCT MODEL(S)

A.C. Supplied Electronic Controlgear For LED Modules (LED Controlgear, Independent, Constant Current Mode, SELV, Class II, IP20, ta:50°C, tc:85°C, Suitable For Direct Mounting On Normally Flammable Material, Non-Controlled Port Dimming)
See Appendix ; Input : 220-240V ~ 50/60Hz

**STANDARDS AND
TECHNICAL REQUIREMENTS**

GB 17625.1-2012;GB/T 17743-2017;GB 19510.1-2009;GB 19510.14-2009

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO. CNCA-C10-01:2014)

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

The certificate information is available through the QR code below or CNCA' s website: www.cnca.gov.cn



SIGNATURE:

CHINA QUALITY CERTIFICATION CENTRE



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO. : 2021011002386035

page 1 of 1

paper:

This certificate and attachments shall be used at the same time, and the verification instructions can be found in the main certificate.

型号	输入电 流 (A)	输入功 率(W)	单路输 出电流 (A)	输出总 电流(A)	输出电压 (Vdc)	最大输出 电压 (Vdc)	输出总 功率 (W)	拨码开关		输出方式
								1	2	
Xitanium 44W 0.7-1.05A 42V WIZ TW 230V	0.16	34.4	0.70	0.70	30-42	60	29.4	ON	ON	两路输出 (CW + ~ CW-、 WW + ~ WW-)
	0.18	39.1	0.80	0.80	30-42	60	33.6	ON	-	
	0.20	44.0	0.90	0.90	30-42	60	37.8	-	ON	
	0.23	51.2	1.05	1.05	30-42	60	44.1	-	-	

型号	输入电 流 (A)	输入功 率(W)	输出电流(A)	输出电压 (Vdc)	最大输出 电压 (Vdc)	输出总 功率 (W)	拨码开关		输出方式
							1	2	
Xitanium 44W 0.7-1.05A 42V WIZ DM 230V	0.16	34.4	0.70	30-42	60	29.4	ON	ON	单路输出 (LED+ ~ LED-)
	0.18	39.1	0.80	30-42	60	33.6	ON	-	
	0.20	44.0	0.90	30-42	60	37.8	-	ON	
	0.23	51.2	1.05	30-42	60	44.1	-	-	

输入均为：220-240V ~ , 50/60Hz

Annex



CHINA QUALITY CERTIFICATION CENTRE