

LED driver





Datasheet

Xitanium Basic Prog LED Outdoor drivers

Xi BP 75W 0.2-0.7A S 230V C133 sXt

9290 028 17006

Xitanium Basic Prog LED Outdoor drivers

Philips Xitanium Basic Programmable LED drivers are offering a basic feature set and high performance, making it a preferred choice for various outdoor applications. The portfolio offers flexibility with a customizable operating window, enabling differentiation in LED lighting designs via system tuning and being prepared for LED efficacy upgrades. In this product family Philips offers drivers in compact form factors with a basic feature set, which offer high value for both OEM customers and end-users. The key features AOC (Adjustable Output Current) and OWP (Over Write Protection) are programmable via SimpleSet^{*}, an easy and fast way to configure the driver without the need to power the driver. A great combination with MultiOne Basic configuration software. The products can replace the existing single current outdoor LED drivers and will bring significant improvement in programming, assembly into a luminaire, electrical performance, and less variety in logistical codes.

Benefits

- Outdoor robustness, offering peace of mind and lower maintenance costs
- Basic configurable features covering many applications
- Easy to design-in and install for Insulation Class I and Class II applications
- Enabling integration in small(er) size luminaires due to compact form factor(s)

Features

- \bullet SimpleSet $^{\circ},$ wireless configuration interface
- High surge immunity
- Long lifetime and robust protection against moisture, vibration and temperature
- Configurable operating window (AOC)
- Over Write Protection (OWP)

Application

- Road and street lighting
- Park lighting (e.g. BP 12W driver for bollards, landscape fixture, wall mounts)
- Residential lighting
- Architectural lighting

Electrical input data

Specification item	Value	Unit	Condition
Rated input voltage range	202254	V _{ac}	Performance range
Rated input voltage	230	V _{ac}	
Rated input frequency range	4763	Hz	Performance range
Rated input current	0.37	A	@ rated output power @ rated input voltage
Max. input current	0.42	A	@ rated output power @ minimum performance input voltage
Rated input power	84	W	@ rated output power @ rated input voltage
Power factor	0.98		@ rated output power @ rated input voltage
Efficiency	91.5	%	@ rated output power @ rated input voltage @ max. Uout
Input voltage AC range	170264	Vac	Safety operational range
Input frequency AC range	4566	Hz	Safety operational range
Isolation input to output	Double		

Electrical output data


Specification item	Value	Unit	Condition
Regulation method	Constant Current		
Output voltage	50150	V _{dc}	
Output voltage max.	220	V	Maximum voltage at open load
Output current	0.20.7	A	
Output current min programmable	200	mA	
Output current tolerance ±	5	%	
Output current ripple LF	≤ 4	%	Ripple = peak / average @ < 3kHz
Output current ripple HF	≤ 4	%	
Output P _{st} ^{LM}	≤ 0.04		In entire operating window
Output SVM	≤ 0.08		In entire operating window
Output power	24.875	W	

Electrical data controls input

Specification item	Value	Unit	Condition
Control method	Fixed		No control options available

Wiring and Connections

Specification item	Value	Unit	Туре
Input wire cross-section	0.51.5 / 2016	mm ² / AWG	solid / stranded wire
Input wire strip length	8.59.5	mm	
Output wire cross-section	0.51.5 / 2016	mm ² / AWG	solid / stranded wire
Output wire strip length	8.59.5	mm	
Maximum cable length	1.5	m	CISPR15: between driver and LED module





Insulation

Insulation per IEC61347-1	Mains	EQUI	LED
Mains		Double	Double
EQUI	Double		Basic
LED	Double	Basic	

Dimensions and weight

Specification item	Value	Unit	Tolerance (mm)
Length (A1)	133	mm	
Mounting hole distance (A2)	122	mm	
Width (B1)	77	mm	
Height (C1)	39.5	mm	
Mounting hole diameter (D1)	4.2	mm	
Weight	595	gram	






Logistical data

Specification item	Value
Product name	Xi BP 75W 0.2-0.7A S 230V C133 sXt
EOC	871951426997200
Logistic code 12NC	9290 028 17006
EAN1 (GTIN)	8719514269972
EAN3 (box)	8719514269989
Pieces per box	12

Operational temperatures and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-40+55	°C	Higher ambient temperature allowed as long as Tcase-max is not
			exceeded
Tcase-max	80	°C	Maximum temperature measured at T _{case} -point
Tcase-life	70	°C	Measured at T _{case} -point
Maximum housing temperature	130	°C	In case of a failure, inherent by design
Relative humidity	1090	%	Non-condensing

Lifetime



Storage temperature and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-40+80	°C	
Relative humidity	595	%	Non-condensing

Programmable features

Specification item	Available	Default setting	Condition
Set Adjustable Output Current (AOC)	SimpleSet	700 mA	
OEM Write Protection (OWP)	Yes	OFF	

Features

Specification item	Value	Condition
Open load protection	Yes	Automatic recovering
Short circuit protection	Yes	Automatic recovering
Over power protection	Yes	Automatic recovering
Hot wiring	No	
Suitable for fixtures with protection class	I and II	per IEC60598
Overtemperature protection	Yes	Automatic recovering

Inrush current

Specification item	Value	Unit			Condition
nrush current I _{peak}	30	А			Input voltage 230V
nrush current T _{width}	320	μs			Input voltage 230V, measured at 50% I _{peak}
Drivers / MCB 16A type B	≤ 10	pcs			Indicative value
			MCB	Rating	Relative number of LED drivers
T /\			В	4A	25%
			В	6A	40%
			В	10A	63%
Ipeak Twidth			В	13A	81%
·width			В	16A	100% (stated in datasheet)
			В	20A	125%
		_	В	25A	156%
			В	32A	200%
			В	40A	250%
			С	4A	42%
			с	6A	63%
			С	10A	104%
			С	13A	135%
			С	16A	170%
			С	20A	208%

Driver touch current / protective conductor current

Specification item	Value	Unit	Condition
Typical Touch Current (ins. Class II)	0.3	mA peak	Acc. IEC61347-1. LED module contribution not included
Typical Protective Conductor Current (ins. Class I)	0.2	mA rms	Acc. IEC60598-1. LED module contribution not included

c c

С

С

25A

32A

40A

260%

340%

415%

Surge immunity


Specification item	Value	Unit	Condition
Mains surge immunity (diff. mode)	6	kV	L-N acc. IEC61000-4-5. 2 Ohm, 1.2/50us, 8/20us
Mains surge immunity (comm. mode)	10	kV	L/N - EQUI 10kV acc. EN61547; 8kV acc. IEC61000-4-5, 12 Ohm
			1.2/50us,8/20us

Application Info


Specification item	Value	
Approval marks	CCC / CE / Double-insulated Built-In / EAC / ENEC / UA / WEEE	
Ingress Protection classification (IP)	20	
Application	Outdoor	
Mounting Type	Built-in	

Graphs


Operating window




Thermal Guard




Mains Guard






Efficiency versus output power



THD versus output power





©2021 Signify Holding, IBRS 10461, 5600 VB, NL. All rights reserved. UK importer address: Signify Commercial UK Limited, 3, Guildford Business Park, GU2 8XG.

The information provided herein is subject to change without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Date of release: June 17, 2021 v3

www.philips.com/oem