



# Datasheet

# LED Power Driver 240W 24VDC 120-240V 9290 021 02080

#### **Product description**

Philips full-electronic constant voltage LED Power drivers are designed to operate 24VDC LED solutions used in general built-in applications such as refrigerated display lighting, retail display lighting and linear accent lighting. They are specifically designed to ensure the highest performance with maximum robustness combined with a long lifetime.

#### **Benefits**

- SELV operating voltages, ensuringsafety even if wiring or LED boardsbecome damaged
- Energy savings through high efficiency
- Ultimate robustness, offering peace of mind and lower maintenance costs
- Easy to design-in and install
- Long lifetime

#### Feature

- Built-in use for Insulation Class I and II applications
- Global approbations and certifications
- Stable output voltage
- Wide ambient temperature range
- Protection against overpower and overvoltage
- Output short-circuit shutdown feature with automatic restart

#### **Application**

- Retail display lighting, linear accent lighting and refrigerated display lighting
- Shelf lighting
- Cove lighting
- Facade accent lighting
- Coolers and freezers

# Electrical input data

Specification item	Value	Value	Unit	Condition
Rated input voltage range	108132	202254	V <sub>ac</sub>	Performance range
Rated input voltage	120	230	V <sub>ac</sub>	
Rated input frequency range	4763	4763	Hz	Performance range
Rated input current	2.25	1.1	А	@ rated output power @ rated input voltage
Max. input current	2.5	1.3	Α	@ rated output power @ minimum performance input
				voltage
Rated input power	263	258	w	@ rated output power @ rated input voltage
Power factor	0.98	0.97		@ rated output power @ rated input voltage
Total harmonic distortion	6	16	%	@ rated output power @ rated input voltage
Efficiency	91	93	%	@ rated output power @ rated input voltage
Input voltage AC range	108132	198264	V <sub>ac</sub>	Safety operational range
Input frequency AC range	4566	4566	Hz	Safety operational range
Isolation input to output	SELV	SELV		

# **Electrical output data**


Specification item	Value	Unit	Condition
Regulation method	Constant Voltage		
Output voltage	24	V <sub>dc</sub>	Output voltage range: 23.5 25.6VDC
Output voltage max.	26	V	
Output current	0.110	Α	
Output voltage ripple	≤ 240	mV <sub>pp</sub>	
Output power	2.4240	W	
Line regulation	≤ 0.1	%	
Load regulation	≤ 0.5	%	
Turn-on delay	≤ 0.18	S	With Integrade engine 24VDC module at rated output power
Output voltage rise time	≤ 30	ms	
Hold-up time	≥ 10	ms	

# Electrical data controls input

Specification item	Value	Unit	Condition
Control method	Fixed		

#### **Wiring and Connections**

Specification item	Value	Unit	Туре
Input wire cross-section	0.75 / 19	mm <sup>2</sup> / AWG	Solid wire
Output wire cross-section	0.75 / 19	mm <sup>2</sup> / AWG	Solid wire
Maximum cable length	2.5	m	Total cable length between driver and LED modules




- IEC: connecting driver housing to Protective Earth (PE) not mandatory unless appliance touch current exceeds 0.7mA\_peak
- Do not insulate the driver housing from the appliance chassis, use toothed washers when mounting the driver

#### Insulation

Insulation per IEC61347-1	Mains	LED output	Housing
Mains		SELV	Double
LED output	SELV		Double
Housing	Double	Double	

# Dimensions and weight

Specification item	Value	Unit	Tolerance (mm)
Length (A1)	240	mm	
Mounting hole distance (A2)	229.2	mm	
Length (A3)	219.1	mm	
Width (B1)	70	mm	
Width (B2)	34.2	mm	
Height (C1)	37.5	mm	
Mounting hole diameter (D1)	4.2	mm	
Weight	1035	gram	



# Logistical data


Specification item	Value
Product name	LED Power Driver 240W 24VDC 120-240V
EOC	871869967938500
Logistic code 12NC	9290 021 02080
EAN1 (GTIN)	8718699679385
Pieces per box	6

# Operational temperatures and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-30+60	°C	Higher ambient temperature allowed as long as Tcase-max is not
			exceeded
Tcase-max	90	°C	Maximum temperature measured at T <sub>case</sub> -point
Tcase-life	80	°C	Measured at T <sub>case</sub> -point
Maximum housing temperature	110	°C	In case of a failure, inherent by design
Relative humidity	1090	%	Non-condensing

#### Lifetime

Specification item	Value	Unit	Condition
Driver lifetime	50,000	hours	Measured temperature at Tcase-point is Tcase-life. Maximum
			failures = 10%



# Storage temperature and humidity


Specification item	Value	Unit	Condition
Ambient temperature	-30+85	°C	
Relative humidity	595	%	Non-condensing

# Features

Specification item	Value	Condition
Open load protection	Yes	Automatic recovering
Short circuit protection	Yes	Hiccup mode, automatic recovering
Over power protection	Yes	Automatic recovering
Hot wiring	Yes	
Suitable for fixtures with protection class	I and II	per IEC60598
Overtemperature protection	Yes	Automatic recovering

#### Inrush current

Specification item	Value	Unit	Condition
Inrush current I <sub>peak</sub>	125	A	Input voltage 230V
Inrush current T <sub>width</sub>	210	μs	Input voltage 230V, measured at 50% I <sub>peak</sub>
Drivers / MCB 16A type B	≤ 4	pcs	Indicative value



МСВ	Rating	Relative number of LED drivers		
В	4A	25%		
В	6A	40%		
В	10A	63%		
В	13A	81%		
В	16A	100% (stated in datasheet)		
В	20A	125%		
В	25A	156%		
В	32A	200%		
В	40A	250%		
С	4A	42%		
С	6A	63%		
С	10A	104%		
С	13A	135%		
С	16A	170%		
С	20A	208%		
С	25A	260%		
С	32A	340%		
С	40A	415%		

# Driver touch current / protective conductor current

Specification item	Value	Unit	Condition
Typical Touch Current (ins. Class II)	0.42	mA peak	Acc. IEC61347-1. LED module contribution not included
Typical Protective Conductor Current (ins. Class I)	0.3	mA rms	Acc. IEC60598-1. LED module contribution not included

# Surge immunity


Specification item	Value	Unit	Condition
Mains surge immunity (diff. mode)	2	kV	L - N acc. IEC61000-4-5, 20hm
Mains surge immunity (comm. mode)	4	kV	L/N - GND acc. IEC61000-4-5, 120hm

# **Application Info**


Specification item	Value	
Approval marks	CCC / CE / Double-insulated / EAC / ENEC / RCM / SELV / VDE / VDE household / VDE-EMC	
Ingress Protection classification (IP)	20	
Application	Indoor Constant Voltage	
Mounting Type	Built-in	

# Graphs


# Operating window




# Power factor versus output power



# **Efficiency versus output power**



#### **THD** versus output power



#### **Notes**

Ingress Protection (IP):

The LED Power Driver is intended for built-in use. It must not be exposed including but not limited to snow, water and ice or any other chemical agent which may have an adverse affect on driver operation and performance. Exposure may lead to driver failure. It is the luminaire manufacturer's / installer's responsibity to prevent exposure.

Driver is certified per following standards:

Safety:

EN~61347-1:2015~(IEC~61347-1:2015), EN~61347-2-13:2014~(IEC~61347-2-13:2014), GB~19510.1-2009, GB~19510.2.14-2009, GB~19510.2.14-20000, GB~19510.2.14-2000, GB~19510.2.14-2000, GB~19510.2.14-2000, GB~19510.2.14-2000, GB~19510

Household:

IEC 60335-1:2010+AMD1:2013+AMD2:2016; IEC 60335-2-24:2010+AMD1:2012; IEC 60335-2-89:2010

+AMD1:2012 +AMD2:2015

Compliant to the "Non-sparking 'n' electrical apparatus" requirements of IEC/EN 60335-2-89, Annex BB and IEC/EN 60335-2-24, Annex CC

EMC:

Emissions: EN55015:2013 + A1:2015, EN61000-3-2 Class C, (>60% load):2014, EN61000-3-3:2013, GB/T 17743-2017

Immunity: EN61000-4-2, 3, 4, 5, 6, 8, 11, EN61547-1:2009, GB 17625.1-2012

Performance:

IEC 62384:2006 + A1:2009

Mains input wires have double insulation.



© 2021 Signify Holding, IBRS 10461, 5600 VB, NL. All rights reserved. UK importer address: Signify Commercial UK Limited, 3, Guildford Business Park, GU2 8XG.

The information provided herein is subject to change without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Date of release: January 19, 2021 v2