

PHILIPS

Sensors

EasyAir

Supported switches



Switch Commissioning Procedure

List of supported switches

This document shows the list of supported switches within Philips Field Apps for EasyAir office sensor SNS200v2 and SNS200v1.

Switch Brand	Type, Identifier	EnOcean Module	Release Status SNS200/SNH200	Commissioning procedure
Philips	UID8450/10 Single Rocker	PTM215Z	Supported	Web Link
	UID8460/10 Dual Rocker	PTM215Z	Supported*, **	Web Link
	Hue Tap	PTM215Z	Supported (Limited functionality – no dimming)	Web Link
Jaeger Direkt	Single Rocker	PTM215ZE	Supported	Web Link
	Dual Rocker	PTM215ZE	Supported	Web Link
Vimar	Dual Rocker	PTM215ZE	Supported	Web Link
Legrand	Single Rocker	Info not available	Supported	Web Link
	Dual Rocker	Info not available	Supported	Web Link

Note: A Single Rocker/ Dual Rocker switch may also be known as 2 button /4 button switch respectively.

Note: Only one type / brand of switch can be supported within one group. Multiple switch-tables are not supported.

Note: SNH200 doesn't support scene settings.

* If a long press is made on Philips UID8460/10, it is susceptible to channel change.

** Dimming is supported only when 2 buttons are pressed together.



© 2019 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

03/2019
Data subject to change

[www.lighting.philips.co.uk/oem-emea/
products/connected-lighting](http://www.lighting.philips.co.uk/oem-emea/products/connected-lighting)