



# Datasheet

# Xitanium LITE Prog LED drivers Independent Xi LP 200W 0.3-1.05A S1 WL I195

9290 028 79180

Philips Xitanium Lite Programmable LED drivers are value engineered to deliver a carefully selected feature set and high-end performance, making it a preferred choice for many outdoor applications. The portfolio offers high flexibility with a customizable operating window, enabling differentiation in LED lighting designs via system tuning and being prepared for LED efficacy upgrades.

In this product family Philips introduces new drivers in a stretched form factor with a balanced feature set, which offer high value for both OEM customers and end-users. The products can replace the existing programmable outdoor LED drivers and will bring significant improvement in programming, assembly into a luminaire and electrical performance. One of the key features is SimpleSet\*, an easy and fast way to configure the driver without the need to power the driver.

#### Benefits

- Ultimate robustness, offering peace of mind and lower maintenance costs
- Long lifetime and high survival rate
- Energy savings through high efficiency
- Balanced configurable feature set covering the most common applications
- Superior thermal management
- Consistent waterproof performance through the lifecycle
- Easy to design-in, configure and install for Class I applications

#### Features

- SimpleSet\*, wireless configuration interface
- High surge protection
- Long lifetime and robust protection against moisture, vibration and temperature
- Configurable operating windows(AOC)
- External control interface (1-10V) available
- Digital Configuration Interface (DCI) via MultiOne Interface
- Autonomous or Fixed time based (FTBD) dimming via integrated 5-step DynaDimmer
- Programmable Constant Light Output (CLO)
- Integrated Driver Temperature protection

#### **Application**

- Residential areas
- Road and street lighting
- Area and flood lighting
- Tunnel lighting
- High-bay lighting

## **Electrical input data**

Specification item	Value	Unit	Condition
Rated input voltage range	202254	V <sub>ac</sub>	Performance range
Rated input voltage	230	V <sub>ac</sub>	
Rated input frequency range	4763	Hz	Performance range
Rated input current	0.96	A	@ rated output power @ rated input voltage
Max. input current	1.12	A	@ rated output power @ minimum performance input voltage
Rated input power	224	W	@ rated output power @ rated input voltage
Power factor	0.95		@ rated output power @ rated input voltage
Total harmonic distortion	10	%	@ rated output power @ rated input voltage
Efficiency	92	%	@ rated output power @ rated input voltage @ max. Uout
Input voltage AC range	85305	V <sub>ac</sub>	Operational range
Input frequency AC range	4566	Hz	Operational range
Isolation input to output	Basic		

# **Electrical output data**

Specification item	Value	Unit	Condition
Regulation method	Constant Current		
Output voltage	142286	$V_{dc}$	
Output voltage max.	420	V	Maximum voltage at open load
Output current	0.31.05	Α	
Output current min programmable	300	mA	
Output current min dimming	70	mA	
Output current tolerance ±	5	%	
Output current ripple LF	≤ 4	%	Ripple = peak / average@ ≤1KHz
Output current ripple HF	≤ 15	%	
Output P <sub>st</sub> <sup>LM</sup>	≤ 0.12		In entire operating window
Output SVM	≤ 0.07		In entire operating window
Output power	10200	W	

# Electrical data controls input

Specification item	Value	Unit	Condition
Control method	1-10V		Default: 1-10V. Optional: reversed 1-9V, reversed 0-5V
Dimming range	10100	%	Default range
Isolation controls input to output	Basic		acc. IEC61347-1

2 / 8 Xi LP 200W 0.3-1.05A S1 WL 1195 May 2021

## **Wiring and Connections**


Specification item	Value	Unit	Туре
Input wire cross-section	1	mm²	3x 1.0mm2 stranded wires, waterproof cable
Output wire cross-section	1	mm²	2x 1.0mm2 stranded wires, waterproof cable
Control wire cross-section	1	mm²	2x 1.0mm2 stranded wires, waterproof cable
Maximum cable length	2	m	Total length of wiring including LED module, one way

#### Insulation

Insulation per IEC61347-1	Input	Output	1-10V&Aux	Ground
Input		Basic	Basic	Basic
Output	Basic		Basic	Basic
1-10V&Aux	Basic	Basic		Basic
Ground	Basic	Basic	Basic	

# Dimensions and weight

Specification item	Value	Unit	Tolerance (mm)
Length (A1)	195	mm	±1
Mounting hole distance (A2)	183	mm	±1
Length (A3)	171	mm	±1
Width (B1)	68	mm	± 0.5
Width (B2)	52.4	mm	± 0.5
Width (B3)	34	mm	± 0.3
Height (C1)	40	mm	± 1
Mounting hole diameter (D1)	4.2	mm	± 0.2
Input cable length (E1)	450	mm	± 30
Output cable length (E2)	450	mm	± 30
Control cable length (E3)	250	mm	± 30
Weight	830	gram	



3 / 8 Xi LP 200W 0.3-1.05A S1 WL 1195 May 2021

# Logistical data


Specification item	Value
Product name	Xi LP 200W 0.3-1.05A S1 WL 1195
EOC	692234194629500
Logistic code 12NC	9290 028 79180
EAN1 (GTIN)	6922341946295
EAN3 (box)	06922341946301
Pieces per box	12

## Operational temperatures and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-40+55	°C	Higher ambient temperature allowed as long as Tcase-max is not
			exceeded
Tcase-max	85	°C	Maximum temperature measured at T <sub>case</sub> -point
Tcase-life	75	°C	Measured at T <sub>case</sub> -point
Maximum housing temperature	130	°C	In case of a failure, inherent by design
Relative humidity	1090	%	Non-condensing

#### Lifetime

Specification item	Value	Unit	Condition
Driver lifetime	50,000	hours	Measured temperature at Tcase-point is Tcase-max. Maximum
			failures = 10%



# Storage temperature and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-40+80	°C	
Relative humidity	595	%	Non-condensing

4/8 Xi LP 200W 0.3-1.05A S1 WL 1195 May 2021

## **Programmable features**


Specification item	Available	Default setting	Condition
Set Adjustable Output Current (AOC)	SimpleSet	700 mA	
Adjustable Light Output (ALO)	Yes		
Constant Light Output (CLO)	Yes		
1-10V	Yes		
Dynadimmer	Yes		

## Features

Specification item	Value	Condition
Open load protection	Yes	Automatic recovering
Short circuit protection	Yes	Automatic recovering
Over power protection	Yes	Automatic recovering
Hot wiring	No	
Suitable for fixtures with protection class	I	per IEC60598
Overtemperature protection	Yes	Automatic recovering
Diagnostics	Yes	

#### Inrush current

Specification item	Value	Unit	Condition
Inrush current I <sub>peak</sub>	65	A	Input voltage 230V
Inrush current T <sub>width</sub>	378	μs	Input voltage 230V, measured at 50% I <sub>peak</sub>
Drivers / MCB 16A type B	≤ 5	pcs	Indicative value



MCB	Rating	Relative number of LED drivers
В	4A	25%
В	6A	40%
В	10A	63%
В	13A	81%
В	16A	100% (stated in datasheet)
В	20A	125%
В	25A	156%
В	32A	200%
В	40A	250%
С	4A	42%
С	6A	63%
С	10A	104%
С	13A	135%
С	16A	170%
С	20A	208%
С	25A	260%
С	32A	340%
С	40A	415%

## Driver touch current / protective conductor current

Specification item	Value	Unit	Condition
Typical Protective Conductor Current (ins. Class I)	0.7	mA rms	Acc. IEC60598-1. LED module contribution not included

5 / 8 Xi LP 200W 0.3-1.05A S1 WL 1195 May 2021

## **Surge immunity**


Specification item	Value	Unit	Condition
Mains surge immunity (diff. mode)	6	kV	Acc. IEC61000-4-5. 2 Ohm, 1.2/50us, 8/20us
Mains surge immunity (comm. mode)	10	kV	Acc. IEC61000-4-5. 12 Ohm 1.2/50us,8/20us

## **Application Info**


Specification item	Value
Approval marks	CB / CCC / CE / ENEC / UKCA
Ingress Protection classification (IP)	67
Application	Outdoor
Mounting Type	Independent

## Graphs


# Operating window




## **Thermal Guard**




6/8 Xi LP 200W 0.3-1.05A S1 WL 1195 May 2021



#### Power factor versus output power




# Efficiency versus output power





7/8 Xi LP 200W 0.3-1.05A S1 WL 1195 May 2021


#### **THD versus output power**




#### I<sub>out</sub> as function of 1-10V interface









Note:

During reversed dimming mode, when the DIM+/DIM- is open, the driver will be at maximum output current.



© 2021 Signify Holding, IBRS 10461, 5600 VB, NL. All rights reserved. UK importer address: Signify Commercial UK Limited, 3, Guildford Business Park, GU2 8XG.

The information provided herein is subject to change without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Date of release: May 27, 2021 v1