

## Datasheet

# Xitanium non-isolated Single Current (Dipswitch)

Xitanium 50W 0.2/0.25A 100-200V DS 230V 9290 016 95106

#### Xitanium LED drivers with single current output offer industry leading performance and reliability at optimized cost.

They are ideal for high volume applications while delivering to specific requirements. These drivers offer the same level of performance as Xitanium adjustable current linear drivers to ensure high quality of light, but with a specific current setting for optimized performance. Due to the low output current ripple, you can be sure to offer your customers high quality of light without visual flicker and stroboscopic effects.

#### **Benefits**

- High quality of light -assurance of camera and scanner-friendly performance
- High reliability
- Optimized performance at specific output current settings

#### **Features**

- Low output current tolerance
- Low output ripple current
- Long lifetime at high operating temperature
- Easy current selection via dipswitch
- Suitable for Class I luminaires

#### **Application**

- Offices
- Retail: supermarkets, shopping malls

#### **Electrical input data**

	1	1	1	
Specification item	Value	Value	Unit	Condition
Rated input voltage range	220240		V <sub>ac</sub>	Performance range
Rated input voltage	230		V <sub>ac</sub>	
Rated input frequency range	5060		Hz	Performance range
Rated input current	0.24		Α	@ rated output power @ rated input voltage
Rated input power	43	53	W	@ maximum rated output power @ rated input voltage
Power factor	0.98			@ maximum output power @ rated input voltage
Total harmonic distortion	9		%	@ maximum output power @ rated input voltage
Efficiency	92.8		%	@230V input, full load @ max. Uout
Rated input voltage DC range	186250		V <sub>dc</sub>	Performance range
Input voltage AC range	198264		V <sub>ac</sub>	Safety operational range
Input frequency AC range	4566		Hz	Safety operational range
Input voltage DC range	168275		V <sub>dc</sub>	Operational range
Isolation input to output	No			

### **Electrical output data**

	T.	1	
Specification item	Value	Unit	Condition
Regulation method	Constant Current		
Output voltage	100200	V <sub>dc</sub>	
Output voltage max.	250	V	Maximum output voltage (rms)
Output current	0.2 / 0.25	A	Select current 200mA (OFF) or 250mA (ON) via dipswitch
Output current tolerance ±	7	%	
Output current ripple LF	≤ 4	%	Ripple = peak / average, < 3kHz
Output P <sub>st</sub> LM	≤ 0.01		
Output SVM	≤ 0.07		
Output power	2050	W	

### Electrical data controls input

Specification item	Value	Unit	Condition
Control method	Fixed		Select output current via the dipswitch

### **Wiring and Connections**

Specification item	Value	Unit	Туре
Input wire cross-section	0.51.5 / 2016	mm <sup>2</sup> / AWG	WAGO744, solid wire
Input wire strip length	89	mm	
Output wire cross-section	0.51.5 / 2016	mm <sup>2</sup> / AWG	WAGO744, solid wire
Output wire strip length	89	mm	
Maximum cable length	2	m	Total length of wiring including LED module, one way





#### Insulation

Insulation per IEC61347-1	Input	Output	Housing
Input		No	Basic
Output	No		Basic
Housing	Basic	Basic	

### Dimensions and weight

Specification item	Value	Unit	Tolerance (mm)
Length (A1)	210	mm	
Mounting hole distance (A2)	198.4	mm	
Width (B1)	30.2	mm	
Height (C1)	21	mm	
Mounting hole diameter (D1)	4	mm	
Weight	134	gram	





### Logistical data


Specification item	Value
Product name	Xitanium 50W 0.2/0.25A 100-200V DS 230V
EOC	871951426647600
Logistic code 12NC	9290 016 95106
EAN1 (GTIN)	8719514266476
EAN3 (box)	8719514266483
Pieces per box	50

### Operational temperatures and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-25+50	°C	Higher ambient temperature allowed as long as Tcase-max is not
			exceeded
Tcase-max	75	°C	Lifetime 50khrs;
Tcase-life	65	°C	Lifetime 100khrs; measured at T <sub>c</sub> -point
Maximum housing temperature	110	°C	In case of a failure, inherent by design
Relative humidity	1090	%	Non-condensing

#### Lifetime

Specification item	Value	Unit	Condition
Driver lifetime	100,000	hours	Measured temperature at Tcase-point is Tcase-life. Maximum
			failures = 10%



### Storage temperature and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-25+85	°C	
Relative humidity	595	%	Non-condensing

### Programmable features


Specification item	Available	Default setting	Condition
Set Adjustable Output Current (AOC)	DipSwitch	200 mA	Manual set the output current via the dipswitch
DC emergency (DCemDim)	No		With a DC mains the output current is 100%. (EOFi)

#### **Features**

Specification item	Value	Condition
Open load protection	Yes	Mains reset needed
Short circuit protection	Yes	Automatic recovering
Over power protection	Yes	Automatic recovering
Hot wiring	No	
Suitable for fixtures with protection class	I	per IEC60598

#### Inrush current

Specification item	Value	Unit	Condition
Inrush current	20.2	A	Input voltage 230V
Inrush peak width	278	μѕ	Input voltage 230 V, measured at 50% height
Drivers / MCB 16A type B	≤ 41	pcs	Indicative value



Please refer to the driver design in guide if you use other MCB-types.

### Driver touch current / protective conductor current


Specification item	Value	Unit	Condition
Typical Protective Conductor Current (ins. Class I)	0.7	mA rms	Acc. IEC60598-1. LED module contribution not included

#### **Surge immunity**


Specification item	Value	Unit	Condition
Mains surge immunity (diff. mode)	1	kV	Acc. IEC61000-4-5. 2 Ohm, 1.2/50us, 8/20us
Mains surge immunity (comm. mode)	2	kV	Acc. IEC61000-4-5. 12 Ohm, 1.2/50us, 8/20us

### **Application Info**


Specification item	Value
Approval marks	CCC / CE / EAC / EL / ENEC / RCM
Ingress Protection classification (IP)	20
Application	Indoor Linear
Mounting Type	Built-in




### Power factor versus output power



#### Efficiency versus output power



### THD versus output power





© 2021 Signify Holding, IBRS 10461, 5600 VB, NL. All rights reserved. UK importer address: Signify Commercial UK Limited, 3, Guildford Business Park, GU2 8XG.

The information provided herein is subject to change without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Date of release: August 23, 2021 v3